

Modern MD2712PW

BE YOUR WINDOW TO THE WORLD







SPECIFICATIONS

PANEL SIZE	27"
PANEL RESOLUTION	1920 x 1080 (FHD)
REFRESH RATE	100Hz
RESPONSE TIME	1ms (MPRT) / 4ms (GTG)
PANEL TYPE	IPS
BRIGHTNESS (NITS)	300 cd/m2
VIEWING ANGLE	178°(H) / 178°(V)
ASPECT RATIO	16:9
CONTRAST RATIO	1000:1
sRGB	117% (CIE 1976)
ACTIVE DISPLAY AREA (MM)	597.888(H) x 336.312(V)
PIXEL PITCH (H X V)	0.3114(H) x 0.3114(V)
SURFACE TREATMENT	Anti-glare
DISPLAY COLORS	16.7M
COLOR BIT	8 bits (6 bits + FRC)
VIDEO PORTS	$1 \times HDMI^{TM}$ (1.4) $1 \times Type C$ (DisplayPort Alternate & 15W PD)
AUDIO PORTS	1 x Headphone-out
KENSINGTON LOCK	Yes
SPEAKER	2x 3W
VESA MOUNTING	75 x 75 mm
POWER TYPE	External Adaptor
POWER INPUT	100~240V, 50~60Hz
ADJUSTMENT (TILT)	-5° ~ 20°
ADJUSTMENT (SWIVEL)	-30° ~ 30°
ADJUSTMENT (PIVOT)	-90° ~ 90°
ADJUSTMENT (HEIGHT)	0 ~ 110 mm
DIMENSION (W X H X D)	613.5 x 413.3 x 200.8 mm (24.15 x 16.27 x 7.91 inch)
CARTON DIMENSION (W X H X D)	893 x 464 x 167 mm (35.16 x 18.27 x 6.57 inch)
WEIGHT (NW / GW)	5.85 kg (12.90 lbs) / 8 kg (17.64 lbs)
CERTIFICATES	CB/CE
VIDEO INPUT COMPATIBILITY	PC, Mac, PS5 [™] , PS4 [™] , Xbox, Mobile, Notebook * All trademarks and the registered trademarks are the property of their

FEATURES



27" FHD 1080P

27" View your applications, spreadsheets and more with a perfect 27 inches screen with a breathtaking viewing experience that comes with Full HD resolution



Instantly optimize the screen colors and brightness to ensure that you enjoy every detail at its best while creating your own on-line video



EyesErgo

EyesErgo An eye care solution designed with ergonomics in mind.



Less Blue Light PRO

BLESS
BLIGHT Use a hardware solution to reduce the light emission in the blueviolet region of the blue light spectrum (wavelength 415 to 455 nm).



Eye-Q Check

Help have self-check eyes & remind to take a rest while using the monitor for a long time.



Adjust the stand to the angle that is most suitable for you to keep yourself work comfortably.



Type C Display

Allows you to connect the latest devices more conveniently and with less trouble.



HDR Ready

Provide eye-catching detail through contrast and shadows adjustment.



Built-In Speaker

Built-in speakers allow you to listen clearly without connecting external speakers.

respective owners.



BUSINESS PRODUCTIVITY MONITORS

Modern MD2712PW

BE YOUR WINDOW TO THE WORLD

Note

HDMI $^{\text{TM}}$: 1920 x 1080 (Up to 100Hz) Type-C: 1920 x 1080 (Up to 100Hz) HDR Ready

Adaptive-Sync Support

CONNECTIONS



- 1. 1x Type C (DisplayPort Alternate)
- 2. 1x HDMI™ (1.4)
- 3. 1x Headphone-out
- 4. 1x DC Jack