MFC-L3780cdw

Advance Specification Sheet

Specifications:

Duint		
Print		
Print Technology	Digital Color LED	
Simplex Print Speed (max.) ¹	Up to 31ppm color/black	
Time to First Page ²	Less than 12.5 seconds mono / color	
Print Resolution (max.)	Up to 2400 x 600 dpi class	
Print Emulations	PCL5e, PCL5c, PCL6 (PCL XL Class 3.0), BR-Script3 ³ , PDF Version 1.7, XPS Version 1.0	
Scan		
Scan Speeds (max.) ⁴	Simplex: Up to 29ppm / 22ppm (black / color); Duplex: Up to 58ipm / 34ipm (black / color)	
Scan Resolution (max.)	Interpolated: Up to 19,200 x 19,200 dpi ADF (optical): Up to 600 x 600 dpi Glass (optical): Up to 1200 x 1200 dpi	
Scan To Capability	PC (Image, Email, OCR, File), Network Folder ⁵ , Email Server ⁶ , SharePoint, FTP, SSH Server (SFTP), USB Memory Stick ⁷ , Cloud Services (Web Connect) ⁸ , Mobile Devices ⁹ , Easy Scan to Email ¹⁰	
Advanced Scanning Features	Auto deskew, File split, Multi-page to single-page, Blank page skip, Base color removal, 1 to 2	
Duplex Scan	Yes	
Сору		
Copy Speed / Copy Resolution (max.)	Up to 31 cpm / Up to 600 x 600 dpi	
Copy Options	Sorting, N-in-1, Multi-copying (up to 99), Reduce / Enlarge 25 - 400% in 1% increments	
Duplex Copy	Yes	
	103	
Fax		
Fax Features	33.6K bps modem speed, Fax page memory: up to 500 pages ¹¹ , Fax forward to: Network Folder ⁵ and Email, Internet Fax ¹⁰ , PC Fax ¹²	
Connectivity & Compatibility		
Standard Interfaces	Wireless 802.11b/g/n (2.4GHz) / 802.11a/n (5GHz), Gigabit Ethernet, Hi-Speed USB 2.0	
USB Host	Front: Print from and scan to USB memory stick; external card reader	
Operating Systems Compatibility ¹³	For the latest OS compatibility and to download drivers, visit support.brother.com.	
Mobile Device Compatibility ⁹	AirPrint [®] , Mopria [®] , Brother Mobile Connect, Wi-Fi Direct [®]	
Cloud Services (Web Connect) ⁸	Google Drive [™] , Evernote [®] , OneDrive, OneNote, Dropbox, Box, SharePoint Online	
Brother Cloud Apps ¹⁰	Easy Scan to Email, Scan to Mobile, Cloud Secure Print, Fax Forward to Cloud or Email, Scan to Searchable PDF, Scan to Word, Scan to Excel, Scan to PowerPoint	
Alexa Print	Yes	
Security		
Security Features	Integrated NFC Card Reader, External Card Reader Compatibility, Active Directory, LDAP, Secure Function Lock, Enterprise Security (802.1x), TLS/SSL, IPSec, IP Filter, Syslog Reporting, SNMP v3, Secure Print, Setting Lock, Firmware Encryption	
Paper Handling		
Paper Input Capacity (max.) ¹⁴	250-sheets paper tray, 30-sheet Multipurpose tray	
Optional Input Capacity ¹⁴	250-sheets via optional lower tray	
Output Capacity (max.) ¹⁴	150 sheets	
Document Glass Size	Up to 8.5" x 11" (Letter)	
Auto Document Feeder Capacity ¹⁴	50 pages	
Paper Size (max.)	Standard Tray: Letter, Legal, Executive, A4, A5, A6, B5, B6, Folio Multipurpose Tray: Width 3.0" to 8.5", Length 4.57" to 14" Duplex: Letter, Legal, Folio	
Media Types	Standard Tray: Plain Paper, Thin Paper, Thick Paper, Recycled Paper Multipurpose Tray: Plain Paper, Thin Paper, Thick Paper, Recycled Paper, Bond, Label, Envelopes (up to 3), Glossy Paper	
Media Weights	Standard/Multipurpose Tray: 16 to 43 lbs ¹⁵ Optional Lower Tray: 16 to 28 lbs ADF: 16 to 28 lbs	
General		
Automatic Duplex Capability	Print, plus single-pass copy / scan	
Display	3.5" Touchscreen	
Customizable Shortcuts	48	
Processor	40 800 MHz	
	512 MB	
Memory (std.) Included Software ⁹	Brother Mobile Connect for iOS [®] and Android [™] Brother iPrint&Scan (desktop) for Windows and Mac [®] BRAdmin Light, BRAdmin Pro, Status Monitor ⁵ , Kofax PaperPort [™] SE 14 ⁵	
Refresh EZ Print Subscription Eligible		
	Yes	
Energy Star [®] Qualified	Yes	
Energy Star® Qualified EPEAT Certified	Yes Yes (Silver Rated)	
Energy Star® Qualified EPEAT Certified Maximum Monthly Duty Cycle ¹⁶	Yes Yes (Silver Rated) Up to 50,000 pages	
Energy Star® Qualified EPEAT Certified Maximum Monthly Duty Cycle ¹⁶ Recommended Monthly Volume ¹⁷	Yes Yes (Silver Rated) Up to 50,000 pages Up to 4,000 pages	
Energy Star® Qualified EPEAT Certified Maximum Monthly Duty Cycle ¹⁶	Yes Yes (Silver Rated) Up to 50,000 pages	



genuine **Replacement Supplies & Optional Accessories:**

optional	
TN229BK	Standard Yield Toner Cartridge (1,500 pages) ¹⁸
TN229C/M/Y	Standard Yield Toner Cartridge (1,200 pages)18
TN229 4PK	4 Pack of Standard Yield Black, Cyan, Magenta, and Yellow Toner Cartridges (approx. 1,500 BK / 1,200 CMY pages) $^{\rm 18}$
TN229XLBK	High Yield Toner Cartridge (3,000 pages)18
TN229XLC/M/Y	High Yield Toner Cartridge (2,300 pages)18
TN229XL 2PK	Twin Pack of High Yield Black Toner Cartridges (approx. 3,000 pages per cartridge) ¹⁸
TN229XXLBK	Super High Yield Toner (4,500 pages)18
TN229XXLC/M/Y	Super High Yield Toner (4,000 pages)18
TN229VBK	Value High Yield Toner (3,300 pages)18
TN229VC/M/Y	Value High Yield Toner (2,530 pages)18
DR229CL	Drum Unit (20,000 pages) ¹⁹
BU229CL	Belt Unit (50,000 pages) ²⁰
WT229CL	Waste Toner Box (50,000 pages) ²¹
LT-310CL	Optional 250-Sheet Capacity Paper Tray ¹⁴

Setup Information:

UPC Code	012502666486
Unit Dimensions / Weight	18.2" (W) x 16.1" (D) x 15.8" (H) / 47.8 lbs.
Carton Dimensions / Weight	23" (W) x 19.6" (D) x 21" (H) / 55 lbs.
Pallet Ti/Hi	4/2
Pallet Quantity	8
Country of Origin	Vietnam
Tariff / Harmonized Code	8443.31.0000

Carton Contents:

Brother MFC-L3780CDW, Starter Black Toner Cartridge (2,300 pages)¹⁸, Starter Cyan, Magenta, Yellow Toner Cartridges (1,200 pages)¹⁸, DR2290L Drum Unit (20.000 pgs)¹⁹, WT229CL Waste Toner Box (50.000 pages)²¹, BU229CL Belt Unit (50,000 pages)²⁰, AC Power Cord, Telephone Line Cord, Product Safety Guide, Reference Guide, Warranty Card, Quick Setup Guide



Working with you for a better environment

At Brother, our green initiative is simple. We strive to take responsibility, act respectfully and try to make a positive difference to help build a society where sustainable development can be achieved. We call this approach Brother Earth.



- 1 Based on one sided printing. Change from default
- 2
- 3 4
- 8
- Based on one sided printing. Change from default setting required. From ready mode and standard tray. PostScript@34" compatible. Color and monochrome scan speed with all advanced features turned off, Letter at 300dpi. Windows only. Requires mail server support. PDF (up to ver. 1.7), JPEG, XPS files. Secure PDF / Signed PDF scan only. Requires an Internet connection and an account with desired service. May requires free download. Compatibility may vary by device and operating system. Requires 9
- way by device and operating system. Requires connection to a wireless network.
 Requires an Internet connection.
 Using ITU-T Test Chart #1 with JBIG coding and std.
 B&W only. PC Fax Receive not available for Mac
- users. 13 For the latest 05 compatibility and to download drivers, visit support brother.com. Printing or scannig via mac05 requires the use of AirPrint. Mac printer drivers are not provided. Server 2012/2015/2019 network printing only. 14 Maximum capacity based on using 201b. paper. 15 Print speed may vary depending on size/type of paper used and paper source.

- 16 Maximum number of printed pages per month can be used to compare designed durability between like Brother products. For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds
- to choose a printer with a duty cycle that far exceeds your print requirements. 17 The recommended range of monthly printed pages to achieve the best possible performance and printer life. Printers are intended to handle occasional usage beyond this range with little or no effect. Consistently printing above the recommended print volume, however, may adversely affect the print quality or life of the machine. It is always best to choose a printer with an appropriate recommended print volume to allow for any anticinated increase in printin peeds.
- or the intachine: It is always best to choose a printer with an appropriate recommended print volume to allow for any anticipated increase in printing needs.
 18 Approximate to ner carting gyield in accordance with ISO/IEC 19738 (letter/A).
 19 Approximately 20,000 pages based on 1 page per job and 30,000 pages based on 3 pages per job (letter/A4 single-sided pages). The number of pages may be affected due to a variety of factors including but not limited to media type and media asize.
 20 Approximately 50,000 pages based on 2 pages per job limited to us to a yate per job limited to a variety of factors including but not affected due to a variety of factors including but not affected due to a variety of factors including but not affected due to a variety of factors including but not factors including but not affected use to a variety of factors including but not factors including but not affected affected affected and affected use to a variety of factors including but not factors including but not affected a
- media size.

©2023 BROTHER INTERNATIONAL CORPORATION ◆ All trademarks and registered trademarks referenced herein are the property of their respective companies. mac05, AirPint, and the AirPintl logo are registered trademarks of Apple Inc., registered in the U.S. and other countries. IOS is a trademarks or registered trademarks of Gooje LLC. Mopriat[™] and the Mopria[™] Logo are registered and/or unregistered trademarks of Gooje LLC. Mopriat[™] and the Mopria[™] Logo are registered and/or unregistered trademarks and service marks of Mopria Alliance, Inc. in the United States and other countries. Unauthorized use is strictly prohibited Wi-Fi DirectKy. the Wi-Fi Certified[™] logo and the Wi-Fi PirectKed Setup[™] Holmfifer Mark are trademarks on Wi-Fi Alliance0e. ENERGY STAR and the ENERGY STAR mark are registered trademarks owned by the U.S. Environmental Protection Agency. Evernote is a trademark of Evernote Corporation and used under a license. All specifications subject to change without notice.