

HL-L3280CDW

Advance Specification Sheet

brother
at your side

Specifications:

Print	
Print Technology	Digital Color LED
Simplex Print Speed (max.) ¹	Up to 27ppm color/black
Time to First Page ²	Less than 13.5 seconds color / black
Print Resolution (max.)	Up to 2400 x 600 dpi class
Print Emulations	PCL5e, PCL5c, PCL6 (PCL XL Class 3.0), BR-Script3 ³ , PDF Version 1.7, XPS Version 1.0
Connectivity & Compatibility	
Standard Interfaces	Wireless 802.11b/g/n (2.4GHz) / 802.11a/n (5GHz), Gigabit Ethernet, Hi-Speed USB 2.0
Operating Systems Compatibility ⁴	For the latest OS compatibility and to download drivers, visit support.brother.com
Mobile Device Compatibility ⁵	AirPrint®, Mopria™, Brother Mobile Connect, Wi-Fi Direct®
Cloud Services (Web Connect)®	Google Drive™, Evernote®, OneDrive, OneNote, Dropbox, Box, SharePoint Online
Alexa Print	Yes
Security	
Security Features	Active Directory, LDAP, Secure Function Lock, Enterprise Security (802.1x), Secure Print, TLS/SSL, IPsec, IP Filter, Syslog Reporting, SNMP v3, Setting Lock, Firmware Encryption
Paper Handling	
Input Capacity (max.) ⁷	250-sheets paper tray, single-sheet manual feed slot
Output Capacity (max.) ⁷	150 sheets
Paper Size (max.)	Standard Tray: Letter, Legal, Executive, A4, A5, A6, B5, B6, Folio Manual Feed Slot: Width 3.0" to 8.5", Length 4.57" to 14" Duplex: Letter, Legal, Folio
Media Types	Standard Tray: Plain Paper, Thin Paper, Thick Paper, Recycled Paper Manual Feed Slot: Plain Paper, Thin Paper, Thick Paper, Recycled Paper, Bond, Label, Envelope (single), Glossy Paper
Media Weights	Standard/Manual Feed Slot: 16 to 43 lbs ⁸
General	
Automatic Duplex	Print
Display	2.7" Color Touchscreen
Processor	800 MHz
Memory (std.)	256 MB
Included Software ⁹	Brother Mobile Connect for iOS® and Android™ Brother iPrint&Scan (desktop) for Windows and Mac® BRAdmin Light, BRAdmin Pro, Status Monitor ⁹
Refresh EZ Print Subscription Eligible	Yes
Energy Star® Qualified	Yes
EPEAT Certified	Yes (Silver Rated)
Maximum Monthly Duty Cycle ¹⁰	Up to 40,000 pages
Recommended Monthly Volume ¹¹	Up to 3,000 pages
Warranty	1-year limited warranty

Replacement Supplies & Optional Accessories:

brother
genuine

TN229BK	Standard Yield Toner Cartridge (1,500 pages) ¹²
TN229C/M/Y	Standard Yield Toner Cartridge (1,200 pages) ¹²
TN229 4PK	4 Pack of Standard Yield Black, Cyan, Magenta, and Yellow Toner Cartridges (approx. 1,500 BK / 1,200 CMY pages) ¹²
TN229XLBK	High Yield Toner Cartridge (3,000 pages) ¹²
TN229XLC/M/Y	High Yield Toner Cartridge (2,300 pages) ¹²
TN229XL 2PK	Twin Pack of High Yield Black Toner Cartridges (approx. 3,000 pages per cartridge) ¹²
TN229VBK	Value High Yield Toner (3,300 pages) ¹²
TN229VC/M/Y	Value High Yield Toner (2,530 pages) ¹²
DR229CL	Drum Unit (20,000 pages) ¹³
BU229CL	Belt Unit (50,000 pages) ¹⁴
WT229CL	Waste Toner Box (50,000 pages) ¹⁵

Setup Information:

UPC Code	012502670254
Unit Dimensions / Weight	15.7" (W) x 15.7" (D) x 10.8" (H) / 33.9 lbs.
Carton Dimensions / Weight	19.2" (W) x 19.2" (D) x 14.6" (H) / 39.7 lbs.
Pallet Ti/Hi	4 / 3
Pallet Quantity	12
Country of Origin	Vietnam
Tariff / Harmonized Code	8443.32.1090

Carton Contents:

Brother HL-L3280CDW, Starter Black Toner Cartridge (1,000 pages)¹², Starter Cyan, Magenta, Yellow Toner Cartridges (1,000 pages)¹², DR229CL Drum Unit (20,000 pgs)¹³, WT229CL Waste Toner Box (50,000 pages)¹⁵, BU229CL Belt Unit (50,000 pages)¹⁴, AC Power Cord, Product Safety Guide, Reference Guide, Warranty Card, Quick Setup Guide



Working with you for a better environment

At Brother, our green initiative is simple. We strive to take responsibility, act respectfully and try to make a positive difference to help build a society where sustainable development can be achieved. We call this approach Brother Earth.

COMPATIBLE WITH
WINDOWS



- Based on one sided printing. Change from default setting required.
- From ready mode and standard tray.
- PostScript[®]3™ compatible.
- For the latest OS compatibility and to download drivers, visit support.brother.com. Printing or scanning via macOS requires the use of AirPrint. Mac printer drivers are not provided. Server 2012/2016/2019 network printing only.
- May require free download. Compatibility may vary by device and operating system. Requires connection to a wireless network.
- Requires an Internet connection and an account with desired service.
- Maximum capacity based on using 20 lb. paper.
- Print speed may vary depending on size/type of paper used and paper source.
- Windows Only
- Maximum number of printed pages per month can be used to compare designed durability between like Brother products. For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds your print requirements.
- The recommended range of monthly printed pages to achieve the best possible performance and printer life. Printers are intended to handle occasional usage beyond this range with little or no effect. Consistently printing above the recommended print volume, however, may adversely affect the print quality or life of the machine. It is always best to choose a printer with an appropriate recommended print volume to allow for any anticipated increase in printing needs.
- Approximate toner cartridge yield in accordance with ISO/IEC 19798 (letter/A4).
- Approximately 20,000 pages based on 1 page per job and 30,000 pages based on 3 pages per job (letter/A4 single-sided pages). The number of pages may be affected due to a variety of factors including but not limited to media type and media size.
- Approximately 50,000 pages based on 2 pages per job and 60,000 pages based on 3 pages per job (letter/A4 single-sided pages). The number of pages may be affected due to a variety of factors including but not limited to media type and media size.
- Approximate yield is declared in accordance with ISO/IEC 19798 (A4/Letter single-sided pages). The number of pages may be affected due to a variety of factors including but not limited to media type and media size.