

MFC-L8395CDW

Digital Color All-in-One Printer with Duplex Print, Copy, Scan and Wireless Networking

brother
at your side

Specifications:

Print	
Print Technology	Digital Color LED
Print Speed (max.) ¹	Up to 31ppm color / black
Time to First Page ²	Less than 12.5 seconds color / black
Print Resolution (max.)	Up to 2400 x 600 dpi class
Print Emulations	PCL5e, PCL5c, PCL6 (PCL XL Class 3.0), BR-Script3 ³ , PDF Version 1.7, XPS Version 1.0
Scan	
Scan Speeds (max.) ⁴	Simplex: Up to 29ppm / 22ppm (black / color); Duplex: Up to 58ipm / 34ipm (black / color)
Scan Resolution (max.)	Interpolated ⁵ : Up to 19200 x 19200 dpi ADF (optical): Up to 600 x 600 dpi Glass (optical): Up to 1200 x 1200 dpi
Scan To Capability	PC (Image, Email, OCR, File), Network Folder ⁶ , Email Server ⁶ , SharePoint, FTP, SSH Server (SFTP), USB Memory Stick ⁷ , Cloud Services (Web Connect) ⁸ , Mobile Devices ⁹ , Easy Scan to Email ¹⁰
Advanced Scanning Features	Auto deskew, File split, Multi-page to single-page, Blank page skip, Base color removal, 1 to 2 Scan
Copy	
Copy Speed / Copy Resolution (max.)	Up to 31 cpm / Up to 600 x 600 dpi
Copy Options	Sorting, N-in-1, Multi-copying (up to 99), Reduce / Enlarge 25 - 400% in 1% increments
Fax	
Fax Features	33.6K bps modem speed, Fax page memory: up to 500 pages ¹¹ , Fax forward to: Network Folder ³ and Email, Internet Fax ¹⁰ , PC Fax ¹²
Connectivity & Compatibility	
Standard Interfaces	Wireless 802.11b/g/n (2.4GHz) / 802.11a/n (5GHz), Gigabit Ethernet, Hi-Speed USB 2.0
USB Host	Front: Print from and scan to USB memory stick; external card reader
Operating Systems Compatibility ¹³	For the latest OS compatibility and to download drivers, visit support.brother.com.
Mobile Device Compatibility ¹⁴	AirPrint®, Mopria®, Brother Mobile Connect, Wi-Fi Direct®
Cloud Services (Web Connect) ⁸	Google Drive™, Evernote®, OneDrive, OneNote, Dropbox, Box, SharePoint Online
Brother Cloud Apps ¹⁰	Easy Scan to Email, Scan to Mobile, Cloud Secure Print, Fax Forward to Cloud or Email, Scan to Searchable PDF, Scan to Word, Scan to Excel, Scan to PowerPoint
Included Brother Value Added Services	Remote Panel
Optional Brother Value Added Services	Secure Print+, Secure Print Advanced, Barcode Print+, Custom UI, Barcode Utility, ThinPrint Client, Remote Panel, Request Help, Order Supplies
Security	
Security Features	Integrated NFC Card Reader, External Card Reader Compatibility, Active Directory, LDAP, Secure Function Lock, Enterprise Security (802.1x), TLS/SSL, IPsec, IP Filter, Syslog Reporting, SNMP v3, Secure Print, Setting Lock, Firmware Encryption
Paper Handling	
Paper Input Capacity (max.) ¹⁵	250-sheets paper tray, 30-sheet Multipurpose tray
Optional Input Capacity (max.) ¹⁵	530-sheets via optional tray
Output Capacity (max.) ¹⁵	150 sheets
Document Glass Size	Up to 8.5" x 11" (Letter)
Auto Document Feeder Capacity ¹⁵	50 pages
Paper Size (max.)	Standard Tray: Letter, Legal, Executive, A4, A5, A6, B5, B6, Folio Multipurpose Tray: 3.0" - 8.5" (W) / 4.57" - 14" (L) Duplex: Letter, Legal, Folio
Media Types	Standard Tray: Plain Paper, Thin Paper, Thick Paper, Recycled Paper Multipurpose Tray: Plain Paper, Thin Paper, Thick Paper, Recycled Paper, Bond, Label, Envelopes (up to 3), Glossy Paper
Media Weights	Standard / Multipurpose Tray: 16 to 43 lbs. ¹⁶ Optional Tray: 16 to 28 lbs. ADF: 16 to 28 lbs.
General	
Automatic Duplex Capability	Print (default setting), plus single-pass copy / scan / fax
Display	3.5" Color Touchscreen
Customizable Shortcuts	48
Processor	800 MHz
Memory (std.)	512MB
Included Software ¹⁴	Brother Mobile Connect for iOS® and Android™ Brother iPrint&Scan (desktop) for Windows and Mac® BRAdmin Light, BRAdmin Pro, Status Monitor®, Kofax PaperPort™ SE 14 ⁵
Energy Star® Qualified	Yes
EPEAT Certified	Yes (Silver Rated)
Maximum Monthly Duty Cycle ¹⁷	Up to 50,000 pages
Recommended Monthly Volume ¹⁸	Up to 4,000 pages
Warranty	1-year limited warranty

Replacement Supplies & Optional Accessories:



TN229BK	Standard Yield Toner Cartridge (1,500 pages) ¹⁹
TN229C/M/Y	Standard Yield Toner Cartridge (1,200 pages) ¹⁹
TN229 4PK	4 Pack of Standard Yield Black, Cyan, Magenta, and Yellow Toner Cartridges (approx. 1,500 BK / 1,200 CMY pages) ¹⁹
TN229XLBK	High Yield Toner Cartridge (3,000 pages) ¹⁹
TN229XLC/M/Y	High Yield Toner Cartridge (2,300 pages) ¹⁹
TN229XL 2PK	Twin Pack of High Yield Black Toner Cartridges (approx. 3,000 pages per cartridge) ¹⁹
TN229XLBK	Super High Yield Toner (4,500 pages) ¹⁹
TN229XLC/M/Y	Super High Yield Toner (4,000 pages) ¹⁹
DR229CL	Drum Unit (20,000 pages) ²⁰
BU229CL	Belt Unit (50,000 pages) ²¹
WT229CL	Waste Toner Box (50,000 pages) ²²
LT-310CL	Optional 250-Sheet Capacity Paper Tray ¹⁵

Setup Information:

UPC Code	012502669470
Unit Dimensions / Weight	18.2" (W) x 16.1" (D) x 15.8" (H) / 47.8 lbs.
Carton Dimensions / Weight	23" (W) x 19.6" (D) x 21" (H) / 55 lbs.
Pallet Ti/Hi	4 / 2
Pallet Quantity	8
Country of Origin	Vietnam
Tariff / Harmonized Code	8443.31.0000

Carton Contents:

Brother MFC-L8395CDW, Starter Black Toner Cartridge (3,000 pages)¹⁹, Starter Cyan, Magenta, Yellow Toner Cartridges (1,400 pages)¹⁹, DR229CL Drum Unit (20,000 pgs)²⁰, BU229CL Belt Unit (50,000 pages)²¹, WT229CL Waste Toner Box (50,000 pages)²², AC Power Cord, Telephone Line Cord, Product Safety Guide, Reference Guide, Warranty Card, Quick Setup Guide



Working with you for a better environment

At Brother, our green initiative is simple. We strive to take responsibility, act respectfully and try to make a positive difference to help build a society where sustainable development can be achieved. We call this approach Brother Earth.

COMPATIBLE WITH
WINDOWS



- Based on one sided printing. Change from default setting required.
- From ready mode and standard tray.
- PostScript®3™ compatible.
- Color and monochrome scan speed with all advanced features turned off, Letter at 300dpi.
- Windows only.
- Requires mail server support.
- PDF (up to ver. 1.7), JPEG, XPS files. Secure PDF / Signed PDF scan only.
- Requires an internet connection and an account with desired service.
- Requires connection to a wireless network.
- Requires an internet connection.
- Using ITU-T Test Chart #1 with JBIG coding and standard resolution.
- B&W only. PC Fax Receive not available for Mac users.
- For the latest OS compatibility and to download drivers, visit support.brother.com. Printing or scanning via macOS requires the use of AirPrint. Mac drivers are not provided. For Windows Server: USB connection supports printing and scanning; network connections support printing only.
- May require free download. Compatibility may vary by device and operating system. May require connection to a wireless network.
- Maximum capacity based on using 20 lb. paper.
- Print speed may vary depending on size/type of paper used and paper source.
- Maximum number of printed pages per month can be used to compare designed durability between like Brother products. For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds your print requirements.
- The recommended range of monthly printed pages to achieve the best possible performance and printer life. Printers are intended to handle occasional usage beyond this range with little or no effect. Consistently printing above the recommended print volume, however, may adversely affect the print quality or life of the machine. It is always best to choose a printer with an appropriate recommended print volume to allow for any anticipated increase in printing needs.
- Approximate toner cartridge yield in accordance with ISO/IEC 19798 (letter/A4).
- Approximately 20,000 pages based on 1 page per job and 30,000 pages based on 3 pages per job (letter/A4 single-sided pages). The number of pages may be affected due to a variety of factors including but not limited to media type and media size.
- Approximately 50,000 pages based on 2 pages per job and 60,000 pages based on 3 pages per job (letter/A4 single-sided pages). The number of pages may be affected due to a variety of factors including but not limited to media type and media size.
- Approximate yield is declared in accordance with ISO/IEC 19798 (A4/Letter single-sided pages). The number of pages may be affected due to a variety of factors including but not limited to media type and media size.

©2023 BROTHER INTERNATIONAL CORPORATION • All trademarks and registered trademarks referenced herein are the property of their respective companies. macOS, AirPrint, and the AirPrint logo are registered trademarks of Apple Inc., registered in the U.S. and other countries. iOS is a trademark or registered trademark of Cisco in the U.S. and other countries and is used under license. Android and Google Drive are trademarks of Google LLC. Mopria™ and the Mopria™ Logo are registered and/or unregistered trademarks and service marks of Mopria Alliance, Inc. in the United States and other countries. Unauthorized use is strictly prohibited. Wi-Fi Direct®, the Wi-Fi CERTIFIED™ logo and the Wi-Fi Protected Setup™ Identifier Mark are trademarks of Wi-Fi Alliance®. ENERGY STAR and the ENERGY STAR mark are registered trademarks owned by the U.S. Environmental Protection Agency. Evernote is a trademark of Evernote Corporation and used under a license. All specifications subject to change without notice.