

VG245 - 24" ERGONOMIC IPS DESIGNED FOR SURFACE MONITOR WITH USB-C

Key Features

- Designed for Surface
- Single-Cable Solution
- A More Comfortable Workspace
- USB HUB
- Frameless Design
- Command and Control Made Easy
- Eco-Friendly Packaging and Quick Deployment
- ENERGY STAR and EPEAT Certified
- 3-year Limited Warranty
- Dual Integrated Speakers



24
DISPLAY



IPS
PANEL



1920 x 1080
RESOLUTION



Product Description

Designed for Surface (DfS) products must meet the rigorous standards of Microsoft to ensure optimal compatibility with Microsoft Surface products.* The ViewSonic® VG245 monitor is compatible with all USB-C Surface devices and is ideal for office and home use. USB-C connectivity offers convenient charging power, video and audio over a single cable, and will charge your Surface device without the need for an additional power cable. Along with USB-C, additional connectivity options include HDMI, DisplayPort, VGA, and a USB hub. This 24" monitor also includes an advanced ergonomic design that features height adjustment, pivot, swivel and tilt for maximum comfort and enhanced productivity. This monitor is shipped in eco-friendly biodegradable packaging, along with an easy-to-install quick release stand that makes for simple out-of-the box setup. The quick release stand also includes an integrated client mount and cable management features.

*Microsoft, Microsoft Surface, Designed for Surface are trademarks of the Microsoft group of companies.

Specifications

	More Information
UPC	766907024197
Screen Size	24
Viewable Area (in.)	23.8
Panel Type	IPS
Display Resolution	1920 x 1080
Display Resolution	Full HD (1920x1080)
Static Contrast Ratio	1,000:1
Dynamic Contrast Ratio	50,000,000:1
Light Source	LED
Brightness	250 cd/m2
Colors	16.7M
Color Space Support	8-bit (6 bit + Hi-FRC)
Aspect Ratio	16:9
Response Time (Typical GTG)	5ms
Viewing Angles	178° horizontal, 178° vertical
Backlight Life (Hours)	30,000
Panel Surface	Anti-Glare type, Hard-coating (3H), Haze 25%
Refresh Rate	60Hz
PC Resolution (max)	1920 x 1080
Mac® Resolution (max)	1920 x 1080
USB Type A	3
USB Type B	1
USB Type C	1
VGA	1
HDMI 1.4 In	1
DisplayPort	1
Internal Speakers	2W (x2)
Eco Mode (Conserve)	13.4w
Eco Mode (optimized)	15.9w
Consumption (typical)	19.3w
Consumption (max)	45.1w
Voltage	AC 100-240V (universal), 50-60Hz
Stand-by	0.3w

Power Supply	Internal
Cable Organization	Yes
Kensington Lock Slot	1
Physical Controls	Key 1 (eye), Key 2, Key 3, Key 4, Key 5, Key 6 (power)
On Screen Display	Input Select, Audio Adjust, ViewMode, Color Adjust, Manual Image Adjust, Setup Menu
Temperature	32-104° F (0 - 40° C)
Humidity (non-condensing)	20-90%
VESA Compatible	100 x 100 mm
Frequency Horizontal	VGA: 24 ~ 82 KHz / HDMI 1.4, DisplayPort, & USB Type C: 15 ~ 82 KHz
Frequency Vertical	VGA: 50 ~ 75 Hz / HDMI 1.4, DisplayPort, & USB Type C: 24 ~ 75 Hz
Height Adjust	130 mm / 5.1 in
Swivel	120°
Pivot (Right/Left)	90° / 90°
Tilt (Forward/Back)	5° / 40°
Net (lbs)	13.7
Net Without Stand (lbs)	8.8
Gross (lbs)	20.1
Net (kg)	6.2
Net Without Stand (kg)	4
Gross (kg)	9.1
Packaging (in.)	23.4 " (W) x 15.6 " (H) x 8.3 " (D)
Physical (in.)	21.2 " (W) x 15.99~20.15 " (H) x 8 " (D)
Physical Without Stand (in.)	21.2 " (W) x 12.6 " (H) x 2 " (D)
Packaging (mm)	595 mm (W) x 396 mm (H) x 210 mm (D)
Physical (mm)	539 mm (W) x 406.19~511.9 mm (H) x 202 mm (D)
Physical Without Stand (mm)	539 mm (W) x 320 mm (H) x 52 mm (D)
Regulations	cTUVus, FCC-B, ICES003, Energy Star, EPEAT, MX-CoC, Mexico Energy
Package Contents	LCD Display, Power Cable, HDMI to HDMI Cable, USB Type C cable, USB Type A/B Cable, Quick Start Guide
Recycle/Disposal	Please dispose of in accordance with local, state or federal laws.
Warranty	Three-year limited warranty on parts, labor and backlight

UPC: 766907024197



Contact Sales

ViewSonic.com

888.881.8781

email:

salesinfo@viewsonic.com