

VP275-4K - 27" COLORPRO™ 4K UHD ERGONOMIC DESIGNED FOR SURFACE MONITOR WITH USB C


Key Features

- · Designed for Surface
- Stunning Ultra HD Resolution
- Single-Cable Solution
- A More Comfortable Workspace
- Amazing Color Accuracy
- Pantone Validated Display










IPS **PANEL**



3840 X 2160 **RESOLUTION**



Product **Description**

Designed for Surface (DfS) products must meet the rigorous standards of Microsoft to ensure optimal compatibility with Microsoft Surface products.* The ViewSonic® VP275-4K monitor is compatible with all USB-C Surface devices and is ideal for office and home use. USB-C connectivity offers convenient charging power, video and audio over a single cable, and will charge your Surface device without the need for an additional power cable. Along with USB-C, additional connectivity options include HDMI, DisplayPort, and a USB hub. With Pantone Validation, stunning 4K Ultra HD (3840 X 2160p) resolution and incredible color accuracy, this monitor displays your work with the vivid detail and lifelike color it deserves. This 27" monitor also includes an advanced ergonomic design that features height adjustment, pivot, swivel and tilt for maximum comfort and enhanced productivity. *Microsoft, Microsoft Surface, Designed for Surface are trademarks of the Microsoft group of companies.

Specifications

More Information	
UPC	766907024227
Screen Size	27
Viewable Area (in.)	27
Panel Type	IPS
Display Resolution	3840 x 2160
Display Resolution	4K (3840x2160)
Static Contrast Ratio	1,200:1
Dynamic Contrast Ratio	20,000,000:1
Light Source	LED
Brightness	360 cd/m2
Colors	1.07B
Color Space Support	10 bit (8 bit + FRC)
Aspect Ratio	16:9
Response Time (Typical GTG)	5ms
Viewing Angles	178º horizontal, 178º vertical
Backlight Life (Hours)	30,000
Panel Surface	Anti-Glare type, Hard-coating (3H), Haze 25%
Refresh Rate	60Hz
PC Resolution (max)	3840 X 2160
Mac® Resolution (max)	3840 X 2160
USB Type A	2
USB Type B	1
USB Type C	60W x 1
HDMI 2.0 In	2
DisplayPort	1
Internal Speakers	2W (x2)
Eco Mode (Conserve)	37.5W
Eco Mode (optimized)	39.5W
Consumption (typical)	42W
Consumption (max)	122W
Voltage	AC 100-240V (universal), 50-60Hz
Stand-by	0.3W
Power Supply	Internal

Cable Organization Yes **Kensington Lock Slot** 1 **Physical Controls** Key 1, Key 2, Key 3, Key 4, Key 5, Key 6 (power) Input Select, Audio Adjust, ViewMode, Color Adjust, Manual Image Adjust, Setup Menu **On Screen Display** 32-104º F (0 - 40º C) **Temperature** 20-90% **Humidity (non-condensing) VESA Compatible** 100 x 100 mm **Frequency Horizontal** HDMI 2.0, DisplayPort, USB Type C: 15 \sim 136 KHz HDMI 2.0, DisplayPort, USB Type C: 24 \sim 75 Hz **Frequency Vertical Height Adjust** 130 mm / 5.1 in 60º Swivel Pivot (Right/Left) 90º / 90º 5º / 21º Tilt (Forward/Back) Net (lbs) 16.9 Net Without Stand (lbs) 11.2 Gross (lbs) 22.5 7.7 Net (kg) Net Without Stand (kg) 5.1 Gross (kg) 10.2 29.1 x 18.3 x 8.9 Packaging (in.) Physical (in.) 24.1 x 16.15~21.27 x 8.5 Physical Without Stand (in.) 24.1 x 14.3 x 2.1 740.0 x 465.0 x 225.0 Packaging (mm) Physical (mm) 613.0 x 410.31~540.31 x 215.0 Physical Without Stand (mm) 613.0 x 363.0 x 53.0 cTUVus, FCC-B, ICES003, Energy Star 8.0, EPEAT Silver, CEC, NOM, Mexico Energy Regulations **Package Contents** VP275-4K, Power Cable, HDMI to HDMI Cable, USB Type C cable, USB Type A/B Cable, Quick Start Guide Recycle/Disposal Please dispose of in accordance with local, state or federal laws. Three-year limited warranty on parts, labor and backlight Warranty

UPC: 766907024227







Contact Sales
ViewSonic.com
888.881.8781
email: salesinfo@viewsonic.com