#### **Overview**

#### Style, comfort and audio quality

Built for style with a sleek design that focuses on comfort and reliability. Poly signature audio quality so you know you will sound great. And intuitive and simple features so every user can connect to their preferred device simply and easily.

#### Connect quickly and easily

The Blackwire 3300 Series is completely plug-n-play with USB devices, so users can take calls in the office or on the go. Its robust design delivers reliability you can count on. This is the hassle-free headset you've been looking for.

#### Look good, feel good, sound amazing

Boost your on-the-call confidence with professional-quality audio and a customized fit with a headset that can connect to your devices quickly and easily and is ready to go with you wherever you go.

#### **Features**

#### High-quality audio

Makes collaboration easy with Poly signature audio quality and reliability.

#### Wearing style

Monaural wearing style for those who prefer to leave one ear open.

#### **Headset flexibility**

With professional voice quality and a customized fit, this fully adjustable headset has 180-degree pivoting speakers and a flexible microphone boom.

#### Long-lasting comfort

Supports long-wearing comfort with a plush, padded headband and pillow soft ear cushions.

#### **Connectivity options**

Enhanced connectivity for your devices: USB Type-C<sup>®</sup> cord with tethered USB-A adapter for PC and 3.5 mm for mobile or tablet connectivity.

#### **Optimized for communications platforms**

An IT manager's dream, this headset was created for communication and is optimized and certified to work with top virtual meeting providers.

# Additional specifications

Acoustic protection technology	SoundGuard <sup>[1]</sup>
Audio	Noise and echo reduction; Dynamic EQ optimized
Boom mic length (ft)	0.44 ft
Boom mic length (mm)	135 mm
Boom mic rotation	280°
Button user controls	Call answer/end; Mute; Volume +/-
Cable length	66.5 cm (inline module to headset); 90 cm (USB to inline module); 215 cm (total USB to headset)
Cable length (imperial)	3.85 ft (inline module to headset); 2.95 ft (USB to inline module); 7.05 ft (total USB to headset)
Color	Black
Compatibility	Compatible with PCs via USB/USB Type-C $^{\circ}$ , connects to mobile devices and tablets via 3.5 mm (BW3315/BW3325) and devices that support USB Type-C $^{\circ}$
Compatible Operating Systems	Windows 10; macOS
Connection type	3.5 mm audio; USB Type-A; Wired USB Type-C®
Ear cushions	Artificial leather (surface material)
Headphone type	On-ear (monoaural)
Impedance	32 ohm
Management Software	Plantronics Hub (desktop)
Manufacturer Warranty	Poly standard two-year limited warranty
Microphone bandwidth	100 Hz to 10 kHz
Microphone type	Omnidirectional
Minimum System Requirements	USB Type-A port; 3.5 mm audio; USB Type-C® port
Nominal sound pressure level	118 dB SPL
Sensitivity (microphone)	-38 +/-3 dB
Sensitivity (speaker)	116 dB
Signal-to-noise ratio	>118 dB
Speaker size	14.2 mm
Special features	UC certified
UNSPSC code	43191638
Weight	0.24 lb
Weight	103 g
What's in the box	Headset; User guide; USB Type-C® to USB Type-A adapter

## Services

## Poly Services ★: Recommended

### **Poly Support Services**

3 year Poly+ Blackwire Service	PBLKWIRE312 ★
3 year Partner Poly+ Blackwire Service	PBLKWIRE362

## **Hybrid Work Solutions**

**Audio** ★: Recommended

#### **Audio Accessories**

Poly Blackwire 3200 Leatherette Ear Cushions (2 Pieces)	85S24AA
Poly Blackwire 3200 USB-A Inline Controls	85R03AA
·	AACOACO
Poly Blackwire 3200 USB-C Inline Controls	85R04AA
Poly Blackwire 3300 Case	85R06AA
Poly Blackwire 3310/3320 Foam Ear Cushions (2 Pieces)	85S23AA
Poly Blackwire 3315/3325 Leatherette Ear Cushions (2 Pieces)	85S22AA
Poly Blackwire 5000 Leatherette Ear Cushions (2 Pieces)	85S19AA
Poly Blackwire 5200 USB-A Inline Controls	85Q62AA
Poly Blackwire 5200 USB-C Inline Controls	85Q64AA
Poly Blackwire 5200 Y Training Cable	85S08AA
Poly Blackwire 7225 Case	85Q69AA
Poly Blackwire 8225 Leatherette Ear Cushions (2 Pieces)	783Q9AA
Poly USB-A to USB-C Adapter	85Q48AA
Poly USB-C to USB-A Adapter	85Q49AA

### Disclaimer — Copyright

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (us-en) – Dec 22, 2023 5:05 PM UTC+0000