

Product data sheet

Specifications



APC NetShelter Rack PDU Advanced, Switched, 7.4kW, 1PH, 230V, 32A, 332P6, 40 Outlet

APDU10150SW

Overview

Lead time Usually in Stock

Main

Main Input Voltage 230 V 3 phase

Product or Component Type PDU

PDU Type Switched

Main Output Voltage 230 V

Input Connection Type IEC 60309 32 A 2P + PE

Number of rack unit 0U

Cable length 9.84 ft (3.0 m)

Communication Port Protocol 1000BASE-T
10/100BASE-T

Physical

Color Black

Height 58.66 in (149.0 cm)

Width 2.20 in (5.6 cm)

Depth 2.95 in (7.5 cm)

Net Weight 16.31 lb(US) (7.4 kg)

Mounting Location Side

Mounting preference No preference

Mounting Mode Rack-mounted

Mounting position Vertical

Input

Line Rated Current 32 A

Permissible voltage 200...240 V

Input current limits 32 A

Load Capacity 7400 VA

Input Frequency 50/60 Hz

Output

Number of power socket outlets	20 C13/C15/C19/C21 20C13/C15
--------------------------------	---------------------------------

Conformance

Product Certifications	UKCA TAA compliance
------------------------	------------------------

Standards	CE EN 62368-1
-----------	------------------

Environmental

Ambient air temperature for operation	23...140 °F (-5...60 °C)
---------------------------------------	--------------------------

Relative Humidity	5...95 %
-------------------	----------

Operating altitude	0...10000 ft
--------------------	--------------

Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
-------------------------------------	----------------------------

Storage Relative Humidity	5...95 %
---------------------------	----------

Storage altitude	0...50000 ft (0.00...15240.00 m)
------------------	----------------------------------

Ordering and shipping details

GTIN	731304439660
------	--------------

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Number of Units in Package 1	1
------------------------------	---

Package 1 Height	67.72 in (172 cm)
------------------	-------------------

Package 1 Width	4.57 in (11.6 cm)
-----------------	-------------------

Package 1 Length	8.19 in (20.8 cm)
------------------	-------------------

Package 1 Weight	20.72 lb(US) (9.4 kg)
------------------	-----------------------

Offer Sustainability

REACH Regulation	REACH Declaration
------------------	-----------------------------------

REACH free of SVHC	Yes
--------------------	-----

EU RoHS Directive	Compliant EU RoHS Declaration
-------------------	--

Mercury free	Yes
--------------	-----

China RoHS Regulation	China RoHS declaration
-----------------------	--

RoHS exemption information	Yes
----------------------------	---------------------

WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
------	--

Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------

Recommended replacement(s)