

2MP Pinhole IP Camera

1920x1080, Built-in SD Card Slot



The R2-2MPPINCAM is a 2MP (1920x1080) pinhole camera constructed with a 3.7mm lens and provides HD image quality. This compact model is ideal for covert applications such as ATMs.

FEATURES

- 1/2.8" PROGRESSIVE SCAN CMOS
- 3.7MM FIXED PINHOLE LENS
- 25/30FPS @ 2MP (1920x1080)
- SUPPORTS FACE, HUMAN, VEHICLE DETECTION
- INTELLIGENT ANALYSIS: INTRUSION, LINE CROSSING, LOITERING, WRONG WAY, ILLEGAL PARKING
- WDR, 3D DNR, ROI, HLC, BLC, AISLE MODE
- 2/1 ALARM INPUT/OUTPUT, 1/1AUDIO INPUT/OUTPUT
- BUILT-IN SD CARD SLOT
- WARRANTY (IF APPLICABLE)
- PART #: R2-2MPINCAM
- UPC: 840049308428
- DIMENSIONS: 1.48" x 1.34" x 1.83"
- WEIGHT: 0.40 LB



FOR MORE INFORMATION, CONTACT YOUR ADI SALES PERSON.

CAMERA	
IMAGE SENSOR	1/2.8" PROGRESSIVE SCAN CMOS
MAX. RESOLUTION	1080P (1920x1080)
ELECTRONIC SHUTTER	AUTO/MANUAL, 1/5 ~ 1/20,000S
MIN. ILLUMINATION	COLOR: 0.01 LUX @ (F2.0, AGC ON), B/W: 0.001 LUX @ (F2.0, AGC ON)
WIDE DYNAMIC RANGE	TRUE WDR
LENS	
LENS TYPE	PINHOLE LENS, FIXED-FOCAL
IRIS	FIXED IRIS
FOCAL LENGTH	3.7MM
F NUMBER	F2.0
ANGLE OF VIEW	H: 81.9°, V: 40.8°
VIDEO	
STREAMING CAPABILITY	3 STREAMS
STREAM/FRAME RATE	STREAM1: 1920x1080, 1280x960, 1280x720 @25/30FPS STREAM2: D1, VGA, 640x360, CIF, QVGA @ 25/30FPS STREAM3: VGA, CIF, QVGA @ 25/30FPS
BITRATE CONTROL	CBR/VBR
BIT RATE	STREAM1: 100KBPS ~ 6MBPS STREAM2: 100KBPS ~ 6MBPS STREAM3: 100KBPS ~ 3MBPS
REGION OF INTEREST	OFF/ON (8 ZONE, RECTANGLE)
IMAGE	
IMAGE ADJUSTMENT	BRIGHTNESS, SHARPNESS, CONTRAST, SATURATION
AISLE MODE	SUPPORTED
MIRROR	SUPPORTED

WHITE BALANCE	AUTO
DAY/NIGHT SETTING	AUTO, DAY
NOISE REDUCTION	2D/3D DNR
IMAGE ENHANCEMENT	HLC, BLC, WDR
MOTION DETECTION	SUPPORTED
PRIVACY MASKING	SUPPORTED
AUDIO	
COMPRESSION	G.711, RAW_PCM
BIT RATE	8KBPS, 16KPS, 64KBPS
SMART FUNCTIONS	
MULTI-OBJECT DETECTION	SUPPORTS FACE, HUMAN AND VEHICLE DETECTION
INTELLIGENT ANALYSIS	INTRUSION, SINGLE LINE CROSSING, DOUBLE LINE CROSSING, LOITERING, WRONG WAY SUPPORT ALARM TRIGGERING BY SPECIFIED TARGET TYPES (HUMAN AND VEHICLE)
NETWORK	
PROTOCOLS	IPV4/IPV6, 802.1X, HTTP, HTTPS, TCP/ IP, UDP/IP, RTSP, DHCP, NTP, RTCP/RTP, PPPOE, SMTP, DNS, UPNP, FTP, ARP, SNMP, TLS/SSL
INTERFACE PROTOCOL	ONVIF, SDK, CGI
STREAMIN METHOD	UNICAST
MAX. USER ACCESS	10 USERS
WEB VIEWER	<IE11, CHROME, FIREFOX, MICROSOFT EDGE
LANGUAGE	ENGLISH, CHINESE, POLISH, ITALIAN, PORTUGUESE, SPANISH, RUSSIAN, FRENCH, CZECH, HUNGARIAN. DEFAULT: ENGLISH

**FOR MORE INFORMATION,
CONTACT YOUR ADI SALES PERSON.**

INTERFACE

NETWORK INTERFACE	1 ETHERNET (10/100 BASE-T) RJ45 CONNECTOR
AUDIO INTERFACE	1CH INPUT, 1CH OUTPUT
ALARM INTERFACE	2CH INPUT, 1CH OUTPUT
CVBS INTERFACE	CUSTOMIZABLE
RESET BUTTON	SUPPORTED
SD CARD SLOT	SUPPORTED, UP TO 256GB

ELECTRICAL

POWER SUPPLY	DC12V (-15%+25%)
POWER CONSUMPTION	MAX 3W
OPERATING TEMPERATURE	-30°C - 55°C (-22°F - 131°F)
OPERATING HUMIDITY	LESS THAN 90% RH
INGRESS PROTECTION	N/A
CERTIFICATIONS	CE/FCC
CASING	METAL
DIMENSIONS	37.6 x 34 x 46.5 MM (1.48 x 1.34 x 1.83 INCHES)
NET WEIGHT	180G (0.40 LB)

FOR MORE INFORMATION,
CONTACT YOUR ADI SALES PERSON.