

# Product datasheet

Specifications



## APC Power Cord, IEC C13 to AS/ NZS 3112 (AU) Plug, 250V 10A, 1ft/ 0.31m cord

AP9869

### Overview

Lead Time Usually in Stock

### Main

Main Input Voltage 250 V  
Input Connection Type AS/NZS 3112 Australian  
Cable Length 31 cm  
Number Of Cables 1

### Physical

Colour Black  
Height 14.4 cm  
Width 10.4 cm  
Depth 4.4 cm  
Net Weight 130 g

### Input

Network Frequency 50 Hz +/- 3 Hz  
Plug Standard Australian  
Number Of Input Connectors 1 IEC C13  
Max Line Current 10 A

### Conformance

Product Certifications RCM

### Environmental

Ambient Air Temperature For Operation 0...40 °C  
Operating Altitude 0...3000 m  
Ambient Air Temperature For Storage -15...45 °C  
Storage Altitude 0...15000 m

### Packing Units

Unit Type Of Package 1 PCE  
Number Of Units In Package 1 1

<b>Package 1 Height</b>	14.4 cm
<b>Package 1 Width</b>	10.4 cm
<b>Package 1 Length</b>	4.4 cm
<b>Package 1 Weight</b>	130 g

## Contractual warranty


<b>Warranty</b>	2 years for repair or replacement
-----------------	-----------------------------------

## Sustainability


**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performances. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

[Learn more about Green Premium >](#)

## Well-being performance

 Reach Free Of Svhc

---

 Rohs Exemption Information [Yes](#)

---

**Reach Regulation** [REACH Declaration](#)

---

**Eu Rohs Directive** Compliant  
[EU RoHS Declaration](#)

---

**China Rohs Regulation** [China RoHS declaration](#)  
Pro-active China RoHS declaration (out of China RoHS legal scope)

---