

ProductSheet

## HP OfficeJet Pro 9130b All-in-One Printer (4U555A)



### Manage printing like a Pro.

The professional color inkjet printer for distributed offices/hybrid workforce from the World's #1 Printer Company, paired with our best technology to help manage it all. This streamlines work into any network with extra performance features.[1,2]



#### **Deploy. Integrate. Customize with ease.**

Easily deploy, integrate, and set up your fleet of printers across multiple locations.

#### **Empower your business with a productivity powerhouse**

Always ready for high volumes, get an HP OfficeJet Pro printer equipped with two 250-page input trays.

#### **Our best technology to help manage it all[2]**

Stay connected with our most reliable Wi-Fi® - dual-band, self-healing - that automatically reconnects.[2]

## Specifications

<b>Print Resolution Technologies</b>	HP Thermal Inkjet
<b>Print quality black (best)</b>	1200 x 1200 rendered dpi
<b>Print quality color (best)</b>	Up to 4800 x 1200 optimized dpi on HP Advance Photo Paper 1200 x 1200 dpi input
<b>Print speed black (ISO, A4)</b>	Up to 25 ppm
<b>Print speed black (ISO, letter)</b>	Up to 25 ppm
<b>Print Speed Color (ISO)</b>	Up to 19 ppm
<b>Print speed color (ISO)</b>	Up to 19 ppm
<b>Print speed</b>	Print speed up to 25 ppm (black) and 19 ppm (color)
<b>Functions</b>	Print, copy, scan, fax
<b>Duplex printing</b>	Automatic
<b>Duty cycle (monthly, A4)</b>	Up to 30,000 pages
<b>Duty cycle (monthly, letter)</b>	Up to 30,000 pages <sup>[7]</sup>
<b>Printer smart software features</b>	Orientation: Portrait/Landscape/Rotate by 180 degrees; Print On Both Sides; None, Flip on Long Edge, Flip on Short Edge; Pages per sheet: 1 page per sheet/2 pages per sheet/4 pages per sheet/6 pages per sheet/9 pages per sheet/16 pages per sheet; Print Quality: HP Standard/Quick Draft/Premium/Detailed; RGB color: Printer Default/Office (sRGB)/Photo (sRGB)/Device RGB/Adobe RGB/Vivid (sRGB)/Custom RGB Printing Shortcuts; Factory Defaults; EcoSMART settings; Labels; CardStock/Heavy; Transparencies; Booklet Printing; General Everyday Printing; Page order: Front to Back/Back to Front/; Booklet Layout: Off/Left binding/Right binding; Print page borders; Special pages: Front cover/Back Cover/Print pages on different paper/Insert Blank Pages Resizing Options: Actual size/Print document on:/Scale manually Watermarks: None/Confidential/Draft/Sample/Custom Copies: Up to 99; Collate; Reverse page order; Print all text as black; Control Panel Shortcuts; HP EasyColor: Off/Conservative/Automatic Wireless
<b>Copier smart software features</b>	Duplex copy, ID Copy, Resolution adjustment, Reduce / enlarge settings, Infinity glass for easy document removal.
<b>Scanner advanced features</b>	Single pass two sided scanning with Auto Document Feeder
<b>Energy savings feature technology</b>	HP Auto-On/Auto-Off Technology
<b>Replacement cartridges</b>	HP 936 Black Original Ink Cartridge (~1,250 pages) 4S6V2LN, HP 936 Cyan Original Ink Cartridge (~800 pages) 4S6U9LN; HP 936 Magenta Original Ink Cartridge (~800 pages) 4S6V0LN; HP 936 Yellow Original Ink Cartridge (~800 pages) 4S6V1LN; HP EvoMore planned to be available April 2024: HP 936e EvoMore Black Original Ink Cartridge (~2,500 pages) 4S6V6LN; HP 936e EvoMore Cyan Original Ink Cartridge (~1,650 pages) 4S6V3LN; HP 936e EvoMore Magenta Original Ink Cartridge (~1,650 pages) 4S6V4LN; HP 936e EvoMore Yellow Original Ink Cartridge (~1,650 pages) 4S6V5LN. Actual yield varies considerably based on content of printed pages and other factors. HP 937 Black Original Ink Cartridge (~1,250 pages) 4S6W5N; HP 937 Cyan Original Ink Cartridge (~800 pages) 4S6W2N; HP 937 Magenta Original Ink Cartridge (~800 pages) 4S6W3N; HP 937 Yellow Original Ink Cartridge (~800 pages) 4S6W4N. HP EvoMore planned to be available April 2024: HP 937e EvoMore Black Original Ink Cartridge (~2,500 pages) 4S6W9N; HP 937e EvoMore Cyan Original Ink Cartridge (~1,650 pages) 4S6W6N; HP 937e EvoMore Magenta Original Ink Cartridge (~1,650 pages) 4S6W7N; HP 937e EvoMore Yellow Original Ink Cartridge (~1,650 pages) 4S6W8N. Actual yield varies considerably based on content of printed pages and other factors. HP 938 Black Original Ink Cartridge (~1,250 pages) 4S6X8P; HP 938 Cyan Original Ink Cartridge (~800 pages) 4S6X5P; HP 938 Magenta Original Ink Cartridge (~800 pages) 4S6X6P; HP 938 Yellow Original Ink Cartridge (~800 pages) 4S6X7P. HP EvoMore planned to be available April 2024: HP 938e EvoMore Black Original Ink Cartridge (~2,500 pages) 4S6Y2P; HP 938e EvoMore Cyan Original Ink Cartridge (~1,650 pages) 4S6X9P; HP 938e EvoMore Magenta Original Ink Cartridge (~1,650 pages) 4S6Y0P; HP 938e EvoMore Yellow Original Ink Cartridge (~1,650 pages) 4S6Y1P. Actual yield varies considerably based on content of printed pages and other factors. For details, see <a href="https://www.hp.com/go/learnaboutsupplies">https://www.hp.com/go/learnaboutsupplies</a>
<b>Connectivity, standard</b>	1 Ethernet; 1 Hi-Speed USB 2.0 (device); 1 Hi-Speed USB 2.0 (host); 1 Wi-Fi 802.11 a/b/g/n/ac (dual band); 2 RJ-11 Fax/Modem port/phone line
<b>Modem</b>	Synaptics Troy modem; Data rate up to 33.6 kbps
<b>Network capabilities</b>	Yes, via built-in Ethernet; Wireless 802.11 a/b/g/n/ac
<b>Wireless capability</b>	Yes, with built-in dual-band Wi-Fi 802.11 a/b/g/n/ac and a self-heal solution
<b>Mobile printing capability</b>	Apple AirPrint™; Wi-Fi® Direct Printing; Mopria™ certified
<b>Network protocols, supported</b>	Supported Network Protocols configurations (IPv4, IPv6); DHCPv4, DHCPv6; DHCP options: 81/RFC4702/RFC4704, 12-Hostname; 44; SMTP client; LLMNR; Bonjour/mdNS; LP/ APIPA (Auto IP); NetBIOS/WINS; LPR/LPD; Port9100; DNS Resolver; SNMPv1/v2; Web Services Discovery; Web Services Print; Syslog; Firewall; SSL/TLS (HTTPS); Password-protected network Embedded Web server; Enable/disable network ports & device features, 802.1x wireless authentication (EAP-TLS, LEAP, and PEAP) & 802.1 Wired
<b>Software included</b>	HP Printer Software

<b>Compatible Operating Systems</b>	Windows 11; Windows 10; Windows Server; macOS 11 Big Sur; macOS 12 Monterey; macOS 13 Ventura; Linux; Chrome OS ( <i>Windows Server 2016 64-bit, Windows Server 2019 64-bit, Windows Server 2022 64-bit, linux (for more information see <a href="http://developers.hp.com/hp-linux-imaging-and-printing">http://developers.hp.com/hp-linux-imaging-and-printing</a>)</i> )
<b>Technical features</b>	Borderless Printing; Automatic two-sided printing; Wireless; Wireless Direct; AirPrint; Touchscreen; ADF
<b>Sustainable impact specifications</b>	Recyclable through HP Planet Partners; Forest First product
<b>Energy star certified</b>	Yes
<b>Ecolabels</b>	IT ECO Declaration; EPEAT® registered
<b>Copy speed black (best, A4)</b>	Up to 5 cpm
<b>Copy speed black (best, letter)</b>	Up to 5 cpm
<b>Copy speed color (best, A4)</b>	Up to 4 cpm
<b>Copy speed color (best, letter)</b>	Up to 4 cpm
<b>Digital sending standard features</b>	Scan-to E-mail; Fax Archive to E-mail
<b>Fax Resolution Black (best)</b>	300 x 300 dpi
<b>Faxing</b>	Yes, color
<b>Scan speed (normal, A4)</b>	Up to 18 ipm (200 ppi, b&w); Up to 18 ipm (200 ppi, color)
<b>Scan speed (normal, letter)</b>	Up to 18 ipm (200 ppi, b&w); Up to 18 ipm (200 ppi, color)
<b>Scan file format</b>	Scan File Type supported by Software: Bitmap (.bmp), JPEG (.jpg), PDF (.pdf), PNG (.png), Rich Text (.rtf), Searchable PDF (.pdf), Text (.txt), TIFF (.tif)
<b>Scan input modes</b>	Front-panel scan, copy, fax, or from software
<b>Scan technology</b>	Contact Image Sensor (CIS)
<b>Scanner type</b>	Flatbed, ADF
<b>Display</b>	4.3" (10.92cm) touchscreen control panel with CGD (color graphic display)
<b>Minimum dimensions (W x D x H)</b>	437 x 396.3 x 318.3 mm (Minimum Storage Mode) ( <i>Dimensions vary as per configuration</i> )
<b>Minimum dimensions (W x D x H)</b>	17.20 x 15.60 x 12.53 in (Minimum Storage Mode) ( <i>With built-in duplexer and second 250-sheet paper tray installed</i> )
<b>Weight</b>	~11.84 kg ( <i>Weight varies as per configuration</i> )
<b>Weight</b>	~26.10 lb ( <i>Weight varies as per configuration</i> )
<b>Power consumption</b>	5.58 watts (ready), 1.22 watts (sleep), 0.14 watts (manual-off) <sup>[3]</sup> ( <i>Power measurements are based on ENERGY STAR® OM test procedure with 230 VAC, 50 Hz input.</i> )
<b>Power supply type</b>	Internal (Built-in) Universal Power Supply
<b>What's in the box</b>	NA: HP OfficeJet Pro 9130b AiO Printer; HP 936 Setup Black Ink Cartridge; HP 936 Setup Cyan Ink Cartridge; HP 936 Setup Magenta Ink Cartridge; HP 936 Setup Yellow Ink Cartridge; Regulatory Flyer; Ink Caution Flyer; Power Cord; Setup Poster; Reference Guide [For more information about fill and yield, see <a href="http://www.hp.com/go/learnaboutsupplies">http://www.hp.com/go/learnaboutsupplies</a> ]; EU / AP Developed Market: HP OfficeJet Pro 9130b AiO Printer; HP 937 Setup Black Ink Cartridge; HP 937 Setup Cyan Ink Cartridge; HP 937 Setup Magenta Ink Cartridge; HP 937 Setup Yellow Ink Cartridge; Regulatory Flyer; Ink Caution Flyer; Power Cord; Setup Poster; Reference Guide [For more information about fill and yield, see <a href="http://www.hp.com/go/learnaboutsupplies">http://www.hp.com/go/learnaboutsupplies</a> ]; LAR / AP Emerging Market: HP OfficeJet Pro 9130b AiO Printer; HP 938 Setup Black Ink Cartridge; HP 938 Setup Cyan Ink Cartridge; HP 938 Setup Magenta Ink Cartridge; HP 938 Setup Yellow Ink Cartridge; Regulatory Flyer; Ink Caution Flyer; Power Cord; Setup Poster; Reference Guide [For more information about fill and yield, see <a href="http://www.hp.com/go/learnaboutsupplies">http://www.hp.com/go/learnaboutsupplies</a> ]
<b>Manufacturer Warranty</b>	One-year limited warranty. For more information please visit us at <a href="http://support.hp.com">http://support.hp.com</a> [8]

## Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

## Messaging Footnotes

[1] Based on 2022 Q4 shipments in the IDC Worldwide Quarterly Hardcopy Peripherals Tracker®, 2022 Q4 Release. Includes shipments of all printing devices (inkjet printers, laser printers, copiers and multifunction devices, including production units).

[2] HP OfficeJet Pro 9100b printer series has dual-band, self-healing Wi-Fi, HP Wolf Pro Security and HP Web Jetadmin, HP's best technologies to seamlessly and securely support your IT business needs. Internet access required and must be purchased separately. Wireless operations are compatible with 2.4 GHz and 5.0 GHz operations only. Learn more at [www.hp.com/go/mobileprinting](http://www.hp.com/go/mobileprinting). HP Security is now HP Wolf Security. Security features vary by platform, please see product data sheet for details.

## Technical Specifications Footnotes

[3] Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty.

[7] HP recommends that the number of printed pages per month be within the stated range for optimum device performance, based on factors including supplies replacement

---

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

