

# Product data sheet

Specifications



APC Back-UPS Pro for Gaming, 1500VA/900W, Tower, 120V, 10x NEMA 5-15R outlets, RGB Lights, Pure Sine Wave, Midnight (Black)

BGM1500B-US

## Overview

Lead time Usually in Stock

## Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Kw Rating	900 W
Rated power in VA	1500 VA
Product or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	NEMA
output connection type	6 NEMA 5-15R
Cable length	6 ft (1.8 m)
Battery Type	Lead-Acid battery

## Batteries & Runtime

Efficiency	<a href="#">View Efficiency Graph</a>
Included Battery Modules	0
Typical recharge time	16 h
Replacement battery	<a href="#">APCRBC163</a>

## General

Provided equipment	Coaxial cable USB cable User Guide in Japanese
product web sub-family	Gaming performance

## Physical

color	Black
Height	11.5 in (291 mm)
Width	4.1 in (105 mm)
Depth	16.06 in (408 mm)
Net Weight	25.4 lb(US) (11.5 kg)
Mounting preference	No preference

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Input

Input Frequency	60 Hz +/- 3 Hz
Efficiency at full load	88...147 V

## Output

Max Configurable Power (Watts)	900 W
Output Frequency (sync to mains)	60 Hz +/- 3 Hz sync to mains
Topology	Line Interactive
Waveform Type	Sine wave
Maximum configurable power in VA	1500 VA

## Conformance

Product Certifications	ENERGY STAR V2.0 (USA) TUV C-US certified
Equipment protection policy	Lifetime : \$500000

## Environmental

Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %

## Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
-------	--

## Surge Protection and Filtering

Surge energy rating	1080 J
Data line protection	Coaxial cable for CATV/SATV/modem/audio-video

## Ordering and shipping details

GTIN	731304624158
Country of origin	VN

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.1 in (15.5 cm)
Package 1 Width	14.0 in (35.5 cm)
Package 1 Length	18.9 in (48 cm)
Package 1 Weight	32.0 lb(US) (14.5 kg)

## Contractual warranty

Warranty	3 year repair or replace
----------	--------------------------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

## Environmental Certifications

 Energy Star® ENERGY STAR UPS V2.0 (USA)

## Certifications & Standards

**Reach Regulation** [REACH Declaration](#)

**Eu RoHS Directive** Pro-active compliance (Product out of EU RoHS legal scope)

**China RoHS Regulation** [China RoHS declaration](#)  
Product out of China RoHS scope. Substance declaration for your information.

**Environmental Disclosure** [Product Environmental Profile](#)

**Circularity Profile** [End of Life Information](#)