



SPECIFICATIONS

Panel Size	27" (69 cm)
Active Display Area (mm)	596.736(H) x 335.664(V)
Curvature	Flat
Panel Type	Ultra Rapid IPS
Panel Resolution	1920 x 1080 (FHD)
Pixel Pitch (H x V)	0.3108(H)x0.3108(V)
Aspect Ratio	16:9
Brightness (nits)	300
Contrast Ratio	1000:1
DCR	100000000:1
Signal Frequency	54~203.7 KHz(H) / 48~180 Hz(V)
ACTIVATED RANGE	48~180Hz
Refresh Rate	180Hz
Response time	1ms (GtG)
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive-Sync
HDR Support	N/A
Video ports	1x Display Port (1.2a) 2x HDMI™ (2.0b)
Audio ports	1x Headphone out
Viewing Angle	178° (H) / 178° (V)
Adobe RGB / DCI-P3 / sRGB	80%/76%/96%
Surface Treatment	Anti-glare
Display Colors	16.7M
Power Type	External Adaptor 20V 2.25A
Power Input	100~240V, 50/60Hz
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Swivel)	N/A
Adjustment (Pivot)	N/A
Adjustment (Height)	N/A
Kensington Lock	Yes
Dimension (W x D x H)	614 x 229 x 456 mm 614 x 45 x 369 mm (without stand)
Carton Dimension (W X D X H)	WW carton: 683 x 157 x 463 mm Outer: 698 x 172 x 488 mm
Frameless Design	Yes
PIP / PBP Function	N/A
VESA Mounting	100 x 100 mm

FEATURES



Ultra Rapid IPS

Equipped with an Oxide panel to provide better picture quality with fast response time.





Experience smooth gaming with a blazing fast 180Hz refresh rate, that gives you the upperhand in fast moving games.



1ms Fast Response Time

Eliminate screen tearing and choppy frame rates with 1ms response time.



Console Mode - FHD only

Best solution for console users: FHD@120Hz



Night Vision

See every detail clearly in the dark, helping you find and attack enemies before they notice.



Wide Color Gamut

wide Color Game colors and details will look more realistic and refined, to | Gamut push game immersion to its limits.



MONITORS **G2712F**

ALL ABOUT GAMING

Weight (NW / GW)	4.2 kg / 6.1 kg 3.4 kg (without stand)
Note	Display Port: 1920 x 1080 (Up to 180Hz) HDMI™: 1920 x 1080 (Up to 180Hz)
	Adobe RGB, DCI-P3 and sRGB follow CIE1976 Standard

CONNECTIONS



© 2023 Micro-Star Int'l Co.Ltd. MSI is a registered trademark of Micro-Star Int'l Co.Ltd. All rights reserved.

- 1. 5-way joystick navigator
- 2. DC jack
- 3. 2 x HDMI[™] (2.0b)
- 4. 1 x Display Port (1.2a)
- 5. Headphone out
- 6. Kensington lock