

PERFORMANCE

Processor

Intel® N100 (4C / 4T, 0.8 / 3.4GHz, 6MB)

Graphics

Integrated Intel® UHD Graphics

Chipset

Intel® SoC Platform

Memory

8GB Soldered LPDDR5-4800

Memory Slots

Memory soldered to systemboard, no slots

Max Memory

8GB soldered memory, not upgradable

Storage

64GB eMMC 5.1

Storage Support

64GB eMMC 5.1 on systemboard

Storage Slot

eMMC on systemboard, no slots

Card Reader

No card reader

Audio Chip

High Definition (HD) Audio

Speakers

Stereo speakers, 2W x2, optimized with Waves MaxxAudio®

Camera

HD 720p with Privacy Shutter

Microphone

Mono

Battery

Integrated 47Wh

Power Adapter

65W USB-C® (2-pin)

DESIGN

Display^[1]

11.6" HD (1366x768) IPS 250nits Anti-glare 60Hz, 50% NTSC, Touch

Touchscreen

On-cell, 10-point Multi-touch

Keyboard

Non-backlit, English

Touchpad

Buttonless Mylar® surface multi-touch touchpad, 60.5 x 104 mm (2.38 x 4.09 inches)

Case Color

Graphite Grey

Surface Treatment

Texture

Case Material

PC-ABS (Top), PC-ABS (Bottom)

Pen

No Support

Dimensions (WxDxH)^[2]

287 x 204.6 x 18.6 mm (11.3 x 8.1 x 0.73 inches)

Weight^[3]

Around 1.23 kg (2.71 lbs)

SOFTWARE

Operating System

ChromeOS

Bundled Software

None

CONNECTIVITY

Ethernet

No Onboard Ethernet

WLAN + Bluetooth®

Intel® Wi-Fi® 6 AX203, 11ax 2x2 + BT5.1

WWAN

None

SIM Card

None

Standard Ports

- 2x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-C® (USB 10Gbps / USB 3.2 Gen 2), with PD and DisplayPort™
- 1x HDMI® 1.4
- 1x Headphone / microphone combo jack (3.5mm)

SECURITY & PRIVACY

Security Chip

Google Security Chip H1

Fingerprint Reader

None

Physical Locks

Kensington® Nano Security Slot™

Other Security

Camera privacy shutter

SERVICE

Base Warranty

1-year, Mail-in

Included Upgrade

None

ACCESSORIES

Bundled Accessories^[4]

None

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 8.0
- EPEAT™ Gold Registered
- ErP Lot 6
- ErP Lot 26
- RoHS compliant
- TCO Certified 9.0

Other Certifications

ASTM F963 test passed

Mil-Spec Test

MIL-STD-810H military test passed

MODEL

TopSeller	: Yes	Announce Date	: 2024-02-02
EAN / UPC / JAN	: 197531525253	End of Support	: N/A



intel

Product image is a sample, it may not match the real color of this model

Note:

[1] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

[2] The system dimensions may vary depending on.....

· Lenovo reserves the right to change specifications without notice.
· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please link to

<https://psref.lenovo.com/Detail/2443?M=83G80001US>

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



ThinkPad Hybrid USB-C with USB-A Dock (American Standard Plug Type B)

40AF0135US

- The ThinkPad Hybrid USB-C with USB-A dock is a productivity solution for any USB-C or USB-A laptop, including non-Lenovo laptops from Dell, HP, and Apple, providing power, display, and port expansion in any m...

Recommended Services

BETTER	3Y Premium Care with Onsite upgrade from 1Y Courier/Carry-in (5WS0U55751)
GOOD	3Y Courier/Carry-in upgrade from 1Y Courier/Carry-in (5WS0Q81869)

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>



PSREF
Product Specifications
Reference