



## SPECIFICATIONS

Panel Size	27" (69 cm)
Active Display Area (mm)	596.736(H) x 335.664(V)
Curvature	Flat
Panel Type	Rapid IPS
Panel Resolution	2560 x 1440 (WQHD)
Pixel Pitch (H x V)	0.2331(H) x 0.2331(V)
Aspect Ratio	16:9
Brightness (nits)	400 (Typ.)
Contrast Ratio	1000:1 (Typ.)
DCR	100000000:1
Signal Frequency	64.56~266.4 KHz(H) / 48~180 Hz(V)
ACTIVATED RANGE	48~180Hz
Refresh Rate	180Hz
Response time	1ms (GTG)
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive-Sync
HDR Support	VESA DisplayHDR 400
Video ports	1 x DisplayPort (1.4a) 2 x HDMI™ (2.0b)
USB ports	N/A
Audio ports	1 x Headphone Out
Viewing Angle	178° (H) / 178° (V)
Adobe RGB / DCI-P3 / sRGB	93% / 95% / 123%
Surface Treatment	Anti-glare
Display Colors	1.07B , 10 bits (8 bits + FRC)
Power Type	External Adaptor 19V 2.58A
Power Input	100 ~ 240V, 50/60Hz
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Swivel)	-45° ~ 45°
Adjustment (Pivot)	0 ~ 130mm
Adjustment (Height)	-90° ~ 90°
Kensington Lock	Yes
Dimension (W x D x H)	TBD
Frameless Design	Yes
PIP / PBP Function	Yes
VESA Mounting	75x 75 mm
Weight (NW / GW)	TBD

## FEATURES

**Rapid IPS**  
Provides 1ms GTG fast response time, optimizes screen colors and brightness.

**180Hz High Refresh Rate**  
Experience smooth gaming with a blazing fast 180Hz refresh rate, that gives you the upperhand in fast moving games.

**1ms Fast Response Time**  
Eliminate screen tearing and choppy frame rates with 1ms response time.

**Adjustable Stand**  
Through adjustments of tilting, lowering and raising, and swiveling, easily change the position of the monitor for maximum ergonomics and optimum viewing experiences.

**Wide Color Gamut**  
Game colors and details will look more realistic and refined, to push game immersion to its limits.

**VESA Certified DisplayHDR 400**

Provide eye-catching detail through contrast and shadows adjustment.

**Less Blue Light PRO**

Use a hardware solution to reduce the light emission in the blue-violet region of the blue light spectrum (wavelength 415 to 455 nm).

**Note**

Display Port: 2560x1440 (Up to 180Hz)  
HDMI™: 2560x1440 (Up to 144Hz)

\*Adobe RGB, DCI-P3 and sRGB follow CIE1976 Standard

## CONNECTIONS



1. 5-Way Joystick Navigator
2. DC Jack
3. Earphone Out
4. 2 x HDMI™ (2.0b)
5. 1 x DisplayPort (1.4a)
6. Kensington Lock