



# HP All-in-One Desktop 22-dg0140 (9U9S0AA)

## Overview

### A powerful, reliable all-in-one desktop PC for everyone

Meet the HP 21.45" All-in-One Desktop PC—your reliable and affordable everyday computing partner. Shop, stream, and connect confidently, with dependable technology, next-level power, and rock-solid performance. Enjoy a stunning display, crisp audio, and sleek design, at an exceptional value. Take on today with tech built for tomorrow.



### Power your modern household

Multitask with ease thanks to fast processing power, tons of ports, and ample storage for photos and videos.



### Chill out with immersive entertainment experience

Relax with FHD[1] visuals on a wide screen[2], with vibrant colors, high contrast[3], and speakers tuned by DTS Audio.



### Be seen, be heard, on your terms

Stand out with advanced video and AI-noise reduction, plus control your privacy with a manual camera shutter.



### Built with our shared future in mind

Contains recycled metals[4] and plastics[5,6], and is EPEAT® Gold[7] and ENERGY STAR® Certified.

# Features



## Get a fresh perspective

From a rejuvenated Start menu, to new ways to connect to your favorite people, news, games, and content—Windows 11 is the place to think, express, and create in a natural way.<sup>[8]</sup>



## Anti-glare panel

Enjoy the sun and your favorite content with this anti-glare panel. Non-reflective and low gloss means you'll get less glare while you're outside.



## Sustainable design

Because little things make a big difference, this product includes sustainable materials like ocean-bound plastic and post-consumer recycled plastic in the design.<sup>[10]</sup>



## Full HD display

Sit back and enjoy crystal-clear visuals and images with the vibrant quality of 2 million pixels. The 1920 x 1080 resolution gives all your digital content a new dimension.<sup>[1]</sup>

## Flicker-free

Using DC Dimming technology that controls brightness by adjusting direct current rather than cycling the backlight, we can eliminate screen flickering for more comfortable viewing.<sup>[9]</sup>



## McAfee Online Protection 30-day trial

Secure your device with award winning antivirus and online protection. Free trial includes secure VPN for privacy and data protection when browsing on public Wi-Fi<sup>[11]</sup>

---

[1] Full high-definition (FHD) content is required to view FHD images.

[2] Percent of active and nonactive viewing area to bezel area including speaker.

[3] All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

[4] Recycled metal is expressed as a percentage of the total weight of the metal according to ISO 14021 definitions for metal parts over 25 grams.

[5] Percentage of post-consumer recycled plastic varies by product. Recycled plastic content percentage is based on the definition set in the IEEE 1680.1-2018 standard.

[6] Percentage of ocean-bound plastic contained in each component varies by product.

[7] Based on U.S. EPEAT® registration according to IEEE 1680.1-2018 EPEAT®. EPEAT® status varies by country. Visit [www.epeat.net](http://www.epeat.net) for more information.

[8] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows is automatically updated and enabled. High speed internet and Microsoft account required. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>.

[9] The flicker-free capability eliminates screen flickering through integrating DC-dimming LED backlights.

[10] Percentage of ocean-bound plastic and post-consumer recycled plastic varies by product. Recycled plastic content percentage is based on the definition set in the IEEE 1680.1-2018

*standard.*

*[11] Internet access required and not included. McAfee is pre-installed on your PC and an account is required for activation. Subscription renewal required after trial period. VPN feature is not available in India, China, Syria or North Korea. McAfee is not compatible with Windows 11 in S mode. You'll need to permanently switch out of S mode. There's no charge to switch out of S mode, but you won't be able to turn it back on.*

## Specifications

<b>Form factor</b>	All-in-One
<b>Operating system</b>	Windows 11 Home
<b>Product color</b>	Cashmere White
<b>Processor family</b>	Intel® Pentium® processor
<b>Processor</b>	Intel® Processor N200 (up to 3.7 GHz with Intel® Turbo Boost Technology, 6 MB L3 cache, 4 cores, 4 threads) <sup>[6,7]</sup>
<b>Memory</b>	8 GB DDR5-4800 MHz RAM (1 x 8 GB)
<b>Memory Slots</b>	2 SODIMM
<b>Internal Storage</b>	512 GB PCIe® NVMe™ M.2 SSD
<b>Product design</b>	Bare resine
<b>Graphics</b>	Integrated
<b>Graphics (integrated)</b>	Intel® UHD Graphics
<b>Display</b>	54.5 cm (21.5") diagonal, FHD (1920 x 1080), VA, anti-glare, 250 nits, 99% sRGB
<b>Display</b>	21.5" diagonal, FHD (1920 x 1080), VA, anti-glare, 250 nits, 99% sRGB
<b>Audio</b>	Dual 2 W speakers
<b>Minimum dimensions (W x D x H)</b>	49.35 x 16.99 x 38.27 cm
<b>Minimum dimensions (W x D x H)</b>	19.43 x 6.69 x 15.07 in
<b>Weight</b>	4.17 kg
<b>Weight</b>	9.19 lb
<b>Keyboard</b>	HP 510SP White Wireless Keyboard and Mouse Combo
<b>Camera</b>	HP True Vision 720p HD privacy camera with temporal noise reduction and integrated dual array digital microphones
<b>Video connectors</b>	1 HDMI-out 1.4
<b>Ports</b>	1 USB Type-C® 5Gbps signaling rate; 2 USB Type-A 5Gbps signaling rate; 2 USB 2.0 Type-A; 1 headphone/microphone combo; 1 RJ-45
<b>Expansion slots</b>	2 M.2 (1 for SSD, 1 for WLAN)
<b>Package dimensions (W x D x H)</b>	59.6 x 15.5 x 39.8 cm
<b>Package weight</b>	7.52 kg
<b>Network interface</b>	Integrated 10/100/1000 GbE LAN
<b>Wireless</b>	Realtek Wi-Fi 6 (1x1) and Bluetooth® 5.3 wireless card <sup>[13]</sup>
<b>Power supply type</b>	65 W Smart AC power adapter
<b>Ecolabels</b>	EPEAT® registered
<b>Energy star certified</b>	ENERGY STAR® certified

<b>Sustainable impact specifications</b>	30% post-consumer recycled plastic; Ocean-bound plastic; 25% recycled metal
<b>Software included</b>	McAfee Online Protection 30-day trial
<b>Software - Productivity &amp; finance</b>	1 month trial for new Microsoft 365 customers <sup>[24]</sup>
<b>Cloud service</b>	25 GB Dropbox storage for 12 months <sup>[1]</sup>
<b>UPC number</b>	198122241989

## Additional specifications

<b>Additional information about HP</b>	<a href="http://www.hp.com">http://www.hp.com</a>
<b>Bluetooth version</b>	Bluetooth® 5.3
<b>Camera brand</b>	HP True Vision
<b>Camera microphone</b>	integrated dual array digital microphones
<b>Camera resolution (vertical)</b>	720p
<b>Camera resolution standard</b>	HD
<b>Color gamut</b>	99% sRGB
<b>Display</b>	21.5" diagonal FHD display
<b>Display</b>	54.5 cm (21.5") diagonal FHD
<b>Display bezel</b>	three-sided micro-edge
<b>Display brightness</b>	250
<b>Display brightness uom</b>	nits
<b>Display panel technology</b>	VA
<b>Display resolution (pixels)</b>	1920 x 1080
<b>Display resolution standard</b>	FHD
<b>Display size (diagonal) uom</b>	"
<b>Display size (diagonal, imperial)</b>	21.5
<b>Display size (diagonal, metric)</b>	54.5
<b>Display size (diagonal, metric) uom</b>	cm
<b>Flicker-free</b>	Yes <sup>[45]</sup>
<b>HDMI version</b>	1.4
<b>HDMI –out</b>	1
<b>I/O Port location</b>	Rear
<b>Memory and storage</b>	8 GB memory; 512 GB SSD storage
<b>Memory layout (slots &amp; size)</b>	1 x 8 GB
<b>Memory module type</b>	SODIMM
<b>Memory size</b>	8
<b>Memory size uom</b>	GB
<b>Memory speed</b>	4800
<b>Memory speed uom</b>	MHz
<b>Memory type</b>	DDR5
<b>Number of memory slots</b>	1

<b>Package dimensions (W x D x H)</b>	23.54 x 6.1 x 15.66 in
<b>Package weight</b>	16.56 lb
<b>Processor Brand</b>	Intel®
<b>Processor cache</b>	6 MB L3
<b>Processor core</b>	4
<b>Processor family</b>	Pentium®
<b>Processor frequency technology</b>	Intel® Turbo Boost Technology
<b>Processor maximum frequency</b>	3.7
<b>Processor maximum frequency uom</b>	GHz
<b>Processor model</b>	N200
<b>Processor threads</b>	4
<b>Product brand name</b>	HP
<b>Product short name specifications</b>	HP All-in-One Desktop 22-dg0140, 21.5", Intel® Pentium®, 8GB RAM, 512GB SSD
<b>Screen-to-body Ratio (with speakers) footnote number</b>	[5]
<b>Screen-to-body ratio (with speakers)</b>	88%
<b>Screen-to-body ratio (without speakers)</b>	98.88% <sup>[4]</sup>
<b>Storage capacity</b>	512
<b>Storage capacity uom 01</b>	GB
<b>Storage form factor 01</b>	M.2
<b>Storage interface 01</b>	PCIe®
<b>Storage interface protocol 01</b>	NVMe™
<b>Storage type</b>	SSD
<b>Storage type 01</b>	SSD
<b>Touchscreen</b>	No
<b>UNSPSC code</b>	43211507
<b>USB Type-A</b>	4
<b>USB Type-C</b>	1
<b>Wireless antenna</b>	1x1
<b>Wireless standard</b>	Wi-Fi 6
<b>Wireless supplier</b>	Realtek

---

[1] 25 GB of free Dropbox storage for 12 months from date of registration. For complete details and terms of use, including cancellation policies, visit the Dropbox website at

*<https://www.dropbox.com/help/space/hp-promotion>. Internet service required and not included.*

*[4] Percent of active and nonactive viewing area to bezel area excluding speaker.*

*[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.*

*[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.*

*[13] Wireless access point and internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 6 (802.11ax) is backwards compatible with prior 802.11 specs. The specifications for Wi-Fi 6 are draft and are not final. If the final specifications differ from the draft specifications, it may affect the ability of the notebook to communicate with other Wi-Fi 6 devices. Only available in countries where 802.11ax is supported.*

*[24] Must activate within 180 days of Windows activation.*

*[45] The Flicker-free capability is eliminating screen flickering through integrating DC-dimming LED backlights.*

---



## Services

### HP Care Pack Services

★ : Recommended

#### Personal Systems Consumer Care Pack Services

HP 2 year 3 day Onsite Desktop Service	UJ216E ★
HP 2 year Accidental Damage Protection Plus 3 day Onsite Desktop Service	UA050E ★
HP 3 years 3 day Onsite Desktop Service	UJ217E ★
HP 1 year Post Warranty Pickup and Return Desktop Service	U4813PE
HP 1 year SmartFriend Standalone Service	UC5Y3E
HP 1 year of Accidental Damage Protection Return to Depot Service	UB9J3E
HP 2 year 3-day Onsite Response for Consumer Desktop	U7C94E
HP 2 year Pickup and Return with 2 incident SmartFriend Service for Consumer Desktop	UN032E
HP 2 year SmartFriend Service	U35QYE
HP 2 years Pickup and Return Desktop Service	UA044E
HP 2 years Return to Depot Desktop Service	U8230E
HP 3 month SmartFriend Standalone Service	UC5Y1E
HP 3 year 3-day Onsite Response for Consumer Desktop	U7C95E
HP 3 year SmartFriend Service	U35QZE
HP 3 years Return to Depot Hardware Support for Desktops	U4810E
HP 6 month SmartFriend Service	UC5Y5E
HP 6 month SmartFriend Standalone Service	UC5Y2E

# Monitors

## Business Monitors

★ : Recommended

### P-Series

HP P24v G5 FHD Monitor	64W18A6
HP P24v G5 FHD Monitor	64W18AA
HP P22 G5 FHD Monitor	64X86AA
HP P22a G4 FHD Monitor	3Y0Q1A6
HP P22a G4 FHD Monitor	3Y0Q1AA
HP P22h G5 FHD Monitor	64W30AA
HP P22v G5 FHD Monitor	64V81AA
HP P24 G5 FHD Monitor	64X66AA
HP P24a G4 FHD Monitor	3Y0Q4A6
HP P24a G4 FHD Monitor	3Y0Q4AA
HP P24h G4 FHD Monitor	9UJ13A8
HP P24h G5 FHD Monitor	64W34AA
HP P27 G5 FHD Monitor	64X69AA
HP P27h G5 FHD Monitor	64W41AA
HP P32u G5 QHD USB-C Monitor	64W51AA
HP P34hc G4 WQHD USB-C Curved Monitor	21Y56AA

### E-Series

HP E22 G5 FHD Monitor	6N4E8AA
HP E24 G4 FHD Monitor	9VF99AA
HP E24 G5 FHD Monitor	6N6E9AA
HP E24 G5 FHD No Stand Monitor	6N6E9A9
HP E24i G4 WUXGA Monitor	9VJ40AA
HP E24m G4 FHD USB-C Conferencing Monitor	40Z32AA
HP E24mv G4 FHD Conferencing Monitor	169L0AA
HP E24q G5 QHD Monitor	6N4F1AA
HP E24t G5 FHD Touch Monitor	6N6E6AA
HP E24u G4 FHD USB-C Monitor	189T0AA
HP E24u G5 FHD USB-C Monitor	6N4D0AA
HP E27 G5 FHD Monitor	6N4E2AA
HP E27k G5 4K USB-C Monitor	6N4C4AA

HP E27m G4 QHD USB-C Conferencing Monitor	40Z29AA
---	---------

HP E27q G4 QHD Monitor	9VG82AA
------------------------	---------

HP E27q G5 QHD Monitor	6N6F2AA
------------------------	---------

HP E27q G5 QHD No Stand Monitor	6N6F2A9
---------------------------------	---------

HP E27u G4 QHD USB-C Monitor	189T3AA
------------------------------	---------

HP E27u G5 QHD USB-C Monitor	6N4D3AA
------------------------------	---------

HP E32k G5 4K USB-C Monitor	6N4D6AA
-----------------------------	---------

HP E34m G4 WQHD Curved USB-C Conferencing Monitor	40Z26AA
---	---------

HP E45c G5 DQHD Curved Monitor	6N4C1AA
--------------------------------	---------

## Value Displays

HP M24m Conferencing Monitor	678U5AA
------------------------------	---------

HP M27m Conferencing Monitor	678U8AA
------------------------------	---------

## Business LCD Monitors

HP P204v 19.5-inch Monitor	5RD66AA
----------------------------	---------

## Series 7 Pro

HP Series 7 Pro 23.8 inch FHD Monitor - 724pf	8X530AA
---	---------

HP Series 7 Pro 31.5 inch 4K Thunderbolt 4 Monitor - 732pk	8Y2K9AA
--	---------

HP Series 7 Pro 39.7 inch 5K2K Conferencing Monitor-740pm	8Y2R2AA
---	---------

## Z Displays

HP Z24f G3 FHD Display	3G828AA
------------------------	---------

HP Z24m G3 QHD Conferencing Display	4Q8N9AA
-------------------------------------	---------

HP Z24n G3 WUXGA Display	1C4Z5AA
--------------------------	---------

HP Z24q G3 QHD Display	4Q8N4AA
------------------------	---------

HP Z24u G3 WUXGA USB-C Display	1C4Z6AA
--------------------------------	---------

HP Z27k G3 4K USB-C Display	1B9T0AA
-----------------------------	---------

HP Z27q G3 QHD Display	1C4Z7A9
------------------------	---------

HP Z27q G3 QHD Display	1C4Z7AA
------------------------	---------

HP Z27u G3 QHD Display	1B9X2AA
------------------------	---------

HP Z32k G3 4K USB-C Display	50U19AA
-----------------------------	---------

HP Z34c G3 WQHD Curved Display	30A19AA	obsolete
--------------------------------	---------	----------

HP Z38c 37.5-inch Curved Display	Z4W65A4	obsolete
----------------------------------	---------	----------

HP Z38c 37.5-inch Curved Display	Z4W65A8
----------------------------------	---------

## HP Home Monitors

### HP Value Displays

HP 24mh 23.8-inch Display	1D0J9AA
HP 27mq 27-inch Display	1F2J9AA
HP M22f FHD Monitor	2D9J9AA
HP M24f FHD Monitor	2D9K0AA
HP M24fw FHD Monitor	2D9K1AA
HP M24fwa FHD Monitor	34Y22AA
HP M32f FHD Monitor	2H5M7AA
HP M32fw FHD Monitor	6R6E6AA
HP M34d WQHD Curved Monitor	3B1W4AA

### HP Home Monitors

HP M27f FHD Monitor	2G3D3AA
HP M27fq QHD Monitor	2H4B5AA
HP M27fw FHD Monitor	2H1A4AA
HP M27fwa FHD Monitor	356D5AA
HP M27ha FHD Monitor	22H94AA
HP U28 4K HDR Monitor	1Z978AA
HP U32 4K HDR Monitor	368Y5AA
HP V20 HD+ Monitor	1H848AA
HP V22v G5 FHD Monitor	65P56AA
HP V24i G5 FHD Monitor	65P58AA
HP V24v G5 FHD Monitor	65P62AA
HP V27c G5 FHD Curved Monitor	65P60AA
HP V27i G5 FHD Monitor	65P64AA

### Series 5

HP Series 5 23.8 inch FHD Height Adjust Monitor - 524sh	94C19AA
HP Series 5 23.8 inch FHD Monitor - 524sf	94C17AA
HP Series 5 23.8 inch FHD Monitor with Speakers - 524sa	94C36AA
HP Series 5 23.8 inch FHD White Monitor - 524sw	94C21AA
HP Series 5 27 inch FHD Height Adjust Monitor - 527sh	94C50AA

HP Series 5 27 inch FHD Monitor - 527sf	94F44AA
---	---------

HP Series 5 27 inch FHD Monitor with Speakers - 527sa	94F48AA
---	---------

HP Series 5 27 inch FHD White Monitor - 527sw	94F46AA
---	---------

HP Series 5 31.5 inch FHD Monitor - 532sf	94F50AA
---	---------

## **OMEN by HP Displays**

OMEN 27u 4K Gaming Monitor	3G6W0AA
----------------------------	---------

OMEN by HP 23.8 inch FHD 165Hz Gaming Monitor - OMEN 24	780D9AA
---	---------

OMEN by HP 27 inch FHD 165Hz Gaming Monitor - OMEN 27	780F9AA
---	---------

OMEN by HP 27 inch FHD 240Hz Gaming Monitor - OMEN 27s	780G5AA
--	---------

OMEN by HP 27 inch QHD 165Hz Gaming Monitor - OMEN 27q	780H4AA
--	---------

OMEN by HP 27 inch QHD 240Hz Gaming Monitor - OMEN 27qs	780J4AA
---	---------

OMEN by HP 27 inch UHD 144Hz Gaming Monitor - OMEN 27k	780G8AA
--	---------

OMEN by HP 31.5 inch QHD 165Hz Curved Gaming Monitor - OMEN 32c	780K6AA
---	---------

OMEN by HP 31.5 inch QHD 165Hz Gaming Monitor - OMEN 32q	780K0AA
--	---------

OMEN by HP 34 inch WQHD 165Hz Curved Gaming Monitor - OMEN 34c	780K8AA
--	---------

## Accessories

### Keyboards/Mice and Input Devices

★ : Recommended

#### Mice

HP 200 Sanitizable Desk Mat	8X596AA
HP 430 Multi-Device Wireless Mouse	3B4Q2AA

#### Keyboards

HP 430 Programmable Wireless Keypad	7N7C2AA
HP 450 Programmable Wireless Keyboard	4R184AA

### Webcams

#### Web Cameras

HP 430 FHD Webcam	77B11AA
-------------------	---------

---

## Disclaimer — Copyright

All other trademarks are the property of their respective owners.

Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers and/or software to take full advantage of Windows functionality. See <http://www.microsoft.com>.

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (us-en) – Mar 18, 2024 1:00 PM UTC+0000