

## Key Features

- Immerse in vibrant visuals with the 2K QHD resolution OLED panel
- Experience smooth gameplay with the 240Hz refresh rate and rapid up to 0.01ms pixel, 0.02 (GTG) response time
- Enjoy tear-free gaming with NVIDIA G-Sync Compatible and AMD FreeSync Premium
- Upgrade your setup with the ergonomic white design and vibrant RGB Lighting
- Seamlessly navigate OSD, input, and game modes using the included remote



## Product Description

More than just a display, the XG272-2K-OLED is an invitation to a gaming realm illuminated in a whole new light. Its mesmerizing 2K QHD resolution and OLED visuals bring every pixel to life with vibrant brilliance, obsidian blacks, and striking contrast, blurring the lines between the virtual world and reality. The remarkable 240Hz refresh rate and lightning-fast up to 0.01ms pixel, 0.02ms (GTG) response time ensure smooth and swift gameplay, orchestrated to perfection. Taking the experience further, the NVIDIA G-Sync Compatible and AMD FreeSync Premium deliver tear-free bliss to your gaming sessions. Beyond its exceptional performance, the XG272-2K-OLED's design is a true work of art. Standing strong and triumphant, its pristine white exterior signifies clarity, and the subtle curves of the ergonomic design converge into sharp edges, poised for any challenge. Complemented by customizable RGB lighting, it transforms your gaming setup into a sanctuary that illuminates your gaming adventures in an ethereal glow. With the included remote, effortlessly navigate on-screen display parameters, inputs, and game modes. Will you reach for the XG272-2K-OLED and claim immersion in your gaming journey?

Visit Us

[www.viewsonic.com](http://www.viewsonic.com)

### DISPLAY

|                                   |                                                                          |
|-----------------------------------|--------------------------------------------------------------------------|
| Display Size (in.):               | 27                                                                       |
| Viewable Area (in.):              | 26.5                                                                     |
| Panel Type:                       | OLED Technology                                                          |
| Resolution:                       | 2560 x 1440                                                              |
| Resolution Type:                  | QHD (Quad HD)                                                            |
| Static Contrast Ratio:            | 150,000:1 (typ)                                                          |
| High Dynamic Range:               | HDR10                                                                    |
| Brightness:                       | 450 cd/m <sup>2</sup> (typ)                                              |
| Colors:                           | 1.07B                                                                    |
| Color Space Support:              | 10 bit true                                                              |
| Aspect Ratio:                     | 16:9                                                                     |
| Response Time (Typical GTG):      | 0.02ms                                                                   |
| Viewing Angles:                   | 178° horizontal, 178° vertical                                           |
| Backlight Life (Hours):           | N/A Hrs (Min)                                                            |
| Curvature:                        | Flat                                                                     |
| Refresh Rate (Hz):                | 240                                                                      |
| Variable Refresh Rate Technology: | FreeSync Premium, G-Sync compatible                                      |
| Low Blue Light:                   | Software solution                                                        |
| Flicker-Free:                     | Yes                                                                      |
| Color Gamut:                      | DCI-P3: 97% coverage (Typ)<br>NTSC: 97% size (Typ) sRGB: 137% size (Typ) |
| Pixel Size:                       | 0.229 mm (H) x 0.229 mm (V)                                              |
| Surface Treatment:                | Anti-Glare, Hard Coating (N/A)                                           |

### COMPATIBILITY

|                        |                                       |
|------------------------|---------------------------------------|
| PC Resolution (max):   | 2560x1440                             |
| Mac® Resolution (max): | 2560x1440                             |
| PC Operating System:   | Windows 10/11 certified; macOS tested |
| Mac® Resolution (min): | 2560x1440                             |

### CONNECTOR

|                                            |                             |
|--------------------------------------------|-----------------------------|
| USB 3.2 Type A Down Stream:                | 3                           |
| USB 3.2 Type B Up Stream:                  | 1                           |
| USB 3.2 Type C DisplayPort Alt mode only : | 1 (15W power charger)       |
| 3.5mm Audio Out:                           | 1                           |
| HDMI 2.1:                                  | 2                           |
| DisplayPort:                               | 2                           |
| Power in:                                  | DC Socket (Center Positive) |

### AUDIO

|                    |           |
|--------------------|-----------|
| Internal Speakers: | 3Watts x2 |
|--------------------|-----------|

### POWER

|                        |                        |
|------------------------|------------------------|
| Eco Mode (Conserve):   | 30W                    |
| Eco Mode (optimized):  | 34W                    |
| Consumption (typical): | 42W                    |
| Consumption (max):     | 55W                    |
| Voltage:               | AC 100-240V            |
| Stand-by:              | 0.5W                   |
| Power Supply:          | External Power Adaptor |

### ADDITIONAL HARDWARE

|                       |     |
|-----------------------|-----|
| Kensington Lock Slot: | 1   |
| Cable Organization:   | Yes |

### CONTROLS

|                    |                                                                              |
|--------------------|------------------------------------------------------------------------------|
| Physical Controls: | Joystick key: Up, Right, Down, Left, Center; Quick Access; Power, Game Modes |
| On Screen Display: | Modes, Gaming, Display, Input Select, Setup Menu                             |

### OPERATING CONDITIONS

|                            |                             |
|----------------------------|-----------------------------|
| Temperature:               | 32°F to 104°F (0°C to 40°C) |
| Humidity (non-condensing): | 20% to 90%                  |

### WALL MOUNT

|                  |              |
|------------------|--------------|
| VESA Compatible: | 100 x 100 mm |
|------------------|--------------|

### INPUT SIGNAL

|                       |                                                                                      |
|-----------------------|--------------------------------------------------------------------------------------|
| Frequency Horizontal: | HDMI (v2.1): 30 ~ 160KHz,<br>DisplayPort (v1.4): 15 ~ 255KHz,<br>Type C: 15 ~ 255KHz |
| Frequency Vertical:   | HDMI (v2.1): 30 ~ 240Hz,<br>DisplayPort (v1.4): 48 ~ 240Hz,<br>Type C: 48 ~ 240Hz    |

### VIDEO INPUT

|               |                                                                                     |
|---------------|-------------------------------------------------------------------------------------|
| Digital Sync: | TMDS compatible - HDMI (v2.1),<br>PCI-E - DisplayPort (v1.4), Micro-Packet - Type C |
|---------------|-------------------------------------------------------------------------------------|

### ERGONOMICS

|                      |           |
|----------------------|-----------|
| Height Adjust (mm):  | 120       |
| Swivel:              | 40°       |
| Tilt (Forward/Back): | -5° / 20° |
| Pivot (Right/Left):  | 90° / 90° |

### WEIGHT (IMPERIAL)

|                          |      |
|--------------------------|------|
| Net (lbs):               | 15.3 |
| Net Without Stand (lbs): | 10.6 |
| Gross (lbs):             | 22.9 |

### WEIGHT (METRIC)

|                         |      |
|-------------------------|------|
| Net (kg):               | 7    |
| Net Without Stand (kg): | 4.8  |
| Gross (kg):             | 10.4 |

### DIMENSIONS (IMPERIAL) (WXHXD)

|                               |                           |
|-------------------------------|---------------------------|
| Packaging (in.):              | 36.5 x 19.9 x 6.7         |
| Physical (in.):               | 23.8 x 17.63~22.31 x 8.54 |
| Physical Without Stand (in.): | 23.8 x 14.35 x 2.45       |

### DIMENSIONS (METRIC) (WXHXD)

|                              |                                |
|------------------------------|--------------------------------|
| Packaging (mm):              | 928 x 506 x 170                |
| Physical (mm):               | 604.42 x 447.81~566.60 x 216.9 |
| Physical Without Stand (mm): | 604.42 x 364.6 x 62.22         |

### GENERAL

|              |                                                                                                        |
|--------------|--------------------------------------------------------------------------------------------------------|
| Regulations: | cTUVus, FCC-B, ICES003, CEC, NOM, Mexico Energy, CE, CE EMC, CB, RoHS, ErP, REACH, WEEE, EAC, UkrSEPRO |
|--------------|--------------------------------------------------------------------------------------------------------|

### PACKAGE CONTENTS:

XG272-2K-OLED x1, 3-pin Plug (IEC C13 / CEE22) x1, DisplayPort Cable (v1.4; Male-Male) x1, USB A/B Cable (v3.2; Male-Male) x1, AC/DC Adapter x1, Quick Start Guide x1, Remote control x1

|                   |                                                                    |
|-------------------|--------------------------------------------------------------------|
| Recycle/Disposal: | Please dispose of in accordance with local, state or federal laws. |
|-------------------|--------------------------------------------------------------------|

|           |                                                    |
|-----------|----------------------------------------------------|
| Warranty: | *Warranty offered may differ from market to market |
|-----------|----------------------------------------------------|