

# Product datasheet

Specifications



## Easy Rack PDU, Switched Metered Outlet, 0U, 3 Phase, 11kW, 230V, 16A, (18) C13 and (6) C19 outlets, IEC60309 3P+N+PE inlet

EPDU2216SMBO

### Overview

Lead Time Usually in Stock

### Main

Colour	Black
Product Or Component Type	PDU
Pdu Type	Metered outlet
Cord Length	3 m
Number Of Cables	1
Provided Equipment	Installation guide

### Complementary

Input Voltage	400 V 3 phases
Height	1800 mm
Width	55 mm
Output Voltage	230 V
Depth	56 mm
Net Weight	7.12 kg
Mounting Location	Side
Mounting Preference	No preference
Input Plug Type	IEC 60309 16 A 3P + N + PE
Mounting Mode	Not rack-mountable
Rack Units	0U
Usb Compatible	No
Mounting Position	Vertical
Communication Port Protocol	SNMP
[In] Rated Current	16 A
Max Line Current	16 A
Input Current Limits	16 A
Load Capacity	11000 VA
Network Frequency	50/60 Hz
Plug Standard	IEC 60309

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

---

<b>Total Number Of Outlets</b>	18 IEC 60320 C13 10 A
--------------------------------	-----------------------

---

<b>Communication Network Type</b>	10/100BASE-T
-----------------------------------	--------------

---

## Environment

---

<b>Product Certifications</b>	CE
-------------------------------	----

---

<b>Ambient Air Temperature For Operation</b>	-5...50 °C
--	------------

---

<b>Relative Humidity</b>	5...95 %
--------------------------	----------

---

<b>Operating Altitude</b>	0...3000 m
---------------------------	------------

---

<b>Ambient Air Temperature For Storage</b>	-25...65 °C
--	-------------

---

<b>Storage Relative Humidity</b>	5...95 %
----------------------------------	----------

---

<b>Storage Altitude</b>	0...15000 m
-------------------------	-------------

---

## Packing Units

---

<b>Unit Type Of Package 1</b>	PCE
-------------------------------	-----

---

<b>Number Of Units In Package 1</b>	1
-------------------------------------	---

---

<b>Package 1 Height</b>	203 cm
-------------------------	--------

---

<b>Package 1 Width</b>	19.5 cm
------------------------	---------

---

<b>Package 1 Length</b>	13 cm
-------------------------	-------

---

<b>Package 1 Weight</b>	8.29 kg
-------------------------	---------

---

## Contractual warranty

---

<b>Warranty</b>	2 Years repair and Replace
-----------------	----------------------------

---

## Sustainability


**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

[Learn more about Green Premium >](#)



RoHS/REACH

## Well-being performance

 **Rohs Exemption Information** [Yes](#)

---

## Certifications & Standards

**Reach Regulation** [REACH Declaration](#)

---

**Eu Rohs Directive** [Compliant with Exemptions](#)

---