

Revolutionary wireless mobile battery duplex scanner

Whatever the place, wherever you are: IRIScan Anywhere 6 Wifi Duplex is a light, autonomous, standalone, high resolution, lithium battery powered portable colour document scanner that allows you to duplex scan contracts, shipping notes, invoices, receipts, medical pre-scripted, patient files records, business cards, pages, letter & A4 color documents.

IRIScan Anywhere 6 Wifi Duplex can easily be transported & connected wireless to your smartphone or tablet on the go. It's an ideal companion for those on the go who needs to scan double-sided important documents with always a very high quality image standard whatever the paper size (up to A4/letter), the paper type (glossy, matte, plastic) and whatever the environment you are in (outside, inside, sunny, dark, over exposed, ...). All images will be stored in your smartphone's preferred directory thanks to the free App "IRIScan PDF scanner" ready to be shared immediately to your office, colleague or secretary.

Business men dealing with legal & invoice management, medical prescription, patient file management, hospital & service desk, ID Cards or business card management, shipping notes or banking & finance document workflow will be delighted to capture perfect double-sided quality image documents on the go or via USB cable when at office. Powered by IRIS latest HQ OCR engine, IRIS highest Quality Optical Character Recognition, you will be able to convert double-side scanned images into searchable PDFs, editable Word, Excel or Text while supporting up to 138 languages.

Such new companion definitively helps you empowering the enterprise' productivity while increasing big time employee's satisfaction.

Key Features

- Scan anywhere with a smartphone, tablet or PC.
- Fast scanning speeds at up to 4 seconds per page (15 ppm – 30 ipm) in USB mode
- Double side document (duplex scan).
- Scan directly to JPEG/TIFF/PDF and other image format.
- Choose scan file prefix & time format.
- Rechargeable Lithium battery power scan up to 180 pages between battery charges.
- Scanning resolutions: 300/600 dpi (1200 interpolated).
- Free IRIScan PDF scanner App to share your scans to ANY tablet or smartphone device (iOS®/Android™).
- Get editable document with free Readiris™ OCR software included.
- Convert to Word, Excel, PDF, etc.
- Enjoy professional PDF management with a free 30 days trial Readiris™ PDF for PDF creation, annotations, comments or signature.

Quick Reference Guide

Product name	IRIScan™ Anywhere 6 Wifi Duplex
SKU	461854
EAN code	5420079900943
UPC-A code	765010766420
Mercury code	(91)3877V399
Box size (L x D x H)	355 x 166 x 68 mm - 13.98 x 6.54 x 2.68 in
Box weight	940 g (2.72 lbs)
Box languages	English, French, German, Dutch, Italian, Spanish, Portuguese, Arabian, Simplified Chinese, Hebrew
Box content	Scanner • Calibration card • USB-C cable • Getting started guide

Scanner specifications

Scanning speed & Format	4sec – Up to 15PPM – A8-A4 / Letter size 8.5 x 11 in
Type of Scanner & Light Source	Single sheet – CIS – Duplex – RGB LED
Scanner dimension	312 x 66 x 49 mm & 12.28 x 2.59 x 1.92 in
Color Depth & Resolution	24bit – 300/600dpi & 1200dpi interpolated
Composite of Battery & Battery weight	Lithium-ion cell & 48gr – 0.11lbs
Number of lithium cells / lithium content in grams	1 & 0.825g
Power	USB powered USB-C
Power Consumption Scanning operating	6.1W
Power Consumption Ready & OFF	1.8W & 0.1W
Maximum DAILY DUTY CYCLE in pages per day	500 pages
Battery life operating (Number of scans)	180 scans/360 images WIFI ON
Scanner Life	20,000 scans
Scanner Weight in kg & lbs	630g (1.389 lbs)
Compatibility	Twain/WIA/ICA
Scanning Width in inch/cm	8.5inch/21.6cm
USB Port	Micro USB
Charging Time in hours	4.5hrs
Wireless LAN Specification parameters	802.11 a/b/g/n/ac
Acoustical Noise in operation	≤ 55 dB

Minimum computer requirements

Scanner

- At least one USB port available
- Wifi connection available
- Compatible with latest Android® and iOS® versions

Software suite for Windows® and macOS®

- Intel® based PC or equivalent recommended
- Microsoft® Windows® 11, 10
- Mac® computer with Intel 64® Arm processor
- macOS® X version 12.x or above
- 512MB RAM recommended
- 1GB of available hard disk space
- Internet connection for software download



IRIScan-PDF Scanner



www.irislink.com

I.R.I.S. s.a. - 10 rue du Bosquet - 1348 Louvain-La-Neuve - Belgium

marketing.distri@iriscompany.com

I.R.I.S. Inc. - 55 NW 17th Avenue, Unit D - Delray Beach, Florida 33445 United States

Canon
CANON GROUP

THL231018-458

© Copyright 2023 I.R.I.S. s.a.
All rights reserved for all countries. IRIS, IRIS' product names, IRIS' logos and IRIS' product logos are IRIS trademarks. All other products and names mentioned are trademarks or registered trademarks from their respective owners.

