



## SPECIFICATIONS

显示区域 (mm)	543.7 (H) x 302.6 (V)
点距 (H x V)	0.27156(H)x0.27156(V)
音频接口	1x Headphone out
激活范围	48~180Hz
动态刷新率技术	Adaptive-Sync
面板类型	Rapid IPS
动态对比度	100000000:1
尺寸 (W x D x H)	557.1 x 220.1 x 418.5 mm 557.1 x 66.4 x 326.9 mm (without stand)
包装尺寸 (W X D X H)	WW carton: 630 x 125 x 411 mm Outer: 650 x 145 x 443 mm
表面处理	Anti-glare
显示色彩	16.7M (8bits)
显示接口	1x Display Port (1.2a) 2x HDMI™ (2.0b)
屏幕尺寸	24.5" (62.2cm)
USB 接口	N/A
屏幕比例	16:9
最佳分辨率	1920 x 1080 (FHD)
防盗锁	Yes
VESA 支架	N/A
刷新率	180Hz
电源适配器规格	Power Cable
响应时间	1ms (GtG)
电源输入	100~240V, 50/60Hz
可视角度	178° (H) / 178° (V)
曲面屏幕	Flat
信号频率	52.7KHz-198KHz / 48-180Hz(V)
调节角度 (倾斜)	-5° ~ 20°
屏幕亮度	300
调节角度 (旋转)	N/A
对比度	1000:1
调节范围 (高度)	N/A
中心轴旋转	N/A
PIP / PBP 分屏	N/A

## FEATURES



### Rapid IPS

Provides 1ms GTG fast response time, optimizes screen colors and brightness.



### 180Hz High Refresh Rate

Experience smooth gaming with a blazing fast 180Hz refresh rate, that gives you the upperhand in fast moving games.



### 1ms Fast Response Time

Eliminate screen tearing and choppy frame rates with 1ms response time.



### Frameless Design

With the narrow bezel, you will not even notice the monitor at all in the heat of the moment.



### Night Vision

See every detail clearly in the dark, helping you find and attack enemies before they notice.



### Wide Color Gamut

Game colors and details will look more realistic and refined, to push game immersion to its limits.

接口分辨率	Display Port: 1920 x 1080 (Up to 180Hz) HDMI™: 1920 x 1080 (Up to 180Hz)
窄边框设计	Adobe RGB, DCI-P3 and sRGB follow CIE1976 Standard
重量	Yes
HDR支持	3.24 / 5.13 (kg) 2.87kg(without stand)
Adobe RGB / DCI-P3 / sRGB	N/A
	82% / 78% / 99%

## CONNECTIONS



1. 5-way joystick navigator
2. DC jack
3. 2 x HDMI™ (2.0b)
4. 1 x Display Port (1.2a)
5. Headphone out
6. Kensington lock