



V7 Premium Wireless Bluetooth Headset with ANC

HB650S

SKU: 12GT05

Turn up your focus and turn down distractions!

Enhance communication and improve focus no matter where you work. Enjoy optimal speech clarity with the environmental noise-cancelling technology (ENC) - perfect for busy office settings so callers hear only you and not the conversations of your workmates, while Hybrid Active Noise Cancellation (ANC) reduces distracting sounds around the office like noisy air conditioning - so you're able to focus on the task at hand.

Enjoy all-day wearability with a ultra-comfortable, ultra-lightweight fit, and useful features like 'Call-Busy' indicators so others won't interrupt, and a convenient Lift-to-Mute boom

Fully compatible with video conferencing programs including Microsoft Teams, Zoom, Google Meet, and many others.

- Noise cancelling (ENC) microphone for optimal communication
- Active Noise Cancellation (ANC) reduces high-frequency noise
- Wireless Bluetooth® technology with up to 30 meters range
- Lift-to-Mute boom
- Busylight appears during calls
- 24-hours talk time (14 w/ANC on) and 150 hours standby

General

Sku: 12GT05
 Model: HB650S
 UPC: 662919116571
 Warranty: 2 years
 Compliance: SIG, CE, FCC, RoHS, UKCA
 Country Of Origin: China
 Package Type: OEM Box
 Package Includes: Headset, USB-A dongle, Type-C adapter, USB charging cable, AUX cable, storage bag, user's guide, compliance and warranty documents

Color

Color: Black
 Accent Color: Red

Design

Audio Segment: Premium
 Headset Form Factor: On Ear
 Controls: Power, pairing, volume, play/pause, forward/repeat, mute, answer/end, ANC, Lift-to-Mute

Package Dimensions

Package Dimensions (L/W/H): 203.2 x 254 x 88.9 mm (8 x 10 x 3.5 in)
 Shipping Weight: 320 g (11.29 oz)

Product Dimensions

Product Dim (L/W/H): 171.5 x 69.9 x 194.3 mm (6.75 x 2.75 x 7.65 in)
 Product Weight: 153 g (5.40 oz)

California Prop 65

No warning required

Technical

Connectivity: Bluetooth
 Decibels: 118 ± 3 dB SPL @ 1KHz
 Impedance: 32 Ω
 Driver Size: 32 mm
 Frequency Range: 20 Hz to 20 kHz
 Mic Sensitivity: -38 dBV/Pa



Specifications

Form Factor	Binaural Stereo
Battery type	Lithium Ion Polymer (380mAh)
Charging time	2 hours
Talk time	Up to 24 hours
Listening time	Up to 40 hours (ANC OFF) Up to 30 hours (ANC ON)
Standby	Up to 150 hours
Microphone Technology	Environmental Noise Cancelling (ENC)
Audio Codecs supported	SBC, AAC
Bluetooth profiles	A2DP, AVRCP, HSP, HFP
Bluetooth version	v5.1; Class 2
Connectivity	Bluetooth and V7-Link 650 USB Dongle, Analog (audio only)
Operating range	Up to 30 meters/100-ft with dongle
ANC Technology	Advanced Hybrid ANC
Maximum device pairing	8
Multipoint connections	2