



# Poly Savi 7320 UC Stereo DECT 1920-1930 MHz Headset (8L549AA)



## Overview

### Ensure secure conversations

Keep conversations private. With up to 2x better density, this secure DECT™ wireless headset is an ideal choice for financial, medical, government, and contact centers or anywhere sensitive conversations happen.

### DECT™ security

Savi 7300 headsets don't just meet security expectations, they exceed them with secure pairing, 128-bit authentication, and military-grade features, such as 256-bit AFS encryption. Conversations stay private and secure.

### Work where you want

With a discreet, easy-to-use DECT wireless adapter, the Savi 7300 UC series is ready to work where you do. Simply plug the adapter into your PC and you are ready to collaborate — in the office, remote, or on the go.

### Interference-free audio

With 2x better density than other DECT™ headsets, more people in shared spaces benefit from wireless headsets with clear, interference-free audio. IT can deploy more Savi 7300 Office Series compared to other DECT™ headsets without concern.

## Features

### Keep conversations private

Make sure nearby conversations are not overheard. The noise-canceling microphone enhanced with Poly Acoustic Fence technology ensure private conversations stay private.

### DECT™ security standards

Designed to meet the highest-level DECT™ Security Step C enhanced with military-grade FIPS 140-2 listed features, such as 256-bit AES encryption.<sup>[2]</sup>

### Meet enterprise security needs

Ideal for use in financial, medical, and government environments, where Bluetooth® technology is typically banned.

### Remote management

Stay in control with remote device management for settings, firmware, and security updates.

### Roaming range

Give users more freedom to move with a line-of-sight wireless range of up to 450 ft / 137 m.

### Training made easy

Make training and collaboration easy with the ability to conference up to 4 headsets on the D400 dongle.

---

[2] DECT security standards can be found on <https://etsi.org>.

## Specifications

<b>Audio</b>	Noise cancellation with Acoustic Fence technology; Up to 2x more density than other DECT™ headsets; Adaptive power control to maximize user density
<b>Weight</b>	160 g
<b>Weight</b>	0.35 lb
<b>Package dimensions (W x D x H)</b>	185 x 210 x 115 mm
<b>Package weight</b>	300 g
<b>Battery life</b>	Up to 13 hours (talk time); Up to 52 hours (standby time)
<b>Special features</b>	Adjustable headband
<b>Minimum System Requirements</b>	USB Type-A port; USB Type-C® port
<b>UPC number</b>	197497837766
<b>Manufacturer Warranty</b>	Poly standard two-year limited warranty
<b>What's in the box</b>	Charging stand; Wireless headset; USB Type-A charging cable; Travel case; USB Type-A to USB Type-C® adapter; D400 USB Type-A DECT™ adapter

## Additional specifications

<b>Acoustic protection technology</b>	SoundGuard Digital <sup>[1,2]</sup>
<b>Battery type</b>	Rechargeable Li-ion polymer
<b>Button user controls</b>	Call answer/end; Mute; Volume +/-; Power on/off
<b>Cartons per layer</b>	10
<b>Cartons per pallet</b>	80
<b>Charge time</b>	2 hours
<b>Charging plug</b>	USB Type-C® to USB Type-A; USB Type-C® to USB Type-C®
<b>Color</b>	Black
<b>Compatible Operating Systems</b>	macOS; Windows
<b>Connection type</b>	DECT™
<b>Connects to</b>	PC
<b>Country of origin</b>	Made in Mexico
<b>ECCN</b>	5A992
<b>Ear cushions</b>	Artificial leather (surface material)
<b>HTS code</b>	8517620090
<b>Indicator light</b>	On call
<b>Management Software</b>	Poly Lens
<b>Multiple order quantity</b>	5
<b>Package dimensions (W x D x H)</b>	7.48 x 8.26 x 2.16 in
<b>Package weight</b>	0.66 lb
<b>Pallet (layers)</b>	8
<b>Pallet dimensions</b>	40 x 48 x 58.66 in
<b>Pallet dimensions (W x D x H)</b>	101.6 x 121.9 x 149 cm
<b>Pallet weight</b>	357 kg
<b>Pallet weight</b>	787.05 lb
<b>Products per pallet</b>	400
<b>Products per pallet layer</b>	50
<b>UNSPSC code</b>	43191638
<b>Voice alerts</b>	Volume maximum; Volume minimum; Mute on; Mute off; Muted; Connection status; Talk time; Battery low
<b>Wireless range</b>	Up to 137 m in open area; Up to 40 m in typical office environment
<b>Wireless range (imperial)</b>	Up to 450 ft in open area; Up to 130 ft in typical office environment

---

*[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA).*

*[2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.*

---

# Services

## Poly Services

★ : Recommended

### Poly Support Services

3 year Poly+ Savi Service	PSAVI312 ★
3 year Next Business Day Hardware Advance Replacement Savi Poly DaaS Service	DSAVIDS3
3 year Partner Poly+ Savi Service	PSAVI362

## Hybrid Work Solutions

### Audio

★ : Recommended

#### Audio Accessories

Poly APA-23 Electronic Hookswitch TAA	85Q50AA
Poly APA-24 Electronic Hookswitch TAA	85Q52AA
Poly APC-43 Electronic Hookswitch (Bagged) TAA	85Q56AA
Poly APC-43 Electronic Hookswitch TAA	85Q55AA
Poly APC-45 Electronic Hookswitch TAA	85Q57AA
Poly APC-82 Electronic Hookswitch TAA	8H981AA
Poly APD-80 Electronic Hookswitch TAA	85Q58AA
Poly APN-91 Electronic Hookswitch TAA	85Q59AA
Poly APP-51 Electronic Hookswitch TAA	85Q60AA
Poly APS-11 Electronic Hookswitch TAA	85Q78AA
Poly APT-31 Electronic Hookswitch TAA	85Q84AA
Poly APU-72 Electronic Hookswitch TAA	85Q95AA
Poly APU-75D Electronic Hookswitch TAA	85Q99AA
Poly APU-76 Electronic Hookswitch TAA	85R00AA
Poly APV-63 Electronic Hookswitch TAA	85R01AA
Poly APV-66 Electronic Hookswitch TAA	85R02AA
Poly Blackwire 7225 Case	85Q69AA
Poly Busy Light (Angle Plug)	920Q4AA
Poly EHS 3.5mm to 3.5mm Cable	85R17AA
Poly HL10 Extended Arm	8L554AA
Poly HL10 Handset Lifter	784Q1AA
Poly HL10 Handset Lifter TAA	8R713AA
Poly HL10 Handset Lifter with Straight Plug TAA	784Q2AA
Poly HL10 Lifter Arm +Ring Detector Accessory	8A7E3AA
Poly RD-1 Electronic Hookswitch	85R71AA
Poly Savi 7300 Battery with Removal Tool	784P8AA
Poly Savi 7300 Leatherette Ear Cushion (1 Piece)	783Q7AA
Poly Savi 7300 Leatherette Ear Cushions (2 Pieces)	783Q8AA
Poly Savi 7310 Monaural DECT 1880-1900 MHz Top	8Y9B6AA
Poly Savi 7310 Monaural DECT 1920-1930 MHz Top	783N0AA

Poly Savi 7310 Monaural Microsoft Teams Certified DECT 1880-1900 MHz Top	8Y9B8AA
Poly Savi 7310 Monaural Microsoft Teams Certified DECT 1893-1906 MHz Top	9V8Z7AA
Poly Savi 7310 Monaural Microsoft Teams Certified DECT 1920-1930 MHz Top	783N2AA
Poly Savi 7320 Stereo DECT 1880-1900 MHz Top	8Y9B7AA
Poly Savi 7320 Stereo DECT 1893-1906 MHz Top	9V8Z6AA
Poly Savi 7320 Stereo DECT 1920-1930 MHz Top	783N1AA
Poly Savi 7320 Stereo Microsoft Teams Certified DECT 1880-1900 MHz Top	8Y9B9AA
Poly Savi 7320 Stereo Microsoft Teams Certified DECT 1893-1906 MHz Top	9V8Z8AA
Poly Savi 7320 Stereo Microsoft Teams Certified DECT 1920-1930 MHz Top	783N3AA
Poly Savi 7410/7420 Office Charging Cradle	8L556AA
Poly Savi 8400/7400 Office DECT 1880-1900 MHz Base	8L569AA
Poly Savi 8400/7400 Office DECT 1920-1930 MHz Base	8L571AA
Poly Savi 8400/7400 Office Microsoft Teams Certified DECT 1880-1900 MHz Base	8L558AA
Poly Savi 8400/7400 Office Microsoft Teams Certified DECT 1920-1930 MHz Base	8L562AA
Poly Savi 8410/8420 Office Charging Cradle	8L573AA
Poly Savi 8440/8445 Office Charging Cradle	8L577AA
Poly Savi D400 UC DECT 1880-1890 MHz Dongle	8J8V9AA
Poly Savi D400 UC DECT 1880-1900 MHz Dongle	8J8V7AA
Poly Savi D400 UC DECT 1893-1906 MHz Dongle	8J8V6AA
Poly Savi D400 UC DECT 1910-1920 MHz Dongle	8J8V8AA
Poly Savi D400 UC DECT 1920-1930 MHz Dongle	85T33AA
Poly Savi D400 UC Microsoft Teams Certified DECT 1880-1900 MHz Dongle	8J8W1AA
Poly Savi D400 UC Microsoft Teams Certified DECT 1893-1906 MHz Dongle	8J8W0AA
Poly Savi D400 UC Microsoft Teams Certified DECT 1910-1920 MHz Dongle	8J8W2AA
Poly Savi D400 UC Microsoft Teams Certified DECT 1920-1930 MHz Dongle	85T34AA
Poly Savi Office Power Supply with Right Angled Plug -9V 1000mA	8L5A2AA
Poly Savi Office S2 Telephone Cable	85R55AA
Poly Savi Office Straight Plug Online Indicator	85R52AA
Poly Savi Office Telephone Interface Cable	85R57AA
Poly Savi Office Universal AC Power Supply with Straight Plug -9V 1000mA	85R59AA
Poly USB-A to USB-C Adapter	85Q48AA
Poly USB-C to USB-A Adapter	85Q49AA
Poly Voyager USB-A Charging Stand	783R6AA
Poly Voyager USB-C Charging Stand	783R7AA



## Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Aug 06, 2024 7:42 PM UTC+0000