










SPECIFICATIONS

Panel Size	31.5" (80.01 cm)
Active Display Area (mm)	698.4(H) x 392.85(V)
Curvature	Curve 1500R
Panel Type	VA
Panel Resolution	1920 x 1080 (FHD)
Pixel Pitch (H x V)	0.36375(H) x 0.36375(V)
Aspect Ratio	16:9
Brightness (nits)	250 (Typ.)
Contrast Ratio	3000:1 (Typ.)
DCR	100000000:1
Signal Frequency	52.7~1125KHz(H) / 48~250Hz(V)
ACTIVATED RANGE	48~250Hz
Refresh Rate	250Hz(OC)
Response time	1ms (MPRT)
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive-Sync
HDR Support	HDR Ready
Video ports	1 x DisplayPort 1.4a 2 x HDMI™ 2.0b (FHD@240Hz)
USB ports	N/A
Audio ports	1 x Headphone Out
Viewing Angle	178° (H) / 178° (V)
Adobe RGB / DCI-P3 / sRGB	81%/78%/101%
Surface Treatment	Anti-Glare
Display Colors	1.07B , 10 bits (8 bits + FRC)
Power Type	Power Cable
Power Input	100 ~ 240V, 50/60Hz
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Swivel)	N/A
Adjustment (Pivot)	N/A
Adjustment (Height)	N/A
Kensington Lock	Yes
Dimension (W x D x H)	709.4 x 507.2 x 249.8mm 709.4 x 419.1 x 107.2mm(without stand)
Carton Dimension (W X D X H)	WW Carton:800 x 170 x 514mm Outer:818 x 188 x 549mm
Frameless Design	Yes

FEATURES

- 
1500R
 Enjoy the most immersive gameplay with 1500R curvature rate.
- 
250Hz High Refresh Rate
 Experience smooth gaming with a blazing fast 250Hz refresh rate, that gives you the upperhand in fast moving games.
- 
1ms Fast Response Time
 Eliminate screen tearing and choppy frame rates with 1ms(MPRT) response time.
- 
Wide Color Gamut
 Game colors and details will look more realistic and refined, to push game immersion to its limits.
- 
Console Mode
 Perfectly support 120Hz at QHD 2K resolution with next-gen console like PS5 and Xbox series X/S.
- 
HDR Ready
 Provide eye-catching detail through contrast and shadows adjustment.
- 
Frameless Design
 With the narrow bezel, you will not even notice the monitor at all in the heat of the moment.

PIP / PBP Function	N/A
VESA Mounting	100 x 100 mm
Weight (NW / GW)	5.4kg / 8.5kg
Note	Display Port: 1920x1080 (Up to 250Hz) HDMI™ 2.0: 1920x1080 (Up to 240Hz) *Adobe RGB, DCI-P3 and sRGB follow CIE1976 Standard

CONNECTIONS



1. 5-Way Joystick Navigator
2. AC-in
3. HDMI™ 2.0b(FHD@240Hz)
4. DisplayPort 1.4a
5. Earphone out
6. Kensington Lock