

ENGAGE 65 SE

Engineered to be the world's most powerful professional wireless headsets.

- > Industry-leading wireless performance. Better customer connections.
- > More talk time, less interruptions. Increase productivity.
- > Crystal-clear calls. Enhance the customer experience.



Product name		Engage 65 SE Stereo	Engage 65 SE Mono	Engage 65 SE Convertible
General info	Box contents	Headset, Phone adapter cable, user documents, Headset base unit, power supply, USB-C to USB-A cable	Headset, Phone adapter cable, user documents, Headset base unit, power supply, USB-C to USB-A cable	Headset, Ear hook, Head band, Phone adapter cable, user documents, Headset base unit, power supply, USB-C to USB-A cable, 3 sizes of EarGels™
	Packaging dimensions (WxHxD)	190mm x 95mm x 147mm 7.48in x 3.74in x 5.79in	190mm x 95mm x 147mm 7.48in x 3.74in x 5.79in	145mm x 95mm x 190mm 5.71in x 3.74in x 7.48in
	Headset Weight	83g 2.93oz	57g 2.01oz	21g 0.74oz
	Warranty	2 years	2 years	2 years
	LED features and functions	Battery status, Busylight, Firmware update status, incoming call, Mute/unmute, Power indicator	Battery status, Busylight, Firmware update status, incoming call, Mute/unmute, Power indicator	Battery status, Busylight, Firmware update status, incoming call, Mute/unmute, Power indicator
	Certifications and compliance	Zoom, Works with all leading UC platforms, Google Meet, Amazon Chime, Works With Chromebook, Microsoft Open Office certification	Zoom, Works with all leading UC platforms, Google Meet, Amazon Chime, Works With Chromebook, Microsoft Open Office certification	Zoom, Works with all leading UC platforms, Google Meet, Amazon Chime, Works With Chromebook, Microsoft Open Office certification
Audio	Speaker frequency range	40Hz - 16000Hz	40Hz - 16000Hz	40Hz - 16000Hz
	Speaker bandwidth (music mode)	40Hz - 16000Hz	40Hz - 16000Hz	40Hz - 16000Hz
	Speaker bandwidth (speak mode)	150Hz - 6800Hz	150Hz - 6800Hz	150Hz - 6800Hz
	Microphone type	1 Analog MEMS and 1 Analog ECM	1 Analog MEMS and 1 Analog ECM	Electret Condenser (ECM) Uni-Directional Microphone
	User hearing protection	PeakStop™, Jabra SafeTone™ 2.0, EU Noise at Work, G616	PeakStop™, Jabra SafeTone™ 2.0, EU Noise at Work, G616	PeakStop™, Jabra SafeTone™ 2.0, EU Noise at Work, G616
	Microphone bandwidth	100Hz - 10000Hz	100Hz - 10000Hz	100Hz - 10000Hz
Software & Apps	Compatible software and/or apps	Jabra Direct, Jabra SDK, Jabra Xpress	Jabra Direct, Jabra SDK, Jabra Xpress	Jabra Direct, Jabra SDK, Jabra Xpress
Fit & Comfort	Form factor	On-ear headband	On-ear headband (neckband as accessory)	Earhook, headband (neckband as accessory)
Battery	Talk time	Up to 13 hours (with busylight off)	Up to 13 hours (with busylight off)	Up to 9 hours (with busylight off)
	Corded charging	USB-C™	USB-C™	USB-C™
	Sleep mode	Yes	Yes	Yes
	Charging time	Up to 90 minutes	Up to 90 minutes	Up to 90 minutes
	Battery status % after 30 min / 60 min	40% after 30 min charging and 80% after 60 min charging	40% after 30 min charging and 80% after 60 min charging	40% after 30 min charging and 80% after 60 min charging
	Battery type	Rechargeable lithium-ion battery	Rechargeable lithium-ion battery	Rechargeable lithium-ion battery
	User exchangeable battery	Yes	Yes	Yes

Connectivity	Wireless technology	DECT	DECT	DECT
	Operating range	Up to 150m 490ft	Up to 150m 490ft	Up to 100m 330ft
Extended info	Power consumption	Up to 0.65A / 7.5V / 4.875W	Up to 0.65A / 7.5V / 4.875W	Up to 0.65A / 7.5V / 4.875W
	Operating temperature	-10°C to 55°C 14°F to 131°F	-10°C to 55°C 14°F to 131°F	-10°C to 55°C 14°F to 131°F
	Storage temperature	-5°C to 45°C 23°F to 113°F	-5°C to 45°C 23°F to 113°F	-5°C to 45°C 23°F to 113°F

PRODUCT TYPE	SKU	DESCRIPTION
Products	9653-553-125	Jabra Engage 65 SE - Mono
	9655-553-125	Jabra Engage 65 SE - Convertible
	9659-553-125	Jabra Engage 65 SE - Stereo
Accessories	14101-60	Jabra Engage Ear Cushions – 5 pairs for Stereo headset
	14101-61	Jabra Engage Ear Cushions – 10 pieces for Mono headset
	14101-72	Jabra Engage Ear Cushions – 1 pair for Stereo headset
	14101-73	Jabra Engage Ear Cushions – 2 pieces for Mono
	14121-34	Jabra Engage Headband Pad - Black, 5 pieces
	14121-37	Jabra Engage Mono Neckband
	14121-38	Jabra Engage Neckband for Convertible headset
	14121-39	Jabra Engage Mono Headband
	14121-40	Jabra Engage Headband for Convertible headset
	14121-41	Jabra Engage Convertible EarGels and Earhook Pack
	14151-09	Jabra Engage Battery Pack
	14201-12	Standard RJ9 to RJ9 Flat Cord with Modular Plug (857 mm)
	14205-13	Jabra Link 400a USB-A, DECT, UC, NA
	14205-23	Jabra Link 400a USB-A, DECT, MS, NA
	14205-33	Jabra Link 400c USB-C, DECT, UC, NA
	14205-43	Jabra Link 400c USB-C, DECT, MS, NA
	14207-42	Jabra Engage Power Supply - EMEA
	14207-43	Jabra Engage Power Supply - NA
	14207-44	Jabra Engage Power Supply - APAC (UK/AU/NZ)
	14208-31	Jabra USB-A to USB-C cable - Black
	14208-32	Jabra USB-C to USB-C cable - Black
	14217-01	Jabra Engage SE Desk Stand (Stereo/Mono), USB-A
	14217-02	Jabra Engage SE Desk Stand (Convertible), USB-A
	14217-04	Jabra Engage 65 SE Replacement Base (Mono/Stereo)
	14217-05	Jabra Engage SE Desk Stand (Stereo/Mono), USB-C
	14217-06	Jabra Engage SE Desk Stand (Convertible), USB-C
	14401-42	Jabra Engage SE Replacement Headset - Mono
14401-47	Jabra Engage SE Replacement Headset - Stereo	
14401-52	Jabra Engage SE Replacement Headset - Convertible	

Please note that different regions use different DECT frequencies. Therefore it is important to select the appropriate SKU for the region where the headset will be used.

Jabra Engage 65 SE Tech Sheet 06082024

Download the latest version of this document at:
jabra.com/support