



Poly Savi 7310 UC Monaural Microsoft Teams Certified DECT 1920-1930 MHz Headset (8L585AA)



Overview

Ensure secure conversations

Keep conversations private. With up to 2x better density, this secure DECT™ wireless headset is an ideal choice for financial, medical, government, and contact centers or anywhere sensitive conversations happen.

DECT™ security

Savi 7300 headsets don't just meet security expectations, they exceed them with secure pairing, 128-bit authentication, and military-grade features, such as 256-bit AFS encryption. Conversations stay private and secure.

Work where you want

With a discreet, easy-to-use DECT wireless adapter, the Savi 7300 UC series is ready to work where you do. Simply plug the adapter into your PC and you are ready to collaborate — in the office, remote, or on the go.

Interference-free audio

With 2x better density than other DECT™ headsets, more people in shared spaces benefit from wireless headsets with clear, interference-free audio. IT can deploy more Savi 7300 Office Series compared to other DECT™ headsets without concern.

Features

Keep conversations private

Make sure nearby conversations are not overheard. The noise-canceling microphone enhanced with Poly Acoustic Fence technology ensure private conversations stay private.

DECT™ security standards

Designed to meet the highest-level DECT™ Security Step C enhanced with military-grade FIPS 140-2 listed features, such as 256-bit AES encryption.^[2]

Meet enterprise security needs

Ideal for use in financial, medical, and government environments, where Bluetooth® technology is typically banned.

Remote management

Stay in control with remote device management for settings, firmware, and security updates.

Roaming range

Give users more freedom to move with a line-of-sight wireless range of up to 450 ft / 137 m.

Training made easy

Make training and collaboration easy with the ability to conference up to 4 headsets on the D400 dongle.

[2] DECT security standards can be found on <https://etsi.org>.

Specifications

Audio	Noise cancellation with Acoustic Fence technology; Microsoft Teams Open Office certified; Up to 2x more density than other DECT™ headsets; Adaptive power control to maximize user density
Weight	120 g
Weight	0.26 lb
Package dimensions (W x D x H)	185 x 210 x 115 mm
Package weight	300 g
Battery life	Up to 13 hours (talk time); Up to 52 hours (standby time)
Special features	Adjustable headband
Minimum System Requirements	USB Type-A port; USB Type-C® port
UPC number	197497838206
Manufacturer Warranty	Poly standard two-year limited warranty
What's in the box	Charging stand; Wireless headset; USB Type-A charging cable; Travel case; USB Type-A to USB Type-C® adapter; D400 USB Type-A DECT™ adapter

Additional specifications

Acoustic protection technology	SoundGuard Digital ^[1,2]
Battery type	Rechargeable Li-ion polymer
Button user controls	Call answer/end; Mute; Volume +/-; Power on/off
Cartons per layer	10
Cartons per pallet	80
Certified collaboration software	Microsoft Teams
Charge time	2 hours
Charging plug	USB Type-C® to USB Type-A; USB Type-C® to USB Type-C®
Color	Black
Compatible Operating Systems	Windows 11; Windows 10; macOS
Connection type	DECT™
Country of origin	Made in Mexico
ECCN	5A992
Ear cushions	Artificial leather (surface material)
HTS code	8517620090
Indicator light	On call
Management Software	Poly Lens
Multiple order quantity	5
Package dimensions (W x D x H)	7.48 x 8.26 x 2.16 in
Package weight	0.66 lb
Pallet (layers)	8
Pallet dimensions	40 x 48 x 58.66 in
Pallet dimensions (W x D x H)	101.6 x 121.9 x 149 cm
Pallet weight	357 kg
Pallet weight	787.05 lb
Products per pallet	400
Products per pallet layer	50
Speaker bandwidth	20 Hz to 20 kHz (multimedia mode); 100 Hz to 6.8 kHz (wideband mode)
UNSPSC code	43191638
Voice alerts	Volume maximum; Volume minimum; Mute on; Mute off; Muted; Connection status; Talk time; Battery low
Wireless range	Up to 137 m in open area; Up to 40 m in typical office environment
Wireless range (imperial)	Up to 450 ft in open area; Up to 130 ft in typical office environment

[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA).

[2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.

Services

Poly Services

★ : Recommended

Poly Support Services

3 year Poly+ Savi Service	PSAVI312 ★
3 year Next Business Day Hardware Advance Replacement Savi Poly DaaS Service	DSAVIDS3
3 year Partner Poly+ Savi Service	PSAVI362

Hybrid Work Solutions

Audio

★ : Recommended

Audio Accessories

PLY Savi D400 -M D1 Dngl	8L552AA	
PLY Savi D400 D1 Dngl	8L550AA	
Poly APA-23 Electronic Hookswitch TAA	85Q50AA	obsolete
Poly APA-24 Electronic Hookswitch TAA	85Q52AA	
Poly APC-43 Electronic Hookswitch (Bagged) TAA	85Q56AA	
Poly APC-43 Electronic Hookswitch TAA	85Q55AA	
Poly APC-45 Electronic Hookswitch TAA	85Q57AA	obsolete
Poly APC-82 Electronic Hookswitch TAA	8H981AA	obsolete
Poly APD-80 Electronic Hookswitch TAA	85Q58AA	
Poly APN-91 Electronic Hookswitch TAA	85Q59AA	
Poly APP-51 Electronic Hookswitch TAA	85Q60AA	
Poly APS-11 Electronic Hookswitch TAA	85Q78AA	
Poly APT-31 Electronic Hookswitch TAA	85Q84AA	obsolete
Poly APU-72 Electronic Hookswitch TAA	85Q95AA	
Poly APU-75D Electronic Hookswitch TAA	85Q99AA	
Poly APU-76 Electronic Hookswitch TAA	85R00AA	
Poly APV-63 Electronic Hookswitch TAA	85R01AA	
Poly APV-66 Electronic Hookswitch TAA	85R02AA	
Poly Blackwire 7225 Case	85Q69AA	obsolete
Poly Busy Light (Angle Plug)	920Q4AA	
Poly EHS 3.5mm to 3.5mm Cable	85R17AA	
Poly HL10 Extended Arm	8L554AA	obsolete
Poly HL10 Handset Lifter	784Q1AA	
Poly HL10 Handset Lifter TAA	8R713AA	
Poly HL10 Handset Lifter with Straight Plug TAA	784Q2AA	
Poly HL10 Lifter Arm +Ring Detector Accessory	8A7E3AA	
Poly RD-1 Electronic Hookswitch	85R71AA	
Poly Savi 7300 Battery with Removal Tool	784P8AA	
Poly Savi 7300 Leatherette Ear Cushion (1 Piece)	783Q7AA	
Poly Savi 7300 Leatherette Ear Cushions (2 Pieces)	783Q8AA	

Poly Savi 7310 Monaural DECT 1880-1900 MHz Top	8Y9B6AA
Poly Savi 7310 Monaural DECT 1920-1930 MHz Top	783N0AA
Poly Savi 7310 Monaural Microsoft Teams Certified DECT 1880-1900 MHz Top	8Y9B8AA
Poly Savi 7310 Monaural Microsoft Teams Certified DECT 1893-1906 MHz Top	9V8Z7AA
Poly Savi 7310 Monaural Microsoft Teams Certified DECT 1920-1930 MHz Top	783N2AA
Poly Savi 7320 Stereo DECT 1880-1900 MHz Top	8Y9B7AA
Poly Savi 7320 Stereo DECT 1893-1906 MHz Top	9V8Z6AA
Poly Savi 7320 Stereo DECT 1920-1930 MHz Top	783N1AA
Poly Savi 7320 Stereo Microsoft Teams Certified DECT 1880-1900 MHz Top	8Y9B9AA
Poly Savi 7320 Stereo Microsoft Teams Certified DECT 1893-1906 MHz Top	9V8Z8AA
Poly Savi 7320 Stereo Microsoft Teams Certified DECT 1920-1930 MHz Top	783N3AA
Poly Savi 7410/7420 Office Charging Cradle	8L556AA
Poly Savi 8400/7400 Office DECT 1880-1900 MHz Base	8L569AA
Poly Savi 8400/7400 Office DECT 1920-1930 MHz Base	8L571AA
Poly Savi 8400/7400 Office Microsoft Teams Certified DECT 1880-1900 MHz Base	8L558AA
Poly Savi 8400/7400 Office Microsoft Teams Certified DECT 1920-1930 MHz Base	8L562AA
Poly Savi 8410/8420 Office Charging Cradle	8L573AA
Poly Savi 8440/8445 Office Charging Cradle	8L577AA
Poly Savi D400 UC DECT 1880-1890 MHz Dongle	8J8V9AA
Poly Savi D400 UC DECT 1880-1900 MHz Dongle	8J8V7AA
Poly Savi D400 UC DECT 1893-1906 MHz Dongle	8J8V6AA
Poly Savi D400 UC DECT 1910-1920 MHz Dongle	8J8V8AA
Poly Savi D400 UC DECT 1920-1930 MHz Dongle	85T33AA
Poly Savi D400 UC Microsoft Teams Certified DECT 1880-1900 MHz Dongle	8J8W1AA
Poly Savi D400 UC Microsoft Teams Certified DECT 1893-1906 MHz Dongle	8J8W0AA
Poly Savi D400 UC Microsoft Teams Certified DECT 1910-1920 MHz Dongle	8J8W2AA
Poly Savi D400 UC Microsoft Teams Certified DECT 1920-1930 MHz Dongle	85T34AA
Poly Savi Office Power Supply with Right Angled Plug -9V 1000mA	8L5A2AA
Poly Savi Office S2 Telephone Cable	85R55AA
Poly Savi Office Straight Plug Online Indicator	85R52AA
Poly Savi Office Telephone Interface Cable	85R57AA
Poly Savi Office Universal AC Power Supply with Straight Plug -9V 1000mA	85R59AA
Poly USB-A to USB-C Adapter	85Q48AA

Poly USB-C to USB-A Adapter	85Q49AA
Poly Voyager USB-A Charging Stand	783R6AA
Poly Voyager USB-C Charging Stand	783R7AA

Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Oct 18, 2024 10:37 PM UTC+0000