



## SPECIFICATIONS

<b>PANEL SIZE</b>	34"
<b>PANEL RESOLUTION</b>	3440 x 1440 (UWQHD)
<b>REFRESH RATE</b>	120Hz
<b>RESPONSE TIME</b>	1ms (MPRT) / 4ms (GtG)
<b>PANEL TYPE</b>	VA
<b>BRIGHTNESS (NITS)</b>	300 cd/m <sup>2</sup>
<b>VIEWING ANGLE</b>	178°(H) / 178°(V)
<b>ASPECT RATIO</b>	21:9
<b>CURVATURE</b>	1500R
<b>CONTRAST RATIO</b>	3500:1
<b>ADOBE RGB / DCI-P3 / SRGB</b>	92% / 95% / 119%
<b>ACTIVE DISPLAY AREA (MM)</b>	797.22 (H) x 333.72 (V)
<b>PIXEL PITCH (H X V)</b>	0.23175 (H) x 0.23175 (V)
<b>SURFACE TREATMENT</b>	Anti-Glare
<b>DISPLAY COLORS</b>	1.07B
<b>COLOR BIT</b>	10 bits (8bits + FRC)
<b>HDR SUPPORT</b>	HDR Ready
<b>VIDEO PORTS</b>	2x HDMI™ 2.0b (UWQHD@100Hz) 1x DisplayPort 1.4a 1x Type-C (DP Alt.) w/ 98W PD
<b>USB Ports</b>	1x USB 5Gbps Type-B 2x USB 5Gbps Type-A
<b>AUDIO PORTS</b>	1 x Headphone-out
<b>KENSINGTON LOCK</b>	Yes
<b>SPEAKER</b>	2x 3W
<b>VESA MOUNTING</b>	75 x 75 mm
<b>POWER TYPE</b>	External Adaptor 19V 9.47A
<b>POWER INPUT</b>	100~240V, 50~60Hz
<b>DYNAMIC REFRESH RATE TECHNOLOGY</b>	Adaptive-Sync
<b>ADJUSTMENT (TILT)</b>	-5° ~ 20°
<b>ADJUSTMENT (SWIVEL)</b>	-30° ~ 30°
<b>ADJUSTMENT (PIVOT)</b>	-5° ~ 5°
<b>ADJUSTMENT (HEIGHT)</b>	0 ~ 110 mm
<b>DIMENSION (W X H X D)</b>	808.6 x 424.1 x 250.6 mm (31.83 x 16.70 x 9.87 inch)
<b>CARTON DIMENSION (W X H X D)</b>	945 x 510 x 245 mm (37.2 x 20.1 x 9.7 inch)
<b>WEIGHT (NW / GW)</b>	8.05 kg (17.81 lbs) / 11.9 kg (26.23 lbs)

## FEATURES

- UWQHD (3440 x 1440)**  

 Game titles will even look better, displaying more details due to the WQHD (3440 x 1440) resolution.
- Curved 1500R**  

 Bring an immersive & comfortable viewing experience to eliminate distortion and cover a wider field of view
- 120Hz High Refresh Rate**  

 Enjoy the high-quality entertainment with a smoother and flicker-free images.
- Type C Display**  

 Allows you to connect the latest devices more conveniently and with less trouble.
- KVM Function Support**  

 Control multiple devices via one set of keyboard, mouse, and MSI monitor.
- PIP / PBP Mode**  

 PIP/PBP mode provide a better efficiency for creators when need it
- EyesErgo**  

 An eye care solution designed with ergonomics in mind.
- Built-In Speaker**  

 Built-in speakers allow you to listen clearly without connecting external speakers.

## Modern MD342CQP

BE YOUR WINDOW TO THE WORLD

<b>CERTIFICATES</b>	CB/CE PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook
<b>VIDEO INPUT COMPATIBILITY</b>	*All trademarks and the registered trademarks are the property of their respective owners.
<b>ACCESSORIES</b>	1x DisplayPort 1.2a cable, 1x USB 3.2 Gen 1 Type-B to A cable, 1x Power Adaptor, 1x Power Cord, 1x Quick Guide, 4x VESA Wall Mount Screws
<b>Note</b>	HDMI™: 3440 x 1440 (Up to 100Hz) DisplayPort: 3440 x 1440 (Up to 120Hz) Type-C: 3440 x 1440 (Up to 120Hz) HDMI™ CEC Support Adobe RGB, DCI-P3 and sRGB follow CIE1976 Standard

## CONNECTIONS



1. 1x DC Jack
2. 1x Headphone-out
3. 2x HDMI 2.0b
4. 1x DisplayPort 1.4a
5. 1x Type-C (DP Alt.) w/ 98W PD
6. 1x USB 5Gbps Type-B
7. 2x USB 5Gbps Type-A
8. 1x Kensington Lock
9. OSD Button