

TECRA® A60-M

PNL11U-15C011

GIVE YOUR WORKFLOW AN AI BOOST

Elevate organizational efficiency with the 16-inch Tecra® A60-M, featuring powerful hardware, AI productivity tools, a generous 16:10 display, and advanced security measures for empowering teams with modern tools for maximum success.



SUPERIOR PERFORMANCE & EFFICIENCY

Delivering unprecedented speed and efficiency, the Tecra® A60 features Intel® Core™ Ultra processors with a Neural Processing Unit and Intel® Arc™ graphics for accelerated performance and enhanced battery life.



A CLEAN STYLISH DESIGN

Features a stylish Dark Metallic Blue chassis that stands out from a sea of monochromatic competitors, and an antimicrobial-coated (IONPURE® IPL) base, lid and palm rest a to inhibit the growth of bacteria.



CONNECT AT SUPERHERO SPEEDS

Stay connected with Wi-Fi 6E and a comprehensive selection of ports, including HDMI, Thunderbolt 4, USB Type-A, and a microSD card slot, ensuring you have all the connections you need.



A STUNNING VISUAL EXPERIENCE

Experience the vibrant new 16-inch WUXGA display with a 16:10 aspect ratio, (touch optional), providing crisp and clear visuals for a more engaging work and entertainment experience.



MASTERING THE HYBRID WORKPLACE

The Tecra® A60-M's 5MP AI-enhanced webcam, dual microphones, and upgraded audio system with DTS processing make it perfect for clear, productive video conferencing.



MEET YOUR PRODUCTIVITY WINGMAN

Microsoft Copilot, accessible via a dedicated key, streamlines tasks, like launching apps and adjusting system settings, through voice or text commands, enhancing efficiency and device navigation.



Laptops That Defend Against Cyber Threats



Dynabook's Windows 11 Secured-core PC laptops offer advanced security by integrating robust hardware and software defenses into their core components. These laptops provide a fortified shield against sophisticated cyber threats, employing specialized hardware protections and firmware safeguards. They ensure unparalleled security from boot-up, defending against malware and firmware attacks to safeguard critical data and uphold the integrity of business operations.



PLATFORM SPECIFICATIONS AND CONFIGURABLE OPTIONS

Operating System*

- Windows 11 Pro

Processor*

- Intel® Core™ Ultra 5 (Series 1) 125U

Memory*

- 16GB DDR5 (Field upgradable)

Graphics

- Intel® Arc™ Graphics

Display*

- 16.0" WUXGA (1920x1200)

Storage*

- 512GB PCIe NVMe SSD

Communications

- Intel® Ethernet Connection i219
- Intel® Wi-Fi 6E AX211, 6 GHz, 802.11ax
- Bluetooth™

Camera w/ Privacy Shutter*

- 5MP Webcam with Dual-Microphones

Audio

- Stereo Speakers w/ DTS Processing
- Dual-microphone array

Ports

- HDMI®
- Two (2) USB-C ports supporting Thunderbolt 4
- Two (2) USB 3.2 Gen 1 Type-A ports
 - One supporting USB Sleep & Charge
- RJ-45 Ethernet LAN port
- Headset jack (3.5mm combo port)
- microSD™ card slot

Security*

- Microsoft Secured-core PC
- Trusted Platform Module 2.0
- Fingerprint Reader
- Security Lock Slot

Input Devices

- Premium Raised-tile, Spill-resistant, Backlit Keyboard with 10-Key
- ClickPad Pointing Device

Battery

- 60 Wh Li-Polymer Battery

Physical Description

- Dark Blue Metallic
- Polycarbonate ABS Chassis
- Designed to MIL-STD-810H standards
- 357 x 248.9 x 19.9 millimeters
- Starting at 1.69 kilograms (3.73 pounds)¹

Regulatory / Environmental Specifications

- EPEAT® Rated
- ENERGY STAR® Qualified
- RoHS Compatible

Warranty*

- 3-Year Standard Limited Warranty²

Optional Accessories

- PS0120UA1PRP – Dynabook Thunderbolt™ 4 Dock
- PA5356U-IPRP – Dynabook USB-C® Dock
- PS0001UA1PRP – USB-C® to HDMI® / VGA / LAN / USB 3.0 Adapter with Power Delivery (PD) Charging
- PS0089UA1PRP – USB-C® to VGA / LAN Adapter with Power Delivery (PD) Charging
- PA5270U-IPRP – USB-C® to VGA Adapter with Power Delivery (PD) Charging
- PA5352U-1ACA – 65W USB-C® AC Adapter (5V / 9V / 15V / 20V)


1. Weight. Weight may vary depending on product configuration, vendor components, manufacturing variability and options selected.
2. Warranty. Dynabook's standard limited warranty terms and limitations apply. Visit www.support.dynabook.com/warranty for details.



Service Warranty with On-Site

+Care Service® Warranty with On-Site

Tecra laptops are backed by one of the best standard warranties in the business. For even greater peace of mind, Dynabook's industry-leading +Care Service® Warranty with On-site can be added for worry-free reliability with up to four years of coverage. With comprehensive warranty coverage and access to a vast service and support network, Dynabook helps businesses minimize downtime, reduce IT costs, and ensure uninterrupted productivity.



* Based on Configuration

** Visit <http://us.dynabook.com/info> for a complete list of all product legal footnotes