



SPECIFICATIONS

Panel Size	31.5"
Active Display Area (mm)	697.344 (H) x 392.256 (V)
Curvature	Curve 1000R
Panel Type	Rapid VA
Panel Resolution	2560 x 1440 (WQHD)
Pixel Pitch (H x V)	0.2724 (H) x 0.2724 (V)
Aspect Ratio	16:9
Brightness (nits)	300 (Typ.)
Contrast Ratio	3500:1 (Typ.)
DCR	100000000:1
Signal Frequency	86.26~433.33 KHz (H) / 48~240 Hz (V)
ACTIVATED RANGE	48~240Hz
Refresh Rate	240Hz
Response time	0.5ms (GtG, Min.)
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive-Sync
HDR Support	HDR Ready
Video ports	1x DisplayPort 1.4a 2x HDMI™ 2.0b (WQHD@144Hz) 1x Type-C (DP alt.) w/ 15W PD
Audio ports	1 x Headphone-out
Viewing Angle	178°(H) / 178°(V)
Adobe RGB / DCI-P3 / sRGB	92% / 96% / 123%
Surface Treatment	Anti-glare
Display Colors	1.07B, 10 bits (8 bits + FRC)
Frameless Design	Yes
PIP / PBP Function	Yes
Power Type	Internal Power Board
Power Input	100~240V, 50/60Hz
Adjustment (Tilt)	-5° ~ 15°
Adjustment (Swivel)	-30° ~ 30°
Adjustment (Height)	0~100 mm
Kensington Lock	Yes
VESA Mounting	100 x 100 mm
Dimension with Stand (W x D x H)	704.62 x 280.98 x 467.02 mm (27.74 x 11.06 x 18.39 inch)
Dimension without Stand (W x D x H)	704.62 x 143.45 x 422.35 mm (27.74 x 5.65x 16.63 inch)

FEATURES

- Curved Gaming**
MSI Curved Gaming Monitor will give you the most immersive and competitive edge you need to take down your opponents.
- Rapid VA Panel**
Make sure the intensity and purity of colors when gaming.
- 240Hz High Refresh Rate**
Experience smooth gaming with a blazing-fast refresh rate, providing you with the upper hand in fast-moving games.
- 0.5ms (GtG, Min.) Response Time**
Eliminate screen tearing and choppy frame rates with 0.5ms (GtG, Min.) Response Time.
- HDR Ready**
Enhance eye-catching details through adjustments in contrast and shadows.
- Adjustable Stand**
Through adjustments of tilting, lowering and raising, and swiveling, easily change the position of the monitor for maximum ergonomics and optimum viewing experiences.
- USB Type-C Power Delivery 90W**
Built-in an USB Type-C connection with 90W power delivery allows you to effortlessly connect to and charge your devices.

Weight (NW / GW)	7.78 kg (17.15 lbs) / 10.9 kg (24.03 lbs)
Dimension (W x D x H)	704.62 x 280.98 x 467.02mm 704.62 x 143.45 x 422.35mm(without stand)
Carton Dimension (W X D X H)	959 x 198 x 520 mm (37.76 x 7.8 x 20.48 inch)
Accessories	1x DisplayPort Cable (1.4a), 1x Power Cord (C13), 1x Quick Guide, 2x Stand Screw, 4x VESA Wall Mount Screw
Note	DisplayPort: 2560 x 1440 (Up to 240Hz) HDMI™: 2560 x 1440 (Up to 144Hz) Type-C: 2560 x 1440 (Up to 240Hz) Support: HDMI™ CEC, PIP/PBP ; Non Support: KVM

CONNECTIONS



1. 5-Way Joystick Navigator
2. DC-in
3. Earphone out
4. DisplayPort 1.4a
5. 2 x HDMI™
2.0b(WQHD@144Hz)
6. USB Type-C (PD 65W)
7. USB 2.0 Type-B
8. 2 x USB 2.0 Type-A
9. Kensington Lock