



## V7 23.8" FHD 1920x1080 IPS LED Monitor

### L238V1-N

SKU: NK2736

The V7 23.8-inch FHD IPS LED monitor offers a vibrant 1920x1080 resolution for clear and detailed visuals. The IPS panel delivers wide viewing angles with accurate colors, while the 16.7 million colors bring images to life. Equipped with FreeSync technology, the monitor eliminates screen tearing and stuttering for smooth gameplay. With a bright 250 nit brightness and a fast 5ms response time, it handles demanding tasks with ease. The 100 Hz refresh rate provides fluid motion, making it ideal for gaming and multimedia. Connectivity options include HDMI, VGA, and DisplayPort, ensuring compatibility with various devices. Built-in speakers add convenience, while the sleek design complements any workspace.

- 1920 x 1080 Full HD Resolution for an excellent viewing experience
- Wide viewing angle 178°(H) / 178°(V) with IPS Panel Technology, ensures visibility in every viewing angle
- Several connectivity options such as VGA, HDMI and DisplayPort with HDMI Cables Included
- Suitable for VESA Mount pattern 100x100 for added desk-space
- 100Hz Refresh Rate for smoother graphics

#### General

Sku: NK2736  
 Model: L238V1-N  
 EAN: 0662919122022  
 Warranty: 3 years  
 Compliance: CE, Energy Star, FCC, RoHS, UKCA, WEEE  
 Country Of Origin: China  
 Package Type: One Color  
 SAP: 6292598  
 Package Includes: Monitor, DisplayPort cable, HDMI cable, Adapter 12V 2.5A, Stand

#### Color

Color: Black

#### Design

Monitor Feature: Fixed Stand

#### Package Dimensions

Package Dimensions (L/W/H): 59 x 9.5 x 41.6 cm (23.23 x 3.74 x 16.38 in)  
 Shipping Weight: 3.5 kg (7.72 lbs)  
 Package Weight: 3.5 kg (7.72 lbs)

#### Product Dimensions

Product Dim (L/W/H): 54.2 x 15.1 x 40.2 cm (21.34 x 5.94 x 15.83 in)  
 Product Weight: 2.6 kg (5.73 lbs)

#### California Prop 65

No warning required

#### Technical

MTBF: 30,000 hrs  
 Viewable Screen Size: 23.8 in  
 Panel Type: IPS  
 Power Input: 30W (12V 2.5A)  
 Tilt: -5°~15°  
 Aspect Ratio: 16:9  
 Response Time: 5 ms  
 Viewing Angle: 178°H / 178°V  
 Maximum Resolution: 1920 x 1080  
 Screen Coating: Matte  
 Brightness: 250 nits  
 Color Depth: 16.7 million colors  
 Contrast Ratio: 1000:1  
 Swivel: -12°~12°  
 Input Port: Audio 3.5mm, DisplayPort, HDMI, VGA  
 VESA Mount: 100 x 100 mm  
 Input AC Plug Type: NEMA 5-15P (US)  
 Refresh Rate: 100Hz  
 Stand: 21.86 x 15.0 x 12.8 cm (8.61 x 5.91 x 5.04 in)  
 Speaker: 2 x 2W  
 Monitor Dim (w/o Stand): 54.2 x 4.2 x 31.7 cm (21.34 x 1.65 x 12.48 in)  
 Pixel Pitch (H/V): 0.2745 x 0.2745mm  
 Display Area (H x L): 29.6 x 52.7 cm (11.67 x 20.74 in)