

ViewSonic® LCD DISPLAY VG2748A-2K

Key Features

- QHD resolution (2560 x 1440) for sharp detail and clarity
- 100Hz refresh rate ensures smooth, fluid visual performance
- USB 3.2 hub with 1 upstream and 4 downstream ports, HDMI, DisplayPort, and VGA inputs for versatile connectivity
- Intelligent sensing technology with built-in sensors and 7 adaptive modes designed to enhance energy efficiency, productivity, privacy, and well-being
- Ergonomic stand with tilt, swivel, pivot, and height adjustment for personalized comfort



Product Description

The **ViewSonic VG2748A-2K** is a 27-inch QHD (2560 x 1440) business monitor designed to elevate productivity, comfort, and energy efficiency in modern workspaces. It features seven intelligent sensing modes that enhance viewing comfort, protect privacy, and support user well-being throughout the workday. A fully adjustable ergonomic stand allows for optimal positioning with tilt, swivel, pivot, and height adjustments. Equipped with a USB 3.2 hub (1 USB-B upstream, 3 USB-A, and 1 USB-C downstream with 15W power delivery), along with HDMI, DisplayPort, and VGA inputs, the VG2748A-2K ensures seamless device connectivity. vDisplay Manager and vSplit software provide enhanced screen management, while the ViewSonic Display Portal supports convenient software access and updates. Designed with sustainability in mind, the monitor meets EPEAT Silver and Energy Star 8.0 certifications and comes in eco-friendly packaging, reducing environmental impact without compromising performance.



1. Menu Control Panel
2. USB 3.2 Downstream (Type A*2)
3. Speakers
4. VESA Compatible(Wall Mount 100 x 100mm)
5. Power In
6. HDMI
7. DisplayPort
8. VGA
9. USB 3.2 Upstream (Type B)
10. USB 3.2 Downstream (Type A)
11. USB 3.2 Downstream (Type C)

Visit Us www.viewsonic.com

DISPLAY

Display Size (in.):	27
Viewable Area (in.):	27
Panel Type:	IPS Technology
Resolution:	2560 x 1440
Resolution Type:	QHD (Quad HD)
Static Contrast Ratio:	1,300:1 (typ)
Dynamic Contrast Ratio:	50M:1
Light Source:	LED
Brightness:	350 cd/m ² (typ)
Colors:	16.7M
Color Space Support:	8 bit true
Aspect Ratio:	16:9
Response Time (Typical GTG):	5ms
Response Time (GTG w/OD):	5ms
Viewing Angles:	178° horizontal, 178° vertical
Backlight Life (Hours):	30000 Hrs (Min)
Curvature:	Flat
Refresh Rate (Hz):	100
Low Blue Light:	Hardware solution
Flicker-Free:	Yes
Color Gamut:	NTSC: 76% size (Typ) sRGB: 108% size / 99% coverage (Typ)
Pixel Size:	0.233 mm (H) x 0.233 mm (V)
Surface Treatment:	Anti-Glare, Hard Coating (3H)

COMPATIBILITY

PC Resolution (max):	2560x1440
Mac® Resolution (max):	2560x1440
PC Operating System:	Windows 10/11 certified; macOS tested
Mac® Resolution (min):	2560x1440

CONNECTOR

VGA:	1
USB 3.2 Type A Down Stream:	3
USB 3.2 Type B Up Stream:	1
USB 3.2 Type C Down stream:	1 (15W power charger)
HDMI 2.0:	1
DisplayPort:	1
Power in:	3-pin Socket (IEC C14 / CEE22)

AUDIO

Internal Speakers:	2Watts x2
--------------------	-----------

POWER

Eco Mode (Conserve):	25.1W
Eco Mode (optimized):	28.5W
Consumption (typical):	33W
Consumption (max):	36.6W
Voltage:	AC 100-240V
Stand-by:	0.5W
Power Supply:	Internal Power Supply

ADDITIONAL HARDWARE

Kensington Lock Slot:	1
Cable Organization:	Yes

CONTROLS

Physical Controls:	Key 1 (auto-dimmer), Key 2, Key 3, Key 4, Key 5, Key 6 (power)
On Screen Display:	Input Select, Intelligent Sensing, ViewMode, Color Adjust, Manual Image Adjust, Setup Menu

OPERATING CONDITIONS

Temperature:	32°F to 104°F (0°C to 40°C)
Humidity (non-condensing):	20% to 90%

WALL MOUNT

VESA Compatible:	100 x 100 mm
------------------	--------------

INPUT SIGNAL

Frequency Horizontal:	RGB Analog: 31 ~ 80KHz, HDMI (v2.0): 31 ~ 150KHZ, DisplayPort (v1.2): 31 ~ 150KHz
Frequency Vertical:	RGB Analog: 50 ~ 75Hz, HDMI (v2.0): 50 ~ 100Hz, DisplayPort (v1.2): 50 ~ 100Hz

VIDEO INPUT

Digital Sync:	TMDS - HDMI (v2.0), PCI-E - DisplayPort (v1.2)
Analog Sync:	Separate/Composite/SOG - RGB Analog

ERGONOMICS

Height Adjust (mm):	130
Swivel:	120°
Tilt (Forward/Back):	-5° / 40°
Pivot (Right/Left):	90° / 90°

WEIGHT (IMPERIAL)

Net (lbs):	15.5
Net Without Stand (lbs):	10.5
Gross (lbs):	21.9

WEIGHT (METRIC)

Net (kg):	7.1
Net Without Stand (kg):	4.8
Gross (kg):	9.9

DIMENSIONS (IMPERIAL) (WXHXD)

Packaging (in.):	27.2 x 16.9 x 8.6
Physical (in.):	24.15 x 15.99~21.01 x 7.96
Physical Without Stand (in.):	24.15 x 14.28 x 2.03

DIMENSIONS (METRIC) (WXHXD)

Packaging (mm):	692 x 430 x 218
Physical (mm):	613.38 x 406.19~533.75 x 202.18
Physical Without Stand (mm):	613.38 x 362.73 x 51.5

GENERAL

Regulations:	cTUVus, FCC-B, ICES003, Energy Star, EPEAT, CEC, NOM, Mexico Energy, CE, CE EMC, CB, RoHS, ErP, REACH, WEEE, EAC, UkrSEPRO
PACKAGE CONTENTS:	VG2748A-2K x1, 3-pin Plug (IEC C13 / CEE22) x1, DisplayPort Cable (v1.2; Male-Male) x1, USB A/B Cable (v3.2; Male-Male) x1, Quick Start Guide x1
Recycle/Disposal:	Please dispose of in accordance with local, state or federal laws.
Warranty:	*Warranty offered may differ from market to market
Power Management:	Energy Star standards, EPEAT