

## PERFORMANCE

### Processor

Intel® Core™ Ultra 7 255H, 16C (6P + 8E + 2LPE) / 16T, Max Turbo up to 5.1GHz, 24MB

### AI PC Category<sup>[1]</sup>

AI PC

### NPU

Integrated Intel® AI Boost, up to 13 TOPS

### Graphics<sup>[2]</sup>

Integrated Intel® Arc™ 140T GPU Functions as Intel® Graphics

### Chipset

Intel® SoC Platform

### Memory

1x 16GB SO-DIMM DDR5-5600

### Memory Slots

Two DDR5 SO-DIMM slots, dual-channel capable

### Max Memory

Up to 64GB DDR5-5600

### Storage

512GB SSD M.2 2242 PCIe® 4.0x4 NVMe® Opal 2.0

### Max Storage Support

Up to two drives, 2x M.2 SSD

- M.2 2242 SSD up to 1TB
- M.2 2280 SSD up to 1TB

### Storage Slot

Two M.2 slots

- One M.2 2242 PCIe® 4.0 x4 slot
- One M.2 2280 PCIe® 4.0 x4 slot

### Card Reader

No card reader

### Audio Chip

High Definition (HD) Audio, Senary SN6147 codec

### Speakers

Stereo speakers, 2W x2, Dolby Atmos®, audio by HARMAN

### Camera

FHD 1080p + IR Hybrid with Privacy Shutter

### Microphone

2x, Array

### Battery

48Wh

### Power Adapter

65W USB-C® (2-pin)

## DESIGN

### Display<sup>[3]</sup>

14" WUXGA (1920x1200) IPS 300nits Anti-glare, 45% NTSC, 60Hz, Touch

### Touchscreen

Add-on Film Touch, 10-point Multi-touch

### Keyboard

Backlit, English

### Case Color

Black

### Case Material

Aluminium (Top), Aluminium (Bottom)

### Pen

Pen Not Supported

### Dimensions (WxDxH)<sup>[4]</sup>

313 x 220.3 x 10.1/15.25 (front/rear), 19.7 (maximum) mm;  
12.32 x 8.67 x 0.40/0.60 (front/rear), 0.78 (maximum) inches

### Weight<sup>[5]</sup>

Starting at 1.34 kg (2.95 lbs)

## SOFTWARE

### Operating System

Windows® 11 Pro, English (US) / English (UK)

### Bundled Software

None

## CONNECTIVITY

### WLAN + Bluetooth<sup>[6]</sup>

Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3

### WWAN

Non-WWAN

### SIM Card

None

### Ethernet

100/1000M (RJ-45)

### NFC

None

### Standard Ports

- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-A (USB 10Gbps / USB 3.2 Gen 2), Always On
- 1x USB-C® (USB 20Gbps / USB 3.2 Gen 2x2), with USB PD 3.1 and DisplayPort™ 1.4
- 1x USB-C® (Thunderbolt™ 4 / USB4® 40Gbps), with USB PD 3.1 and DisplayPort™ 2.1
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Ethernet (RJ-45)

### Docking

Various docking solutions supported via Thunderbolt™ or USB-C®.

For more compatible docking solutions, please visit [Docking for ThinkPad® E14 Gen 7 \(Intel®\)](#)

## SECURITY & PRIVACY

### Smart Card Reader

None

### Security Chip

Discrete TPM 2.0 Enabled

### Fingerprint Reader

Touch Style, Match-on-Chip, Integrated in Power Button

### Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

### Other Security

- Camera privacy shutter
- IR camera for Windows® Hello (facial recognition)

## MANAGEABILITY

### System Management

Non-vPro®

## SERVICE

### Base Warranty

1-year, Courier or Carry-in

### Included Upgrade

None

## ACCESSORIES

### Bundled Accessories

None

## CERTIFICATIONS

### Green Certifications<sup>[7]</sup>

- ENERGY STAR® 9.0
- EPEAT™ Gold Registered
- ErP Lot 6/26
- RoHS compliant
- TCO Certified 10.0

### Other Certifications

TÜV Rheinland® Low Blue Light (Software Solution)

### Mil-Spec Test

MIL-STD-810H military test passed

## MODEL

**TopSeller** : Yes **Announce Date** : 2025-06-10

**EAN / UPC / JAN** : 198157338630 **End of Support** : N/A

• Lenovo reserves the right to change specifications without notice.  
• California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please access the [web page](#).

## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### Lenovo 65W USB-C DC Travel Adapter

40AK0065WW

Power up and stay productive on the road with this DC Travel adapter. Lenovo 65W USB-C DC Travel Adapter is the universal DC adapter, providing 65W power via USB-C for outdoor use.

## Recommended Services

BEST	3Y Premier Support Plus upgrade from 1Y Courier/Carry-in (5WS1L39180)
BETTER	3Y Premier Support Upgrade from 1Y Courier/Carry-in (5WSOT36151)
GOOD	3Y Onsite upgrade from 1Y Courier/Carry-in (5WSOA23681)

Please click [here](#) to view the full list of accessories.



**PSREF**  
Product Specifications  
Reference