

## PERFORMANCE

### Processor

Intel® Core™ Ultra 7 255H, 16C (6P + 8E + 2LPE) / 16T, Max Turbo up to 5.1GHz, 24MB

### AI PC Category

AI-Ready Workstations

### NPU

Integrated Intel® AI Boost, up to 13 TOPS

### Graphics

NVIDIA® RTX PRO 2000 Blackwell Generation 8GB GDDR7 Laptop GPU

### Chipset

Intel® SoC Platform

### Memory

32GB LPCAMM2 LPDDR5x-7467

### Memory Slots

One LPCAMM2 connector, dual-channel

### Max Memory

Up to 64GB (1x 64GB LPCAMM2), upgradable

### Storage

1TB SSD M.2 2280 PCIe® 5.0x4 Performance NVMe® Opal 2.0

### Storage Slot

Two M.2 2280 PCIe® 4.0 x4 slots

### Max Storage Support<sup>[1]</sup>

Up to two M.2 2280 Gen 5 Performance SSD; up to 8TB, 4TB each

### Card Reader

SD Express 7.0 Card Reader

### Audio Chip

SoundWire®, Cirrus Logic® CS42L43 codec

### Speakers

Stereo speakers, 2W x2, Dolby Atmos®

### Microphone

2x, Array

### Camera

5.0MP + IR with Privacy Shutter and Computer Vision Human Presence Detection on ISP

### Battery

90Wh

### Power Adapter

140W USB-C® GaN (3-pin)

## DESIGN

### Display

16" WQUXGA (3840x2400) IPS 800nits Anti-glare, 100% DCI-P3, 60Hz, DisplayHDR™ 400, Dolby Vision®, Eyesafe®, TÜV Low Blue Light

### Screen-to-Body Ratio

91.7% (IPS models)

### Color Calibration

X-Rite® Factory Color Calibration

### Pen

Pen Not Supported

### Keyboard

Backlit, English

### Dimensions (WxDxH)<sup>[2]</sup>

354.3 × 241.0 × 9.9 / 15.8 (front / rear), 20.6 (maximum) mm  
13.95 x 9.49 x 0.39 / 0.62 (front / rear), 0.81 (maximum) inches

### Weight<sup>[3]</sup>

Starting at 1.84 kg / 4.06 lbs

### Case Color

Black

### Case Material

Aluminium (Top), Aluminium (Bottom)

## SOFTWARE

### Operating System

Windows® 11 Pro, English (US) / English (UK)

### Bundled Software

Intel® Connectivity Performance Suite + Lenovo® AI Now

## CONNECTIVITY

### WLAN + Bluetooth®

Intel® Wi-Fi® 7 BE201, 802.11be 2x2 + BT5.4

### WWAN

Non-WWAN

### Ethernet

No Onboard Ethernet

### Standard Ports

- 1x USB-A (USB 10Gbps / USB 3.2 Gen 2), Always On
- 2x Thunderbolt™ 5, with USB PD 3.1 140W input / 15W output
- 1x Thunderbolt™ 4, with USB PD 3.1 140W input / 15W output
- 1x HDMI® 2.1, up to 8K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x SD Express 7.0 card reader

## SECURITY & PRIVACY

### Security Chip

Discrete TPM 2.0 Enabled

### Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

### Fingerprint Reader

Touch Style, Match-on-Chip, Integrated in Power Button

### Other Security

- Bottom cover tamper detection
- Camera privacy shutter
- Computer Vision-based User Presence Sensing on Image Signal Processor (ISP)
- IR camera for Windows® Hello (facial recognition)

## MANAGEABILITY

### System Management

Non-vPro®

## SERVICE

### Base Warranty

1-year, Courier or Carry-in

### Included Upgrade

1Y Premier Support Upgrade from 1Y Courier/Carry-in

## CERTIFICATIONS

### ISV Certifications

Please visit [ISV certifications for Lenovo® Workstations](#)

### Green Certifications

- ENERGY STAR® 9.0
- EPEAT™ Gold Registered
- RoHS compliant
- TCO Certified, generation 10

### Mil-Spec Test

MIL-STD-810H military test passed

### Other Certifications

- Eyesafe® Certified 2.0
- Intel® Evo™ Platform
- TÜV Rheinland® Low Blue Light

## MODEL

**TopSeller** : Yes **Announce Date** : 2025-09-05

**EAN / UPC / JAN** : 199272427773 **End of Support** : 2032-04-25

### Note:

[1] The storage capacity supported is based on the test results with current Lenovo storage offerings.

[2] The system dimensions may vary depending on configurations.

[3] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

• Lenovo reserves the right to change specifications without notice.

• California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please access the [web page](#).

## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### ThinkPad Hybrid USB-C with USB-A Dock (American Standard Plug Type B)

40AF0135US

- The ThinkPad Hybrid USB-C with USB-A dock is a productivity solution for any USB-C or USB-A laptop, including non-Lenovo laptops from Dell, HP, and Apple, providing power, display, and port expansion in any m...



### ThinkPad Thunderbolt 4 Workstation Dock - US

40B00300US

Premium Thunderbolt™ 4 Docking Experience: ThinkPad Thunderbolt 4 Workstation Dock delivers reliable and consistent industry leading video, data and power connectivity; Maximize Your Productivity: Expand your horizon...

Please click [here](#) to view the full list of accessories.

**Lenovo**

**PSREF**  
Product Specifications  
Reference