



## SPECIFICATIONS

<b>PANEL SIZE</b>	27"
<b>PANEL RESOLUTION</b>	1920 x 1080 (FHD)
<b>REFRESH RATE</b>	144Hz
<b>RESPONSE TIME</b>	1ms (MPRT) / 4ms (GtG)
<b>PANEL TYPE</b>	IPS
<b>BRIGHTNESS (NITS)</b>	300 cd/m2
<b>VIEWING ANGLE</b>	178°(H) / 178°(V)
<b>ASPECT RATIO</b>	16:9
<b>CONTRAST RATIO</b>	1500:1
<b>DCR</b>	100000000:1
<b>Signal Frequency</b>	52.85~158.54 KHz(H) / 48~144 Hz(V)
<b>ADOBE RGB / DCI-P3 / SRGB</b>	83% / 87% / 116% (CIE 1976)
<b>ACTIVE DISPLAY AREA (MM)</b>	597.888(H) x 336.312(V)
<b>PIXEL PITCH (H X V)</b>	0.3114(H) x 0.3114(V)
<b>SURFACE TREATMENT</b>	Anti-glare
<b>DISPLAY COLORS</b>	16.7M, 8 bits (6 bits + FRC)
<b>HDR SUPPORT</b>	HDR Ready
<b>VIDEO PORTS</b>	1x HDMI™ 2.0 (FHD@144Hz) 1x DisplayPort 1.2a 1x D-Sub (VGA)
<b>USB Ports</b>	N/A
<b>Audio Interface</b>	1x Line-in 1x Headphone-out
<b>KENSINGTON LOCK</b>	Yes
<b>SPEAKER</b>	2W x2
<b>Webcam</b>	N/A
<b>VESA MOUNTING</b>	100 x 100 mm
<b>POWER TYPE</b>	Internal Power Board
<b>POWER INPUT</b>	100~240V, 50/60Hz
<b>DYNAMIC REFRESH RATE TECHNOLOGY</b>	AMD FreeSync™
<b>ADJUSTMENT (TILT)</b>	-5° ~ 20°
<b>ADJUSTMENT (SWIVEL)</b>	N/A
<b>ADJUSTMENT (PIVOT)</b>	N/A
<b>ADJUSTMENT (HEIGHT)</b>	N/A
<b>Dimension with Stand (W x D x H)</b>	611.7 x 206.8 x 453.1 mm (24.08 x 8.14 x 17.84 inch)

## FEATURES



### IPS Panel with Wide Viewing Angle

Instantly optimize the screen colors and brightness to ensure that you enjoy every detail at its best.



### PerfectEdge

Set-up multi-display immensely with the 4-side edgeless design and enjoy the wider and more immersive view.



### 144Hz Game Ready

Thanks to the high refresh rate and adaptive-sync support, our gaming experience becomes completely smooth and free from interruptions.



### EyesErgo

An eye care solution designed with ergonomics in mind. Includes Eye care & Ergonomic features.



### Eye-Q Check

Help have self-check eyes & remind to take a rest while using the monitor for a long time.



### MSI Power Link

A desktop PC can be powered by an MSI-selected monitor through MSI Power Link technology, enabling the most convenient user experience.



### VESA Mountable

To be mounted on the wall of your office & home with a VESA standard design which can make it completely invisible on a desk.



### Built-In Speaker

Built-in speakers allow you to listen clearly without connecting external speakers.

<b>Dimension without Stand (W x D x H)</b>	611.7 × 51.4 × 355.5 mm (24.08 x 2.02 x 13.0 inch)
<b>CARTON DIMENSION (W X D X H)</b>	688 × 128 × 440 mm (27.09 x 5.04 x 17.32 inch)
<b>WEIGHT (NW / GW)</b>	4 kg (8.82 lbs) / 6.1 kg (13.45 lbs)
<b>CERTIFICATES</b>	CB/CE Energy Star
<b>VIDEO INPUT COMPATIBILITY</b>	PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook * All trademarks and the registered trademarks are the property of their respective owners.
<b>ACCESSORIES</b>	1x HDMI™ Cable (1.4), 1x Quick Guide, 1x Power Cord (C13)
<b>Note</b>	HDMI™: 1920 x 1080 (Up to 144Hz) DisplayPort: 1920 x 1080 (Up to 144Hz) D-Sub (VGA): 1920 x 1080 (Up to 60Hz) Support: HDMITM CEC/ MSI Power Link, FW Update ; Non Support: PIP/PBP, KVM

## CONNECTIONS



1. 5-Way Navi Key
2. AC-in
3. DisplayPort 1.2a
4. 1x HDMI™ 2.0 (FHD@144Hz)
5. 1x D-Sub (VGA)
6. 1x Line-in
7. 1x Headphone-out