

8 Port VGA Video Splitter - 250 MHz

Product ID: ST128L



The ST128L 8 Port VGA Video Splitter allows a single VGA source to display VGA video onto eight monitors simultaneously. Perfect for classrooms, tradeshows, or in-store displays where high quality video on several monitors is needed. The simple plug and play operation makes setup quick and easy so you can be up and running in minutes.

The ST128L supports displays with up to 250 MHz of bandwidth, providing brilliant resolutions up to 1920x1440. A built-in booster circuit lets you situate your displays up to 210 ft away from your source.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Male to Female VGA extension cable required (MXT101HQ)

Certifications, Reports and Compatibility



Applications

- Use for in-store product merchandising in retail environments to give your advertisements greater visibility
- Display travel schedules and alerts in airports, bus terminals and train stations
- Create engaging multimedia presentations for demonstration in lecture halls and classrooms
- Get your message across multiple displays for trade-shows or information booths/kiosks
- Quick and easy solution to split a video signal in an auditorium or house of worship

Features

- Supports resolutions up to 1920x1440
- Supports cable distances up to 65m / 210ft
- Supports Cascading up to 3 levels
- 250 MHz video bandwidth
- Compatible with VGA, SVGA and Multisync monitors

	Warranty	2 Years
Hardware	Daisy-Chain	Yes
	Ports	8
Performance	Bandwidth	250MHz
	General Specifications	Male to Female VGA extension cable required (MXT101HQ)
	Maximum Analog Resolutions	1920x1440
	Maximum Cable Length	213.2 ft [65 m]
Connector(s)	Connector Type(s)	1 - VGA (15 pin, High Density D-Sub) Male 8 - VGA (15 pin, High Density D-Sub) Female
Power	Output Current	0.5A
	Output Voltage	9 DC
	Plug Type	M
	Power Consumption (In Watts)	4.5
	Power Source	AC Adapter Included
Environmental	Humidity	0~90% RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Physical Characteristics	Color	Black
	Product Height	1 in [2.6 cm]
	Product Length	2.6 in [65 mm]
	Product Width	5.2 in [13.1 cm]
	Weight of Product	7.8 oz [221 g]
Packaging Information	Package Height	7.5 in [19 cm]
	Package Length	10.8 in [27.4 cm]
	Package Width	3.2 in [81 mm]
	Shipping (Package) Weight	2.5 lb [1.1 kg]
What's in the Box	Included in Package	1 - 8 Port VGA Splitter 1 - Power Adapter 1 - User Manual

Product appearance and specifications are subject to change without notice.