

Tripp Lite Waber Industrial Power Strip, 6-Outlet, 15 ft. (4.57 m) Cord, 5-20P Plug

MODEL NUMBER: UL620-15



Description

The Waber-by-Tripp Lite UL620-15 Power Strip offers a convenient method of power distribution in workbench, wallmount or floor mount applications. Includes 6 NEMA 5-15R/20R output receptacles with 1.625 inch center-to-center spacing, 15-ft. (4.57 m) AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes UL620-15 ideal for distributing alternate waveform UPS or generator power. Features rugged all-metal housing, lighted power switch with transparent guard to prevent accidental shutoff, 20 amp resettable circuit breaker and attractive blue/gray color scheme. PLUG/OUTLETS - Input: NEMA 5-20P/Output: 6 NEMA 5-15R/20R ELECTRICAL - 120V AC, 50/60Hz, 20A (Requires standard NEMA 5-20R wall receptacle) FORMAT - Corded power distribution strip

Features

• Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount

applications

- Includes 6 NEMA 5-15R/20R output receptacles with 1.625 inch center-to-center outlet spacing
- · Lighted power switch with transparent snap-over guard to prevent accidental shutoff
- · Keyhole mounting tabs for installation in a wide variety of applications
- UL1363 (USA), cUL (Canada)
- 20 amp power handling capacity with circuit breaker
- 15-ft. (4.57 m) AC line cord

Specifications

OVERVIEW

UPC Code

037332103703

Highlights

- 6 outlets accept NEMA5-15P or 5-20P input plugs
- 15-ft. (4.57 m) cord
- 12.5" length
- 20-amp circuit breaker
- · Lighted master switch
- All metal housing

Package Includes

- UL620-15 Power Strip
- Warranty information
- Instruction manual



INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	20A 120V	
Input Cord Gauge Type	12 gauge; SJT	
Voltage Compatibility (VAC)	120	
Input Plug Type	NEMA 5-20P	
Input Cord Length (ft.)	15	
Input Cord Length (m)	4.57	
Integrated Cord Clip	No	
OUTPUT		
Frequency Compatibility	50 / 60 Hz	
Output (Watts)	2400	
Output Receptacles	(6) 5-15/20R	
Circuit Breaker (amps)	20	
Transformer Accommodation	(2) Yes	
Outlet Orientation	Single row of 6	
Right-Angle Outlets	No	
Outlet Spacing	1.625 in.	
USER INTERFACE, ALERTS & CONTROLS		
Switches	Lighted 2 position switch controls power to all outlets	
Locking Switch Cover	Transparent on/off switch cover prevents accidental turn-off	
PHYSICAL		
Color	Gray	
Antimicrobial Coating	No	
Color (AC Line Cord)	Black	
Integrated Keyhole Mounting Slots	Yes (Includes flanges)	
Keyhole Slot Mounting Measurement (Center to Center)	261.92mm	
Material of Construction	Metal	
Outlets Measurement (Center to Center)	41.3mm	
Receptacle Color	Black	
Shipping Dimensions (hwd / cm)	5.72 x 38.10 x 15.24	
Shipping Dimensions (hwd / in.)	2.25 x 15.00 x 6.00	



[
Shipping Weight (kg)	1.73	
Shipping Weight (lbs.)	3.81	
Unit Dimensions (hwd / cm)	31.75 x 6.35 x 3.8	
Unit Dimensions (hwd / in.)	12.5 x 2.5 x 1.5	
STANDARDS & COMPLIANCE		
Canada	cUL	
UL1363 (Power Tap)	UL1363	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies