CANON INC. 30-2, Shimomaruko 3-chome, Ohta-ku Tokyo 146-8501, Japan

CANON U.S.A., INC. Digital Home and Personal Systems Division 2995 Redhill Avenue Costa Mesa, CA 92626 1-800-OK-CANON http://www.ccsi.canon.com

CANON CANADA INC. 6390 Dixie Road, Mississauga Ontario L5T 1P7, Canada 1-800 OK CANON http://www.canon.ca

CANON LATIN AMERICA, INC. 6505 Blue Lagoon Drive, Suite 325 Miami, Florida 33126, U.S.A.

CANON MEXICANA, S. de R.L. de C.V. Anillo Periferico Sur No. 4124, Torre Zafiro (II) Colonia Ex-Rancho de Anzaldo, Piso 5 y 6, Mexico D.F. Tel. (525) 5490-2000

CANON PANAMA, S.A. Apartado 7022, Panama 5 Rep. de Panama Tel. (507) 279-8900

CANON CHILE, S.A. Ave. Manquehue Norte #1337, Piso 3, Casilla 187-9, Santiago, Chile Tel. (562) 366-6600

CANON ARGENTINA, S.A. Ave. Corrientes 420 (1043) Buenos Aires, Argentina Tel. (5411) 432-59800

CANON EUROPA N.V. P.O. Box 2262 1180 EG Amstelveen, The Netherlands

CANON (UK) LTD.

Woodhatch, Reigate Surrey RH2 8BF, United Kingdom For technical support, please contact Canon Helpdesk. Helpdesk: P.O. Box 431, Wallington, Surrey SM6 0XU TEL: (08705) 143 723

FAX: (08705) 143 340 For sales enquiries: (0121) 666-6262 CANON COMMUNICATION & IMAGE FRANCE S.A.

102 Avenue du Général de Gaulle 92257 LA GARENNE COLOMBES CEDEX, France Tel: 01.41.30.15.15 Fax: 01.41.30.15.05

CANON DEUTSCHLAND GmbH

Postfach 528, 47705 Krefeld, Germany CANON- Hotline-Service Customer Support: (0 21 51) 349-555 Info-Desk: (0 21 51) 349-566 Mailbox: (0 21 51) 349-577 Telefax: (0 21 51) 349-588

CANON ITALIA S.p.A

Palazzo L, Strada 6, 20089 Milanofiori-Rozzano (MI), Italy TEL: 02/8248. 1 FAX: 02/8248. 4604 Pronto Canon 02/8249. 2000 http://www.canon.it

CANON BENELUX NEDERLAND N.V. Neptunusstraat 1, 2132 JA Hoofddorp The Netherlands Tel: 023-5 670 123 Fax: 023-5 670 124 Helpdesk: 023-5 681 681

CANON BENELUX BELGIUM N.V./S.A. Bessenveldstraat 7, 1831 Diegem, Belgium Tel: 02 7220411 Fax: 02 7213274 Helpodesk: 02 7220404

CANON GmbH Zetschegasse 11, 1232 Wien, Austria

CANON (SCHWEIZ) A.G.

Industriestrasse 12, CH-8305 Dietlikon Switzerland Tel: (01) 835 61 61 Fax: (01) 835 68 60 Hotline: 157 30 20 CANON ESPAÑA S.A. C/Joaquin Costa No 41, 28002 Madrid, Spain Help Desk: 906.301255

Tel.: 91-5384500 Fax.: 91-4117780 CANON DANMARK Vasekær 12, DK-2730 Herlev, Denmark Hotline: 44 88 26 66

http://www.canon.dk CANON NORGE AS Hallagerbakken 110, Boks 33, Holmlia, 1210 Oslo 12, Norway Tif: 2262 9321 FAX. 2262 0615

CANON SVENSKA AB Gustav III:s Boulevard 26, S-169 88 Solna, Sweden Tel 08-744 85 00 Fax 08-744 64 65 http://www.canon.se

CANON OY AB Kornetintie, 3, 00380 Helsinki, Finland Puhelin: 010 544 20 Helpdesk: 0600-0-22606 (maksu 14,80 mk/min) Fax: 010 544 4571

CANON SINGAPORE PTE. LTD. 79 Anson Road #09-01/06 Singapore 079906

http://www.canon-asia.com CANON MARKETING SERVICES PTE. LTD.

No. 1, Jalan Kilang Timor #09-00 Pacific Tech Centre Singapore 159303 Tel: 65-7998888, Fax: 65-2736786, Hotline: 65-3342726 http://www.canon.com.sg

CANON MARKETING (MALAYSIA) SDN. BHD.

Block D, Peremba Square Saujana Resort, Section U2, 40150 Shah Alam Selangor Darul Ehsan, Malaysia Tel: 603-7446000, Fax: 603-7446048, **Helpdesk:** 603-7446008/9 Enquiry: print&scan@canon.com.my http://www.canon.com.my

CANON MARKETING (THAILAND) CO. LTD. 179/34-45 Bangkok City Tower, 9th-10th Floor South Sathorn Road, Thungmahamek,

Sathorn, Bangkok 10120, Thailand Tel: 662-3449999, Fax: 662-3449968 http://www.canon.co.th

CANON MARKETING (PHILIPPINES) INC. Marvin Plaza Building, 2153 Don Chino Roces Ave, Makati City, Metro Manila, Philippines Tel: 632-8126047, Fax: 632-8120067/8109797

CANON INDIA PVT LTD. Neela Gagan, Mandi Road, Mehrauli, New Delhi-110030, India Tel: 91-11-6806572, Fax: 91-11-6807180

CANON HONGKONG CO., LTD.

9/F, The Hong Kong Club Building 3A Chater Road, Central, Hong Kong TEL: (852) 2739 0802 FAX: (852) 2739 6428

CANON AUSTRALIA PTY. LTD. 1 Thomas Holt Drive, North Ryde, Sydney N.S.W. 2113, Australia Info-Line: (02) 9805 2864

CANON NEW ZEALAND LTD. Fred Thomas Drive, Takapuna P.O. Box 33-336, Auckland, New Zealand Info-Line: 0900-522666

ADOBE SYSTEMS INCORPORATED http://www.adobe.com

ARCSOFT, INC. http://www.arcsoft.com

SCANSOFT, INC.

Canon

Canon Color Image Scanner CanoScan N670U/N676U/N1240U

Quick Start Guide



Warning

When you use this product, you should pay attention to the following legal issues:

- Scanning of certain documents, such as bank notes (bank bills), government bonds and public certificates, may be prohibited by law and may result in criminal and/or civil liability.
- You may be required under law to obtain authorization from a person possessing copyrights or other legal rights to the item being scanned.
- If you are uncertain of the legality of scanning any particular item, you should consult your legal adviser in advance.
- CanoScan and ScanGear are trademarks of Canon Inc.
- Adobe® Acrobat® and Photoshop® are trademarks of Adobe Systems Incorporated.
- Macintosh, Power Macintosh and Mac OS are trademarks of Apple Computer, Inc., registered in the U.S. and other countries.
- iMac is a trademark of Apple Computer, Inc.
- Microsoft and Windows are registered trademarks of Microsoft Corporation in the U.S. and other countries.
- OmniPage Pro and OmniPage SE are trademarks of ScanSoft, Inc.
- Other names and products not mentioned above may be trademarks or registered trademarks of their respective companies.

System Information

This form is used to record the operating environment of the purchased scanner.

If any problems occur with the scanner, you will need this information when you contact our Customer Support Help Desk. Please make sure to record this and secure it safely.

- When a repair is needed, warranty information is required. Please make sure to record this information and secure it carefully.
- The maintenance service of this equipment expires in seven years after production ceases.

Date of Purchase:		
Dealer:	Tel:	
Dealer Address:		
Scanner Model: CanoScan 🗆 N67	70U 🗅 N676U 🗅 N1240U	
Serial Number (on the back of the equipment)):	
About the Computer Used		
Manufacturer:	Model:	
CPU:	Clock Speed:	MHz
Memory Capacity (RAM): MB		
Hard Disk Capacity: MB	Space Available:	MB
OS : Windows 🗅 Me 🗅 98 🗅 2000	Mac OS 🛛 8.6 🖵 9.0	🗅 9.1 🛛 X (Classic)
Monitor Type:	Monitor Size:	Inches
Printer:	Manufacturer:	
Type of Printer:	Printer Resolution:	dpi
Installed Virus Protection Program:		
Installed Compression Program:		
On-Board Expansion Cards:		
Attached Peripherals:		
Name of Network Connected:		

Scanner Unit and Accessories




Software and Documents

- CanoScan Setup Utility CD-ROM Contains software programs, PDF manuals, troubleshooting guide, etc.
- Adobe Photoshop CD-ROM (with only CanoScan N1240U)
- Quick Start Guide (this guide)
- Additional documents


Unlock the Scanning Unit

Unlock the scanner before connecting to the computer. If it is left locked, a malfunction or other problem may occur.

- **1.** Peel the seals off the scanner.
- **2.** Gently turn the scanner over.




3. Push the lock switch toward the unlock mark.




4. Return the scanner to a horizontal position.

Confirm that the power switches for the computer and other connected devices are off.

Connect the scanner to the computer with the supplied USB interface cable.



• The scanner does not have a power switch. The power is activated as soon as the computer is turned on.



- The screen shots common to both Windows and Macintosh used in this manual are from the Windows platform, unless otherwise noted.
- The scanner used for the screen shot in this manual is N1240U. Scanner name shown in screen shots will vary depending on the model purchased.

Install the Software

1. Install the Driver Software

Install the Driver Software (ScanGear CS-U) with the following procedure.

For Windows 98/2000 Professional users

Jump to page 4.

Windows Millennium Edition

- **1.** Turn the computer on.
- **2.** The [Add New Hardware Wizard] dialog box will appear.

Confirm that "Automatic search for a better driver (Recommended)" is selected.

- **3.** Place the CanoScan Setup Utility CD-ROM in the drive.
- **4.** Wait for 10 seconds, then click [Next]. The driver will begin to install.

5. When "Windows has finished installing the new hardware device." appears, click [Finish].

Jump to page 5.












Windows 98 / 2000 Professional

The screen shots in this section are from Windows 98.

- **1.** Turn the computer on.
- 2. When [Add New Hardware Wizard] appears, click [Next].
- **3.** Confirm that "Search for the best driver for your device. (Recommended)" is selected and click [Next].
- **4.** Place the CanoScan Setup Utility CD-ROM in the drive.
- 5. Confirm that "CD-ROM drive" is selected, wait for 10 seconds, and then click [Next]. If "Driver Not Found" appears, click [Back] and repeat this step.



The driver will begin to install.

Windows 98 Users


If prompted to insert the Windows 98 CD-ROM, follow the instructions below.


- a. Click [OK].
- **b.** Click [Browse].
- c. Select the CD-ROM drive and click [OK].
- d. Click [OK].


Windows 2000 Professional Users

If the message box "The software you are about to install does not contain a Microsoft digital signature." appears, continue installation by clicking [Yes].

7. Click [Finish].











5

2. Install the Application Software

List of Software to Be Installed (approx. total of 209MB)

- ScanGear Toolbox (10 MB) -Scanning Utility Program
- ArcSoft PhotoStudio 2000 (40 MB) Image Editing Program
- ArcSoft PhotoBase
- (60 MB) -Photo Album Program
- ScanSoft OmniPage Pro
 Adaba Acrobat Baadar
- (75 MB) -OCR (Optical Character Recognition) Program
- Adobe Acrobat Reader
- (24 MB) -Electronic Manual Viewer Program

Installation Procedures

1. The CanoScan Setup Utility main menu will appear.

If the CanoScan Setup Utility main menu does not automatically appears, eject the CD-ROM and re-insert it.

2. Click [Install the Software].

[Software User License Agreement] is confirmed. Click [Yes] if you accept the agreement.

The [Install] window will display.

- **3.** Click [Start Installation].
- **4.** The installation procedure will start. Follow the on-screen message prompts and click [Yes] or [Next] to continue the installation.

- **5.** When the installation is complete, click [Yes]. The computer will restart.
- **6.** After Windows restarts, remove the CD-ROM from the drive and store it in a safe place.
- Jump to page 7.







List of Software to Be Installed (approx. total of 94MB)

- ScanGear CS-U
- ScanGear Toolbox
- ArcSoft PhotoStudio
- ArcSoft PhotoBase
- ScanSoft OmniPage SE
- Adobe Acrobat Reader
- (10 MB) -Photo Album Program

(10 MB) -Scanning Utility Program

(10 MB) -Image Editing Program

(10 MB) -Driver Program

(30 MB) -OCR (Optical Character Recognition) Program

CanoScan Novus CanoScan Setup Utility

Ç

can N 670U / N 676U / N 1240U

(24 MB) -Electronic Manual Viewer Program

Installation Procedures

1. Turn the computer on.

When "...Would you like to look for these drivers over the internet?" appears, click [Cancel].

2. Place the CanoScan Setup Utility CD-ROM in the drive.

The CanoScan Setup Utility main menu will appear.


If no window displays, double-click the CD-ROM icon, then the Setup icon.


3. Click [Install the Software]. [Software User License Agreement] is confirmed. Click [Yes] if you accept the agreement.

The [Install] window will display.

- 4. Click [Start Installation].
- **5.** The installation procedure will start. Follow the on-screen message prompts and click [Yes], [Next] or [Install] to continue the installation.
- Install the ArcSoft PhotoStudio image editing program? There are six more programs to install on Color image Scanne oScan Setu<u>p Utili</u>ty No ArcSoft PhotoStudio Click the "Install" button to install elect the installation folder-Easy Install nstall Locatio Macintosh HD **T** Switch Disk Instal Installation was successfully completed. To use the new software, you must restart your computer Click [Yes] to restart your computer. on Color Image Sciling noScan Setup Util II Yes
- **6.** When the installation is complete, click [Yes]. The computer will restart.
- **7.** After restarting, remove the CD-ROM from the drive and store it in a safe place.

6






Cancel




3. Click the Acquire icon **.** ScanGear CS-U will start.




Macintosh


3. Click the [File] menu and select [Acquire] and [ScanGear CS-U 6.2.0...]. ScanGear CS-U will start.




4. Click [Preview].

After calibration, the preview scan will start and gradually display the image.








6. Click [Scan].

The final scan will start.



7. The scanned image will appear in the PhotoStudio window.



- **8.** Save the scanned image. Click the [File] menu and select [Save As]. Select the folder where you wish to store the image file, enter a file name and select a file type, and click [Save].
- **9.** Click the 💌 or 🔲 (close box) in the PhotoStudio window to close it.


You have now confirmed the scanner operation. You should now be ready to explore the possibilities of the bundled software.

For details about the bundled software, read the Product Guide or User's Guide for each software program contained on the CanoScan Setup Utility CD-ROM as PDF manuals.

If the scanner does not perform as described above, read the [Troubleshooting] section of the CanoScan Setup Utility CD-ROM.


Using the Scanner Buttons

You can use the 3 convenient buttons on the front of the scanner, to scan and perform related tasks easily, with a single touch of the button. Place an item on the scanner before pressing a button.




- To use these buttons, ScanGear CS-U, ScanGear Toolbox and ArcSoft PhotoBase should be installed from the CanoScan Setup Utility CD-ROM.
- While scanning, you can change the default settings for scanning by clicking the [Cancel] button. For details on changing settings or arranging the scanner's button-to-function assignment, refer to the ScanGear Toolbox User's Guide (PDF manual).


1. Attaching the Velcro[®] Strip



2. Installing the Stand



3. Positioning an Item



Specifications

		CanoScan N670U/N676U	CanoScan N1240U
Scanner Type		Flatbed	
Scanning Element		CIS (Contact Image Sensor)	
Light Source		3-color (RGB) LED	
Optical Resolution		600 x 1200 dpi	1200 x 2400 dpi
Selectable Resolution	n	25 - 9600 dpi (ScanGear CS-U)	
Scanning Bit Depth	Color	16 bit input / 8 bit output for each color (RGB)	
	Grayscale	16 bit input/8 bit output	
Scanning Speed*1 Color Grayso B&W	Color	16 msec/line (600 dpi)	16 msec/line (600 dpi)
			32 msec/line (1200 dpi)
	Grayscale	5.3 msec/line (600 dpi)	5.3 msec/line (600 dpi)
			10.6 msec/line (1200 dpi)
	B&W	5.3 msec/line (600 dpi)	5.3 msec/line (600 dpi)
			10.6 msec/line (1200 dpi)
Preview Speed*2		15 sec (approx.)	
Interface		USB 1.1	
Maximum Documer	nt Size	A4/Letter: 216 x 297mm (8.5 x 11.7 in.)	
Scanner Buttons		3 buttons : SCAN, COPY, E-MAIL	
· · · · -	Temperature	5° to 35° C (41° to 95° F)	
	Humidity	10 % to 90 % RH (without condensation formation)	
Power Requirements Supplied via USB port		a USB port	
Power Consumption		In operation: 2.5 watts max	ximum Stand-by: 1.25 watts
Maximum Exterior Dimensions		256 x 383 x 34mm (10.1 x 15.1 x 1.3 in.)	
Weight		Approximately 1.5 kg (3.3 lbs.)	

*1 Transfer time to computer is not included.

*2 Calibration processing time is not included.

• Specifications are subject to change without notice.