



# SAMSUNG ATIV BOOK 9

THE ULTIMATE ULTRA-PORTABLES FOR BUSINESS



## KEY FEATURES



### Premium Design and Durability

Designed for mobility and durability, the ATIV Book 9 features a slim, lightweight magnesium casing as strong as it is sleek.



### Full HD SuperBright™ Display

The LED-backlit 1920 x 1080 Full HD LCD display produces sharp, high-resolution video. And Samsung SuperBright™ technology is up to 50% brighter than typical laptop screens, for more vivid colors.



### Next Generation Processing Power

With Intel® 4th Generation Core™ i5 and i7 processors, the ATIV Book 9 speeds its way through the workday.



### Start Even Faster

The Samsung ATIV Book 9 is equipped with a solid state drive, to provide greater stability and to boot up as much as 60% faster than a PC with a hard disk drive.



### 1500-Cycle Battery

Samsung's PowerPlus charging technology and advanced Lithium-Polymer battery combine to deliver a lifespan of up to 1,500 charge cycles, up to 3 times longer than a conventional battery.

## A BIG EXPERIENCE IN A SMALL FORM FACTOR

Introducing the ultrabook that's redefining the business experience. At just 2.49 lbs. and just .51" thin, the ultra-portable 13.3" ATIV Book 9 is ready for anything, anywhere, anytime. The same slim form factor as its predecessor now features a 1920 x 1080 Full HD resolution and 8GB of RAM for an even higher level of performance. Sleek, slim and spectacular. It's the way business should be. **The New Business Experience**

### CONTACT US:

1-800-SAMSUNG | 1-866-SAM4BIZ

[samsung.com/business](http://samsung.com/business)

[samsung.com/b2blaptop](http://samsung.com/b2blaptop)

### FOLLOW US:



[youtube.com/samsungbizusa](http://youtube.com/samsungbizusa)



[@SamsungBizUSA](https://twitter.com/SamsungBizUSA)

# Samsung ATIV Book 9



NP900X3G-S02US



NP900X3G-S01US

Samsung recommends Windows 8.

## KEY SPECIFICATIONS

For complete product specifications, visit [samsung.com/b2blaptop](http://samsung.com/b2blaptop)

	CPU	Intel® Core™ i5-4200U Processor	Intel® Core™ i7-4500U Processor
Operating System	Windows® 7 Professional with Windows 8 Pro COA	Windows® 7 Professional with Windows 8 Pro COA	Windows® 7 Professional with Windows 8 Pro COA
Display	13.3" LED Full HD, 1920 x 1080, 16:9, Anti-glare	13.3" LED Full HD, 1920 x 1080, 16:9, Anti-glare	13.3" LED Full HD, 1920 x 1080, 16:9, Anti-glare
Brightness	300 nit SuperBright™ Technology	300 nit SuperBright™ Technology	300 nit SuperBright™ Technology
CPU Clock Speed	1.6 GHz (Up to 2.6 GHz)	1.8 GHz (Up to 3.0 GHz)	1.8 GHz (Up to 3.0 GHz)
System Memory (Standard/Maximum) <sup>1</sup>	8GB (On Board) / 8GB	8GB (On Board) / 8GB	8GB (On Board) / 8GB
Memory Speed/DIMM Slots	DDR3 (1600MHz) / 0 DIMM Slots	DDR3 (1600MHz) / 0 DIMM Slots	DDR3 (1600MHz) / 0 DIMM Slots
Storage <sup>2</sup>	128GB SSD	256GB SSD	256GB SSD
Graphics	Intel® HD Graphics 4400	Intel® HD Graphics 4400	Intel® HD Graphics 4400
Graphics Memory	Shared	Shared	Shared
Speaker	3W Stereo Speaker (1.5W x 2)	3W Stereo Speaker (1.5W x 2)	3W Stereo Speaker (1.5W x 2)
Headphone Out/Microphone In	Yes (Headphone/MIC combo)	Yes (Headphone/MIC combo)	Yes (Headphone/MIC combo)
Internal Mic	Yes	Yes	Yes
Web Camera	720p HD Webcam	720p HD Webcam	720p HD Webcam
USB Ports	1 x USB 2.0 + 1 x USB 3.0	1 x USB 2.0 + 1 x USB 3.0	1 x USB 2.0 + 1 x USB 3.0
Multi Card Slot	3- in-1 (SD/SDHC/SDXC)	3- in-1 (SD/SDHC/SDXC)	3- in-1 (SD/SDHC/SDXC)
Touch Pad/Point Stick	Clickpad	Clickpad	Clickpad
Wireless LAN	Intel® Dual Band Wireless-AC 7260 802.11 ac/a/b/g/n (2x2)	Intel® Dual Band Wireless-AC 7260 802.11 ac/a/b/g/n (2x2)	Intel® Dual Band Wireless-AC 7260 802.11 ac/a/b/g/n (2x2)
Bluetooth/WiDi/3	Bluetooth 4.0 / Yes	Bluetooth 4.0 / Yes	Bluetooth 4.0 / Yes
Wired Ethernet LAN	Gigabit LAN (with dongle included in box)	Gigabit LAN (with dongle included in box)	Gigabit LAN (with dongle included in box)
VGA4	Mini VGA (Mini VGA to VGA dongle sold separately)	Mini VGA (Mini VGA to VGA dongle sold separately)	Mini VGA (Mini VGA to VGA dongle sold separately)
HDMI	Micro HDMI	Micro HDMI	Micro HDMI
AC Adapter	40W	40W	40W
Battery Capacity	4 cell / Li-Po 44 WHr	4 cell / Li-Po 44 WHr	4 cell / Li-Po 44 WHr
Battery Life	Up to 10 hours	Up to 10 hours	Up to 10 hours
Security	TPM	TPM	TPM
Color	Ash Black	Ash Black	Ash Black
Warranty	3 Year Standard Parts/Labor	3 Year Standard Parts/Labor	3 Year Standard Parts/Labor
Dimensions (L x W x H)	12.35" x 8.60" x 0.52"	12.35" x 8.60" x 0.52"	12.35" x 8.60" x 0.52"
Weight	2.49 lbs.	2.49 lbs.	2.49 lbs.

## INCLUDED SOFTWARE

### Samsung Support Center

Keep your laptop running smoothly with the latest drivers.

### Samsung Recovery Solution

Back up your laptop easily for that just-in-case moment.

### S Player+

Media player for movie and music formats not supported by Windows 8.

### S PhotoStudio

Photo editing made simple. Crop, rotate, auto fix, enhance and much more, with or without an S Pen.

### S Settings

Easy control of system settings in one application.

### Microsoft® Office Trial


A productivity suite with limited functionality versions of Word and Excel.

### Norton Internet Security (60 days Trial)

Keeps you safe when you surf, shop and bank online. Even warns about social media scams and suspicious content.

## CONNECTIVITY

- 3-In-1 Multi Card Slot
- Mic In
- Mini VGA (optional dongle sold separately)
- Audio In/Out
- USB 2.0
- AC Power
- USB 3.0 (Chargeable)
- Micro HDMI
- RJ45 MDC



## ACCESSORIES

### AA-AV2N12B/US

Mini VGA to VGA Dongle



### AA-BS8N13B/US

13" Synthetic Leather Protective Sleeve



### AA-PA3NS40/US

Slim AC Adapter



### AA-ES3P95M/US

Optical Disk Drive



For complete product information and accessories, visit [samsung.com/business](http://samsung.com/business) or [samsung.com/b2blaptop](http://samsung.com/b2blaptop)

Follow us: [@SamsungBizUSA](https://twitter.com/SamsungBizUSA) | [youtube.com/samsungbizusa](https://www.youtube.com/samsungbizusa)

Samsung Electronics has been named 2013 ENERGY STAR Partner of the Year in the product manufacturing category by the U.S. Environmental Protection Agency (EPA).

Product Support: 1-800-SAMSUNG

1-866-SAM4BIZ

©2014 Samsung Electronics America, Inc. Samsung is a registered mark of Samsung Electronics Corp., Ltd. Specifications and designs are subject to change without notice. Non-metric weights and measurements are approximate. Intel, the Intel logo, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and other countries. All other brand, product, service names and logos are trademarks and/or registered trademarks of their respective manufacturers and companies. See [samsung.com](http://samsung.com) for detailed information. Printed in USA. COM-ATIVBOOK9B2BDSHT-JAN14T



<sup>1</sup>Battery life will vary depending on the product model, configuration, power management settings, applications used and wireless settings. The maximum capacity of the battery will decrease with time and use. Test results based on independent MobileMark 2007 tests. <sup>2</sup>Total amount of available memory may be less based on configuration. <sup>3</sup>Accessible capacity varies; MB = 1 million bytes; GB = 1 billion bytes; TB = 1 trillion bytes. Please note that a portion of the hard drive is reserved for system recovery, operating system and preloaded content software. See [samsung.com](http://samsung.com) for further details.

