

Veriton | X



X2631G

Essential computing for efficient work



 Windows 7 Professional

 Windows 8 Pro

Part No: DT.VKBEQ.007

EAN: 4713147357413



General	System Type	Desktop
	Modell	VX2631G
	Form Factor	Small Form Factor
Operating System	Operating System I	Windows 7 Professional 64-bit
	Operating System II	Windows 8 Professional 64-bit
	Language	DA/SV/FI/NO/EN
Processor / Chipset	CPU	Intel® Core™ i3-4130 Processor
	# of Cores	2
	Max Turbo Speed	3.40 GHz
	Cache	3 MB
	64-Bit Computing	Yes
	Chipset	Intel® H81 Express Chipset
Memory	Ram	1 X 4 GB
	Max RAM Supported	Up to 16 GB
	Technology	DDR3 1600 MHz UDIMM
	Slots Qty	2
	Empty Slots	1
Storage	Hard Drive	500GB / 7200rpm
Optical	Type	16X Super Multi
Graphics	Type	Intel® HD Graphics 4400
Communications	LAN	Gigabit Ethernet
	Wireless	No (Option)
	Bluetooth	No (Option)
Audio	Type	Integrated high-definition, 5.1-channel surround sound

Input	Keyboard	USB Keyboard
	Keyboard Layout	Nordic
	Mouse	USB Mouse
Connections & Expansion	Front	Quantity
	Card reader	No (Option)
	Audio jack (s)	2
	USB 3.0	2
	Back	Quantity
	D-Sub port(s)	1
	HDMI port(s)	0
	DVI port(s):	1
	Display port(s):	0
	COM port(s):	1
	Serial ports on board header (COM2):	1
	LAN port(s):	1
	PS/2 port(s):	2
	Audio jack(s):	3
	USB 2.0 port(s):	4
Expansion slot(s)	PCI Express® 2.0 x16 slot	1
	PCI Express® 2.0 x1 slot	1
	Parallel port connector	Option
	Serial port connector	Option (Com 2)
Software	ISP & Communications	Skype
	Multimedia	Cyberlink® PowerDVD™
	Productivity	Acer SmartBoot
		NewsXpresso
		PowerSaver
		Veriton ControlCenter
	Security	Acer ProShield
		McAfee® Internet Security Suite
		Norton™ Online Backup
	Utilities	Acer eSettings Management
Commercial features	Intrusion alert (via BIOS)	Yes
	One-Button Recovery (OBR)	Yes
	Kensington lock slot	Yes
	Hard drive password protection (via BIOS)	Yes
	PXE (Preboot eXecution Environment)	Yes
	WOL (Wake On Lan)	Yes
	TPM chip with TPM 1.2 compliance	No (Option)
Power supply	Type	FR 220W (8.5L) EuP 82+
	Power Cord	EU/Danish
Dimensions	Bezel	102 (W) x 368.15 (D) x 267 (H) mm