


Model #: GC2000

- 1. Audio Left/Right Ports
- 2. Y/Pb/Pr Component & Video Ports
- 3. HDMI IN Port
- 4. USB 2.0 Port
- 5. HDMI OUT Port
- 6. Ethernet Port
- 7. Triple Play Mode Switch: Standalone/Streaming/PC
- 8. SD Card Slot
- 9. Push-Button Record





Diamond GameCaster HD Triple Play Game Capture Box

Introduction:

Revolutionize your Gaming Experience with the Diamond GameCaster HD 1080P Game Capture. Capture and record your gameplay in HD 1080P from all the major game consoles and share them with your friends and family. Stream your edited scenes on YouTube, Facebook, Twitch® or stream® with real-time Voice Commentary. Seamlessly go from streaming to saving your gameplay on external SD cards and archive hours of your most inspired gaming experiences. With its sleek and compact design, the Diamond HD 1080P Game Capture is a breeze to use. Just set it and forget it. The LOOP-THROUGH function lets you record and play simultaneously with no delay.

The Diamond HD 1080P Game Capture features Triple Play Game Capture Modes:

- Capture/Edit including real-time "Voice Commentary"
- Standalone Record directly to a SD card without a PC
- Streaming Stream directly to Twitch, Ustream or your Smartphone/Tablet

Product Information

• **Product Description:** Diamond Game Caster HD GC2000 1080P Game Capture for PC/PS3/PS4/WiiU/Xbox/XboxOne ,Win7, Win8, Win8.1 (Android Streaming), (iOS Streaming) with Voice Commentary.

Series: Game Caster
Model: GC2000
PN Number: 69000

• **UPC Number**: 757448024494

• Case Quantity: 20

• Case Dimensions: 13.6 x 11.7 x 18.5 inches

Master Case WT: 20 Lbs.Warranty: 1 year

• Target Audience: Office/Home/Educational

Specifications

Product weight 0.35 Lbs.Package weight 1.0 Lbs.

• **Product Dimensions** 3.4 (L) x 5.5 (W) x 1.0 (H)

Package Dimensions $6.5(L) \times 8.75 (W) \times 2.125(H)$ Inches

SoC	H.264 Hardware compression SoC		
Input	Video	HDMI	
		YPbPr	
	Audio	HDMI	
		Audio L/R	
Loop Through Video Resolution	320 x 240(60p), 640 x 480 (60p), 720 x 480 (60p), 720 x 576 (50p), 800 x 600 (60p), 1024 x 768 (60p), 1280 x 720p (60p), 1280 x 768 (60p), 1280 x 800 (60p), 1280 x 1024 (60p), 1360 x 768 (60p), 1440 x 900 (60p), 1680 x 1050 (60p), 1920 x 1080 (60p)		
Ethernet	10/100M		
Capture Resolution	Up to 1080p @ 30fps		
Support Format	Video Input	VBS (Video Baseband Signal/Video-RAW)	
	Audio Input	ABS (Audio Baseband Signal/Audio-RAW)	
	Video Output	H.264 AVC	
	Audio Output	H.264 AAC	
USB	PC Mode	USB 2.0 interface	
	Standalone / Streaming Mode	USB Power (5V1/A)	
Dimension	Box size	139mm X 83 mm X 31 mm	

Mode	PC	Standalone	Streaming
Power	From PC	From USB Power	From USB Power
Store	Hard Disk	Standard SD Card*	Server/Client
Input	HDMI & YPbPr(L/R)		
Output	НДМІ		HDMI & LAN**
Resolution	480p/576p/720p/1080i/1080p***		Maximum 720p

Package Contents

- GC2000 Triple Play Capture Box
- Quick Installation Guide
- Installation CD/Application CD
- HDMI cable
- USB Cable

System Requirements

- Intel Core 2 Duo 2.4GHz or higher (recommended)
- 1024 MB RAM of system memory or above (recommended)
- One available USB2.0 port
- Graphics Card (Must support DirectX 9.0c)
- Sound Card (AC97 compatible sound card)
- 1GB Free HD Space
- DVD-ROM Drive (For software installation)
- Microsoft Windows 7 Home Premium above / Windows 8 / Windows 8.1 operation system
- Android 4.2 or later version (For Streaming)
- iOS 6.0 or later version (For Streaming)