





HP Digital Sender Flow 8500 fn2 Document Capture Workstation,
HP ScanJet Enterprise Flow N9120 fn2 Document Scanner

Technical Specifications



8500 fn2



N9120 fn2



www.hp.com/go/DSFlow8500fn2
www.hp.com/support/sjflowN9120fn2



HP Digital Sender Flow 8500 fn2 Document
Capture Workstation, HP ScanJet Enterprise
Flow N9120 fn2 Document Scanner

Technical Specifications

Copyright and license

© 2017 Copyright HP Development Company, L.P.

Reproduction, adaptation or translation without prior written permission is prohibited, except as allowed under the copyright laws.

The information contained herein is subject to change without notice.

The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Trademark credits

Adobe®, Adobe Photoshop®, Acrobat®, and PostScript® are trademarks of Adobe Systems Incorporated.

Apple and the Apple logo are trademarks of Apple Inc., registered in the U.S. and other countries.

OS X is a trademark of Apple Inc., registered in the U.S. and other countries.

AirPrint is a trademark of Apple Inc., registered in the U.S. and other countries.

Microsoft®, Windows®, Windows® XP, and Windows Vista® are U.S. registered trademarks of Microsoft Corporation.

Google™ is a trademark of Google Inc.

1, 10/2017

Table of contents

Web only content	1
Technical specifications (HP Digital Sender Flow 8500 fn2 Document Capture Workstation)	1
Technical specifications (HP ScanJet Enterprise Flow N9120 fn2 Document Scanner)	2
Index	5

Web only content

Technical specifications (HP Digital Sender Flow 8500 fn2 Document Capture Workstation)

Name	Description	
Paper handling	Input tray capacity	150 sheets 75 gsm
	Minimum paper size (ADF)	68.07 x 147.06 mm (2.68 x 5.79 in)
	Maximum paper size (ADF)	215.9 x 863.6 mm (8.5 x 34 in)
	Maximum paper size (scanner glass)	215.9 x 330.2 mm (8.5 x 14 in)
	Minimum paper weight (ADF)	12 lb (45 gsm)
	Maximum paper weight (ADF)	53 lb (199 gsm)
	Resolution	Up to 600 dpi
	Environmental features	<ul style="list-style-type: none">• By default, scanner enters Sleep Mode prior to 10 minutes of inactivity.• ENERGY STAR® qualified.
Connectivity	10/100/1000 Ethernet LAN connection with IPv4 and IPv6	
	Hi-Speed USB 2.0	
	Easy-access USB port for scanning without a computer and upgrading the firmware	
	Hardware integration pocket (HIP) for connecting accessories and third-party devices	
	HP Internal USB ports	NOTE: The HP Internal USB ports are only supported with an AA accessory module.
Memory	Standard: 2.5 GB	
	Maximum: 3.5 GB	
Storage	500 GB hard disk drive	
Control-panel display and input	<ul style="list-style-type: none">• 8" color touchscreen	
	<ul style="list-style-type: none">• Retractable keyboard	

Name	Description	
Scan	HP EveryPage with ultrasonic multi-feed sensor detects when multiple pages feed through simultaneously.	
NOTE:	For the most current information, go to www.hp.com/go/DSFlow8500fn2 or www.hp.com/support/sjflowN9120fn2	
	Embedded optical character recognition (OCR) provides the ability to convert scanned pages into text that can be edited or searched using a computer.	
	SMART Label feature provides paper-edge detection for automatic page cropping	
	Automatic page orientation for pages that have at least 100 characters of text.	
	Automatic tone adjustment sets contrast, brightness, and background removal for each page.	
Digital Send	Scan to E-mail , Scan to Fax , Scan to SharePoint , Scan to USB , and Scan to Network Folder	
Product dimensions	Width	512 mm (20.2 in)
	Depth	585.3 mm (23.04 in)
	Height	263.4 mm (10.4 in)
	Weight	17.46 kg (38.5 lb)
Supported operating systems	Windows 7	
	Windows 8	
	Windows 8.1	
	Windows 10	
	OS X 10.10 Yosemite	
	OS X 10.11 El Capitan	
	OS X 10.12 Sierra	

Technical specifications (HP ScanJet Enterprise Flow N9120 fn2 Document Scanner)

Name	Description	
Paper handling	Input tray capacity	200 sheets 75 gsm
	Minimum paper size (ADF)	68.07 x 147.06 mm (2.68 x 5.79 in)
	Maximum paper size (ADF)	296.92 x 863.6 mm (11.69 x 34 in)
	Maximum paper size (scanner glass)	296.42 x 431.8 mm (11.67 x 17 in)
	Minimum paper weight (ADF)	45 gsm
	Maximum paper weight (ADF)	199 gsm
	Resolution	Up to 600 dpi

Name	Description
Environmental features	<ul style="list-style-type: none"> By default, scanner enters Sleep Mode prior to 10 minutes of inactivity. ENERGY STAR® qualified.
Connectivity	<p>10/100/1000 Ethernet LAN connection with IPv4 and IPv6</p> <p>Hi-Speed USB 2.0</p> <p>Easy-access USB port for scanning without a computer and upgrading the firmware</p> <p>Hardware integration pocket (HIP) for connecting accessories and third-party devices</p> <p>HP Internal USB ports</p> <p>NOTE: The HP Internal USB ports are only supported with an AA accessory module.</p>
Memory	<p>Standard: 2.5 GB</p> <p>Maximum: 3.5 GB</p>
Storage	500 GB hard disk drive
Control-panel display and input	<ul style="list-style-type: none"> 8" color touchscreen Retractable keyboard
Scan	<p>HP EveryPage with ultrasonic multi-feed sensor detects when multiple pages feed through simultaneously.</p> <p>NOTE: For the most current information, go to www.hp.com/go/DSFlow8500fn2 or www.hp.com/support/sjflowN9120fn2</p> <p>Optical character recognition (OCR) provides the ability to convert scanned pages into text that can be edited or searched using a computer.</p> <p>SMART Label feature provides paper-edge detection for automatic page cropping</p> <p>Automatic page orientation for pages that have at least 100 characters of text.</p> <p>Automatic tone adjustment sets contrast, brightness, and background removal for each page.</p>
Digital Send	Scan to E-mail , Scan to Fax , Scan to Network Folder , Scan to USB , and Scan to SharePoint
Product dimensions	<p>Width 601.98 mm (23.7 in)</p> <p>Depth 635 mm (25 in)</p> <p>Height 287.02 mm (11.3 in)</p> <p>Weight 21.4 kg (47.18 lb)</p>
Supported operating systems	<p>Windows 7</p> <p>Windows 8</p> <p>Windows 8.1</p> <p>Windows 10</p> <p>OS X 10.10 Yosemite</p> <p>OS X 10.11 El Capitan</p>

Name	Description
OS X 10.12 Sierra	

Index

C

copying
resolution 1, 2

D

dimensions, scanner 1, 2
document feeder
capacity 1, 2

M

memory
included 1, 2
mobile printing solutions 1, 2

N

networks
supported 1, 2

O

operating systems (OS)
supported 1, 2
OS (operating system)
supported 1, 2

P

pages per minute 1, 2

R

resolution
copy and scan 1, 2

S

scanning
resolution 1, 2

T

technical specifications
8500 fn2 1
N9120 fn2 2

trays

capacity 1, 2
included 1, 2

W

weight, scanner 1, 2

