

DATE CHANGES INTL. REV. 07.30.18 ORIGINAL RD 1.0

IK-DELL-AT Operations Guide Touchpad: Resistive FN Lock: FN + Esc, Enables FN lock, allows user to use secondary functions with FN key Mute: FN + F1 Volume Down: FN + F2 Volume Up: FN + F3 Mute microphone: FN + F4 Num Lock: FN + F5 Scroll Lock: FN + F6 Screen Blackout: FN + F7 Project Screen: FN + F8 Search: FN + F9 Backlight: FN+F10 to Cycle Brightness (4 levels) FN + C to Cycle Color (4 colors) Toggle Wireless: FN + F10 Sleep: FN + Insert Home: FN + Left Arrow End: FN + Right Arrow Applications: FN + Right Ctrl

> VIBRATION MINIMUM INTEGRITY: 0.04g/Hz @ 20-2000Hz 60 Minutes/axis, 3 axes VEHICLE VIBRATION: 1-200Hz, 0.52grms 90 Minutes/axis, 3 axes

KEY SWITCH LIFE: 10 MILLION CYCLES TRAVEL: 1.3mm ACTUATION FORCE: 65gf FEEDBACK: TACTILE CLICK

PROPRIETARY AND CONFIDENTIAL

POWER USB: 250mA @ 5V (from CPU port) WEIGHT 1.6lbs

SHOCK

DROP TEST: 48", 26 DROP ANGLES CRASH HAZARD: 185g, 2 Shocks/axis/direction (12 total shocks) FUNCTIONAL SHOCK: 40g, 3 Shocks/axis, 3 axes

TEMPERATURE STORAGE: -51°C TO +71°C (-60°F TO 160°F) OPERATING: -29°C TO 63°C (-20°F TO 145°F)

IKey, Ltd.
2621 Ridgepoint Dr. Suite 233
Austin, Texas 78754@2018 iKey,Ltd.Part Number:IK-DELL-ATDrawing Number:MKT0433Sheet:1 OF 1Voice: (512) 837-0283
Fax: (512) 927-8530Voice: (512) 837-0283
Fax: (512) 927-8530Part Number:IK-DELL-AT-MKTRevision:1.0Date:7/30/2018RJD