
7170-0977 Series

Installation Guide

Outdoor Flat/Tilt Wall Mount For Samsung OH55





BASIC INFORMATION

Wall mount model 7170-0977-00 (flat) 7170-0977-01 (Tilt)

Display Model OH55

Installation Configuration

Landscape

Portrait

Tilt feature Available by model Fixed at flat, 5 deg, 10 deg , 15 deg

Environment Temperature Negative 30 Celsius to 50 Celsius, 24/7 operation

Wall application Solid concrete, Hollow Brick, or 3/4" plywood-backed wall

Product Weight 31.5 lbs [14.4 kg] for flat model 45.5 lbs [20.6 kg] for tilt model

OA Weight (Mount & Flat-Panel) 147.5 lbs [66.9 kg] (flat) 161.5 lbs [73.26 kg] (Tilt)

OA Width x Depth x Height (Portrait) 28.8" x (5.55" flat to 17.33" tilt) x 50.87"

OA Width x Depth x Height (Landscape) 49.63" x (5.55" flat to 14.62" tilt) x 30.38"

INSTALLATION ENVIRONMENT

Beach Must not be placed in areas where seawater is accessible

Wind Must not be placed in areas with strong winds caused by storms or other

natural phenomenon

եթ

Snow Awning or cover is needed to avoid snow piling directly onto inlet


Iron Dust Suitable, (e.g. train or subway station)

ENCLOSED OR RECESS AREA


Clearance 52mm (2.05") minimum all around

Additional front glass Prohibited in any enclosed area





TILT ADAPTER (OPTION):



HARDWARE:



1/4-20 x 5" Pan Head



1/4-20" x 3/4" Button Head



1/4" Flat Washer



5/16" x 3" Hex Lag



5/16" Split Lock Washer



5/16" Flat Washer



Shell Expansion Anchor




M8 x 16mm Hex Bolt




Lock-it Security Barrel











Solid Concrete/Brick Use proper mounting guideline per state code. All hardware, threaded rod, epoxy, and other mounting hardware are not supplied. Shown for reference only.

Wood Application

Use a stud finder to determine the center of the wall studs in the vicinity of the mount and mark the wall. Drywood wall must be backed with at least 3/4" plywall to support the weight of the mount and flat-panel.

