

Product data sheet

Specifications



APC Essential SurgeArrest, 7 outlet, phone line protection, 10 ft power cord

P7T10

⚠ To be discontinued on: Aug 30, 2024

⚠ To be discontinued

Overview

Lead time Usually in Stock

Main

Main Input Voltage	120 V
Input Connection Type	NEMA 5-15P
Cable length	10 ft (3.05 m)
Number of cables	1
Provided equipment	2 x 1.8 Meter Tel cable User Manual

Physical

Color	Beige
Height	14.02 in (35.6 cm)
Width	3.0 in (7.6 cm)
Depth	2.008 in (5.1 cm)
Net Weight	1.23 lb(US) (0.56 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Maximum Line Current per phase	15 A
Input Frequency	50/60 Hz +/- 5 Hz manual switch

Output

Number of power socket outlets	7
Outlet standard	NEMA 5-15R

Conformance

UL 1449 TVSS Rating	330
Product Certifications	CSA
Standards	UL 1449
Equipment protection policy	Lifetime : \$25000

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environmental

Ambient Air Temperature for Operation	32.0000000000...104.0000000000 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5.0000000000...113.0000000000 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

Surge Protection and Filtering

NM Surge Response Time (ns)	0 ns common mode
Common mode rejection	55 dB
Peak current	30 kAcommon mode 10 kAnormal mode
Surge energy rating	840 J

Ordering and shipping details

GTIN	731304016588
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	14.02 in (35.6 cm)
Package 1 Width	1.9 in (4.8 cm)
Package 1 Length	5.2 in (13.3 cm)
Package 1 Weight	1.81 lb(US) (0.82 kg)
Number of Units in Package 2	12
Package 2 Height	8.13 in (206.50 mm)
Package 2 Width	15.5 in (393.7 mm)
Package 2 Length	16.37 in (415.80 mm)
Package 2 Weight	20 lb(US) (9.07 kg)
Number of Units in Package 3	360
SCC14	10731304016585

Contractual warranty

Warranty	Limited Lifetime
----------	------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

Reach Free Of Svhc

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

Circularity Profile [End of Life Information](#)

California Proposition 65 WARNING: This product can expose you to chemicals including: 1,3-Butadiene, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov