



This cable is constructed from 28 AWG wire, and is foil shielded to protect short cable runs from EMI/RFI interference. The fully molded connectors have easy-to-use extra long thumbscrews for a fast connection. Use this cable for video presentations, classroom environments or just for organizing a work area for maximum comfort and efficiency.

SVGA provides a screen resolution of 800 x 600 pixels.

Please Note: Pin 9 is not loaded. Pin 9 is not required for standard computer video applications.

Features & Benefits

SVGA resolution 800 x 600 pixels

Foil shielded to protect cable runs from EMI/RFI

Extra long thumbscrews for easy connecting

Specifications

General Info

Product Line	C2G	Color	Beige
UPC Number	757120094555	Country Of Origin	China
Application Sector	Commercial, Residential	Warranty Type	Lifetime
Type	Cable		

Dimensions

Product Length US	10.0 FT	Cable Length	10 ft
-------------------	---------	--------------	-------

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Wire Gauge	28 AWG
Video Resolution	SVGA (800x600)	Cable Type	Video
Jacket Rating	Standard / Non-Rated	Adapter Rear	VGA Male

Adapter Front

VGA Male
