

# Product data sheet

Specifications



## Power Cord, C19 to L6-20P, 3.7m

AP9871



**Product availability: Stock - Normally stocked in distribution facility**

### Overview

Lead time Usually in Stock

### Main

Product or Component Type	Power cord
Input Connection Type	NEMA L6-20P
number of rack unit	0U
Cable length	12 ft (3.7 m)
Number of cables	1

### Physical

Color	Black
Height	2.5 in (6.4 cm)
Width	4.02 in (10.2 cm)
Depth	11.5 in (29.2 cm)
Net Weight	2.2 lb(US) (1 kg)
mounting location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable

### Input

Input Frequency	50/60 Hz
Acceptable Input Voltage	200...240 V
Max line current	16 A
Input current limits	16 A

### Output

Maximum Total Current Draw per Phase	16 A
Number of power socket outlets	1 IEC 60320 C19
Protection Type	Without circuit breaker

### Conformance

Product Certifications	CSA UL Listed
------------------------	------------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Environmental

Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

## Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304111030
Returnability	No
Country of origin	US

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.02 in (10.2 cm)
Package 1 Width	12.008 in (30.5 cm)
Package 1 Length	4.02 in (10.2 cm)
Package 1 Weight	2.4 lb(US) (1.1 kg)

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Take-back   Transparency   RoHS/REACH

## Resource performance

 Take-Back Program Available

## Well-being performance

 Lead Free

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Circularity Profile

[End of Life Information](#)

California Proposition 65

WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)