

# Product data sheet

Specifications



## Power Cord, C19 to IEC309 16A, 2.5m



AP9876

Product availability: Stock - Normally stocked in distribution facility

### Overview

Lead time Usually in Stock

### Main

Product or Component Type Power cord  
Input Connection Type IEC 60309 16 A  
Cable length 8.2 ft (2.5 m)  
Number of cables 1

### Physical

Color Black  
Net Weight 0.53 lb(US) (0.24 kg)  
Mounting preference No preference  
Mounting Mode Not rack-mountable

### Input

Input Frequency 50/60 Hz  
Acceptable Input Voltage 90...250 V  
Max line current 16 A  
Input current limits 16 A

### Output

Maximum Total Current Draw per Phase 16 A  
Number of power socket outlets 1 IEC 60320 C19  
Protection Type Without circuit breaker

### Conformance

Product Certifications VDE

### Environmental

Ambient Air Temperature for Operation 32...113 °F (0...45 °C)  
Relative Humidity 0...95 %  
Operating altitude 0...10000 ft

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

## Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304189398
Returnability	No
Country of origin	CN

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.008 in (5.1 cm)
Package 1 Width	4.02 in (10.2 cm)
Package 1 Length	8.0 in (20.3 cm)
Package 1 Weight	0.659 lb(US) (0.299 kg)
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	9.2 in (23.3 cm)
Package 2 Width	12.8 in (32.5 cm)
Package 2 Length	20.9 in (53 cm)
Package 2 Weight	11.2 lb(US) (5.1 kg)
Unit Type of Package 3	PAL
Number of Units in Package 3	10
Package 3 Height	56.69 in (143.99 cm)
Package 3 Width	39.4 in (100 cm)
Package 3 Length	47.2 in (120 cm)
Package 3 Weight	11.2 lb(US) (5.1 kg)

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Take-back Transparency RoHS/REACH

## Resource performance

 Take-Back Program Available

## Well-being performance

 Lead Free

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Circularity Profile

[End of Life Information](#)

California Proposition 65

WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)