

Product data sheet

Specifications



Power Cord, C19 to CEE/7 Schuko, 2.5m



AP9875

Product availability: Stock - Normally stocked in distribution facility

Overview

Lead time Usually in Stock

Main

| | |
|----------------------------------|------------------------|
| Product or Component Type | Power cord |
| Input Connection Type | Schuko CEE 7 / EU1-16P |
| number of rack unit | 0U |
| Cable length | 8.2 ft (2.5 m) |
| Number of cables | 1 |

Physical

| | |
|----------------------------|-----------------------|
| Color | Black |
| Net Weight | 0.49 lb(US) (0.22 kg) |
| Mounting preference | No preference |
| Mounting Mode | Not rack-mountable |

Input

| | |
|---------------------------------|------------|
| Input Frequency | 50/60 Hz |
| Acceptable Input Voltage | 90...250 V |
| Max line current | 16 A |
| Input current limits | 16 A |

Output

| | |
|---|-------------------------|
| Maximum Total Current Draw per Phase | 16 A |
| Number of power socket outlets | 1 IEC 60320 C19 |
| Protection Type | Without circuit breaker |

Conformance

Product Certifications VDE

Environmental

| | |
|--|-------------------------|
| Ambient Air Temperature for Operation | 32...113 °F (0...45 °C) |
| Relative Humidity | 0...95 % |
| Operating altitude | 0...10000 ft |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| | |
|-------------------------------------|--|
| Ambient Air Temperature for Storage | -13...149 °F (-25...65 °C) |
| Storage Relative Humidity | 0...95 % |
| Storage altitude | 0...50000 ft (0.0000000000...15240.0000000000 m) |

Ordering and shipping details

| | |
|-------------------|---------------------------|
| Category | 11309-APC RESALE PRODUCTS |
| Discount Schedule | APC1 |
| GTIN | 731304189404 |
| Returnability | No |
| Country of origin | CN |

Packing Units

| | |
|------------------------------|-------------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 2.008 in (5.1 cm) |
| Package 1 Width | 4.02 in (10.2 cm) |
| Package 1 Length | 8.0 in (20.3 cm) |
| Package 1 Weight | 0.659 lb(US) (0.299 kg) |
| Unit Type of Package 2 | CAR |
| Number of Units in Package 2 | 10 |
| Package 2 Height | 10.04 in (25.5 cm) |
| Package 2 Width | 13.07 in (33.2 cm) |
| Package 2 Length | 21.1 in (53.6 cm) |
| Package 2 Weight | 9.9 lb(US) (4.5 kg) |
| Unit Type of Package 3 | PAL |
| Number of Units in Package 3 | 10 |
| Package 3 Height | 56.69 in (143.99 cm) |
| Package 3 Width | 39.4 in (100 cm) |
| Package 3 Length | 47.2 in (120 cm) |
| Package 3 Weight | 9.9 lb(US) (4.5 kg) |

Contractual warranty

| | |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Take-back Transparency RoHS/REACH

Resource performance

 Take-Back Program Available

Well-being performance

 Lead Free

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Circularity Profile

[End of Life Information](#)

California Proposition 65

WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov