

40 ft DVI-D Dual Link Cable - M/M

Product ID: DVIDDMM40



The DVIDDMM40 40ft DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and offers 40 feet in cable length, making it perfect for longer connections between your desktop or laptop computer and a DVI-D monitor or projector.

The 40 ft DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices

- Compliant with DVI DDWG Standards

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Industry Standards	DVI DDWG Standard

Connector(s)

Connector A	DVI-D (25 pin)
Connector B	DVI-D (25 pin)

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	40.0 ft [12.2 m]
Product Length	40.0 ft [12.2 m]
Weight of Product	2.5 lb [1.1 kg]

Packaging Information

Package Length	8.7 in [22 cm]
Package Width	8.7 in [22 cm]
Package Height	2.4 in [60 mm]
Shipping (Package) Weight	2.5 lb [1.1 kg]

What's in the Box

Included in Package	40 ft DVI-D Dual Link Cable - M/M
---------------------	-----------------------------------

****Product appearance and specifications are subject to change without notice.***