

50 ft DVI-D Dual Link Cable - M/M

Product ID: DVIDDMM50



The DVIDDMM50 50ft DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and offers 50 feet in cable length, making it perfect for longer connections between your desktop or laptop computer and a DVI-D monitor or projector.

The 50 ft DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices

- Compliant with DVI DDWG Standards

Hardware

Warranty	Lifetime
Industry Standards	DVI DDWG Standard

Connector(s)

Connector A	DVI-D (25 pin)
Connector B	DVI-D (25 pin)

Environmental

Operating Temperature	0C to 40C (32F to 104F)
-----------------------	-------------------------

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	50.0 ft [15.2 m]
Product Length	50.0 ft [15.2 m]
Weight of Product	3.0 lb [1.4 kg]

Packaging Information

Package Length	12.6 in [32 cm]
Package Width	9.8 in [25 cm]
Package Height	2.8 in [70 mm]
Shipping (Package) Weight	3.0 lb [1.4 kg]

What's in the Box

Included in Package	50 ft DVI-D Dual Link Cable - M/M
---------------------	-----------------------------------

**Product appearance and specifications are subject to change without notice.*

