

## 2 Port VGA Video Splitter - USB Powered

**Product ID:** ST122LE



This 2-Port VGA Video Splitter allows a computer to display VGA video on two monitors simultaneously.

Perfect for classrooms, tradeshows, or any environment requiring high quality video on several monitors, the ST122LE VGA splitter supports displays with up to 300 MHz of bandwidth and up to 2048x1536 resolution. Plus, to simplify placement of your VGA displays, the splitter features a built-in booster circuit that allows you to locate VGA monitors up to 200 ft away from your system, and can be powered through a USB connection to the host computer, eliminating the need to find an available power outlet.

### Application Diagram

The ST122LE VGA Splitter supports easy plug and play installation, and is backed by StarTech.com's 2-year warranty and FREE lifetime tech support.

## Certifications, Reports and Compatibility

### Applications

- Use for in-store product merchandising in retail environments to give your advertisements greater visibility
- Display travel schedules and alerts in airports, bus terminals and train stations
- Create engaging multimedia presentations for demonstration in lecture halls and classrooms
- Get your message across multiple displays for trade-shows or information booths/kiosks
- Quick and easy solution to split a video signal in an auditorium or house of worship

## Features

- Supports resolutions up to 2048 x 1536 @60Hz
- USB-Powered
- Our most compact VGA splitter
- 300 MHz video bandwidth
- Integrated signal amplifier boosts your connection range to 200 feet (60 meters)
- Supports DDC, DDC2, DDC2B (For video out port 1)

---

### Hardware

Warranty	2 Years
Ports	2
Industry Standards	DDC, DDC2, DDC2B, on Video Out Port 1

---

### Performance

Maximum Cable Length	199.9 ft [61.0 m]
Maximum Analog Resolutions	2048x1536
Bandwidth	300MHz
MTBF	40,000 Hours

---

### Connector(s)

Connector A	VGA (15 pin, High Density D-Sub)
Connector B	VGA (15 pin, High Density D-Sub)

---

### Power

Power Source	USB-Powered
Output Voltage	5 DC
Output Current	0.5A
Center Tip Polarity	Positive
Plug Type	M

---

### Environmental



Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-20C to 85C (-4F to 185F)
Humidity	0% - 95%

---

**Physical Characteristics**

Color	Black
Material	Plastic
Weight of Product	3.5 oz [100 g]

---

**Packaging Information**

Package Length	8.3 in [21 cm]
Package Width	5.7 in [14.5 cm]
Package Height	1.6 in [40 mm]
Shipping (Package) Weight	8.3 oz [235 g]

---

**What's in the Box**

Included in Package	Video Splitter
	USB to DC power adapter
	User Manual

---

***\*Product appearance and specifications are subject to change without notice.***

